

## I10100

**Model Number:** MN01X1R0-10D203-2ST5A0H10-S  
**Category:** Basic  
**Sub Category:** Upgradeable  
**Power Configuration:** 20A, 120V, 1.9kW  
**Physical Configuration:** 19in / 483mm, Horizontal



**Description:** I10100 provides reliable power distribution where you need it in the rack. With the Geist Upgradeable hot-swap technology, users may easily transform basic PDUs to metered or monitored PDUs with the addition of the appropriate Interchangeable Monitoring Device (IMD) module; all without causing any interruption.

**Product Summary:** I10100 - Basic, Upgradeable, 20A, 120V, Horizontal, (10) NEMA 5-20R, 10 ft power cord with 5-20P, No Monitoring (Upgradeable with IMD module). Black Powder Coat.

**Monitoring:** No Monitoring (Upgradeable with IMD module)

**Plug Form:**



5-20P

**Receptacle:**



NEMA 5-20R  
(Quantity: 10)

**Chassis Colors Options:**



Geist Americas

800.432.3219  
geistglobal.com

Geist DCIM  
1.877.449.4150  
geistglobal.com

Geist Europe

+44 (0) 1823.275100  
geistglobal.com

Geist Asia

China  
+86.755.86639505  
geistglobal.com

*To discuss color options, contact your local sales representative.*

**Geist Americas**

800.432.3219  
[geistglobal.com](http://geistglobal.com)

Geist DCIM  
1.877.449.4150  
[geistglobal.com](http://geistglobal.com)

**Geist Europe**

+44 (0) 1823.275100  
[geistglobal.com](http://geistglobal.com)

**Geist Asia**

China  
+86.755.86639505  
[geistglobal.com](http://geistglobal.com)

## Product Specification and Options:

Monitoring	No Monitoring (Upgradeable with IMD module)
Quantity Of Inputs	1
Voltage	120V
Current	20A
VA per Input (Load Capacity)	1.9kW
Frequency	50/60Hz
Over Current Protection	None
Switch	No
Power Cable Wire Gauge	12/3
Power Cable Length	10ft
Power Entry Location	Left Rear
Plug Type	NEMA 5-20P
Receptacle/Socket Type #1	NEMA 5-20R
- Quantity on Rear	10
- Style	Duplex
- Voltage per Receptacle/Socket	120V
Maximum Operating Temperature	60C / 140F
Heavy Steel - Powder Coat Finish	Black
Configuration	1U
Adjustable Mount Brackets	Yes
Made in the USA	Yes
Product Warranty	5-year limited warranty if registered within 120 days of purchase, otherwise warranty defaults to 3 years
Certification/Agency Approvals	FCC Part 15 Class A Conformance
Certification/Agency Approvals	RoHS Compliant
Certification/Agency Approvals	UL & c-UL Listed 60950
Chassis Dimensions (HxWxD)	1.72in x 17in x 8.5in
Shipped Weight	12lbs (5.44kg)

### Geist Americas

800.432.3219  
geistglobal.com

Geist DCIM  
1.877.449.4150  
geistglobal.com

### Geist Europe

+44 (0) 1823.275100  
geistglobal.com

### Geist Asia

China  
+86.755.86639505  
geistglobal.com