

## 11029

**Model Number:** VHVLN082-102I44TL6  
**Category:** Basic  
**Sub Category:** Standard  
**Power Configuration:** 20A, 208V, 3.3kW  
**Physical Configuration:** 17in / 432mm, Horizontal/Vertical



**Description:** The 11029 functions as a basic power strip without built-in surge protection. This unit is ideal for installations in facilities with proper surge protection at the main electrical service entrance.

**Product Summary:** 11029 - Basic, Standard, 20A, 208V, Horizontal/Vertical, (4) IEC C13, (4) IEC C19, 10 ft power cord with L6-20P, Black Powder Coat.

**Plug Form:**



L6-20P

**Receptacle:**



IEC C13  
(Quantity: 4)



IEC C19  
(Quantity: 4)

**Chassis Colors Options:**



*To discuss color options, contact your local sales representative.*

## Product Specification and Options:

Quantity Of Inputs	1
Voltage	208V
Current	20A
VA per Input (Load Capacity)	3.3kW
Frequency	50/60Hz
Over Current Protection	None
Switch	No
Power Cable Wire Gauge	12/3
Power Cable Length	10ft
Plug Type	NEMA L6-20P Twistlock
Combined Total Receptacle/Socket Quantity	8
Receptacle/Socket Type #1	IEC C13
- Quantity on Face	4
- Style	Banks of 2
- Maximum Output per Receptacle/Socket	15A per receptacle bank
- Voltage per Receptacle/Socket	208V
Receptacle/Socket Type #2	IEC C19
- Quantity on Face	4
- Style	Individual
- Maximum Output per Receptacle/Socket	20A
- Voltage per Receptacle/Socket	208V
Continuous Operating Temperature Range	10-45C / 50-113F
Heavy Steel - Powder Coat Finish	Black
Configuration	17in / 432mm Vertical/Horizontal Rackmount
19in Panel Mount Brackets	Yes
SLB-4 Brackets	Yes
Made in the USA	Yes
Product Warranty	5-year limited warranty if registered within 120 days of purchase, otherwise warranty defaults to 3 years
Certification/Agency Approvals	RoHS Compliant
Certification/Agency Approvals	UL & c-UL Listed 60950
Chassis Dimensions (LxWxD)	17.0in x 1.72in x 1.85in
Shipped Weight	6lbs (2.72kg)

### Geist Americas

800.432.3219  
geistglobal.com

Geist DCIM  
1.877.449.4150  
geistglobal.com

### Geist Europe

+44 (0) 1823.275100  
geistglobal.com

### Geist Asia

China  
+86.755.86639505  
geistglobal.com