

38136

Model Number: VREBN200-103D20TL6
Category: Basic
Sub Category: Standard
Power Configuration: 30A, 208V, 4.9kW
Physical Configuration: 66in / 1683mm, Vertical



Description: The 38136 functions as a basic power strip without built-in surge protection. This unit is ideal for installations in facilities with proper surge protection at the main electrical service entrance.

Product Summary: 38136 - Basic, Standard, 30A, 208V, Vertical, (20) NEMA 6-20R, breakered, 10 ft power cord with L6-30P, Black Powder Coat.

Plug Form:



L6-30P

Receptacle:



NEMA 6-20R
(Quantity: 20)

Chassis Colors Options:



To discuss color options, contact your local sales representative.

Product Specification and Options:

Quantity Of Inputs	1
Voltage	208V
Current	30A
VA per Input (Load Capacity)	4.9kW
Frequency	50/60Hz
Over Current Protection	(4) 15A Thermal Breakers
Switch	No
Power Cable Wire Gauge	10/3
Power Cable Length	10ft
Plug Type	NEMA L6-30P Twistlock
Receptacle/Socket Type #1	NEMA 6-20R
- Quantity on Face	20
- Quantity per Breaker Pair	10
- Style	Duplex
- Maximum Output per Receptacle/Socket	15A
- Voltage per Receptacle/Socket	208V
Continuous Operating Temperature Range	10-45C / 50-113F
Heavy Steel - Powder Coat Finish	Black
Configuration	66in / 1683mm Vertical Rackmount
7938 Vertical Mounting Bracket Kit	Yes
Toolless Mounting Hardware - Center to Center Spacing	61.25in and 64.75in
Made in the USA	Yes
Product Warranty	5-year limited warranty if registered within 120 days of purchase, otherwise warranty defaults to 3 years
Certification/Agency Approvals	RoHS Compliant
Certification/Agency Approvals	UL & c-UL Listed Accessory 1950
Chassis Dimensions (LxWxD)	66.25in x 1.85in x 1.61in
Shipped Weight	15lbs (6.8kg)