

27849

Model Number: BRF060-10
Category: Basic
Sub Category: Standard
Power Configuration: 15A, 120V, 1.4kW
Physical Configuration: 19in / 483mm, Horizontal



Description: The 27849 functions as a basic power strip without built-in surge protection. This unit is ideal for installations in facilities with proper surge protection at the main electrical service entrance.

Product Summary: 27849 - Basic, Standard, 15A, 120V, Horizontal, (6) NEMA 5-15R, power switch, breakered, 10 ft power cord with 5-15P, Black Powder Coat.

Plug Form:



5-15P

Receptacle:



NEMA 5-15R
(Quantity: 6)

Chassis Colors Options:



To discuss color options, contact your local sales representative.

Geist Americas

800.432.3219
geistglobal.com

Geist DCIM
1.877.449.4150
geistglobal.com

Geist Europe

+44 (0) 1823.275100
geistglobal.com

Geist Asia

China
+86.755.86639505
geistglobal.com

Product Specification and Options:

Quantity Of Inputs	1
Voltage	120V
Current	15A
VA per Input (Load Capacity)	1.4kW
Frequency	50/60Hz
Over Current Protection	15A Thermal Breaker
Switch	Yes
Indicators - LED(s)	1 - Power ON Green LED
Power Cable Wire Gauge	14/3
Power Cable Length	10ft
Plug Type	NEMA 5-15P
Receptacle/Socket Type #1	NEMA 5-15R
- Quantity on Face	6
- Quantity per Breaker	6
- Style	Duplex
- Maximum Output per Receptacle/Socket	15A
- Voltage per Receptacle/Socket	120V
Continuous Operating Temperature Range	10-45C / 50-113F
Heavy Steel - Powder Coat Finish	Black
Configuration	19in / 483mm Horizontal Rackmount
Adjustable Mount Brackets	Yes
Made in the USA	Yes
Product Warranty	5-year limited warranty if registered within 120 days of purchase, otherwise warranty defaults to 3 years
Certification/Agency Approvals	RoHS Compliant
Certification/Agency Approvals	UL & c-UL Listed 60950
Chassis Dimensions (HxWxD)	1.72in x 17in x 4.50in
Shipped Weight	6lbs (2.72kg)

Geist Americas

800.432.3219
geistglobal.com

Geist DCIM
1.877.449.4150
geistglobal.com

Geist Europe

+44 (0) 1823.275100
geistglobal.com

Geist Asia

China
+86.755.86639505
geistglobal.com