

## NS30047L

<b>Model Number:</b>	MNS3EHW1-48MI18-5CS15A0A10-S-A
<b>Category:</b>	Switched
<b>Sub Category:</b>	Unit Level Monitoring EC
<b>Power Configuration:</b>	50A, 208V DELTA, 14.4kW
<b>Physical Configuration:</b>	75in / 1905mm, Vertical



**Description:** The NS30047L provides IP-based monitoring and outlet control with quick access to real-time power metrics and environmental sensor data. Using Visible Light Communication (VLC) technology, NS30047L optically transmits power usage data from its LED display to a handheld device using the Geist Mobile App, presenting comprehensive power usage data down to the phase and circuit levels. With the Geist Upgradeable hot-swap technology, users may easily upgrade PDUs to the latest available technology by replacing the Interchangeable Monitoring Device (IMD) module.

**Product Summary:** NS30047L - Switched, Unit Level Monitoring EC, Upgradeable, 50A, 208V DELTA, 3 Phase, Vertical, (42) Locking IEC C13, (6) Locking IEC C19, Alternating Phase/Circuits, breaker, 10 ft / 3m power cord with 3P+E CA, Input power monitoring with Outlet switching. Circuit/Breaker current monitoring. Environmental monitoring via optional remote sensors. Daisy chain Ethernet connectivity. Local high visibility LED display. Black Powder Coat.

**Monitoring:** Input power monitoring with Outlet switching. Circuit/Breaker current monitoring. Environmental monitoring via optional remote sensors. Daisy chain Ethernet connectivity. Local high visibility LED display.

**Plug Form:**



3P+E CA

**Receptacle:**



Locking IEC C13  
(Quantity: 42)



Locking IEC C19  
(Quantity: 6)

---

**Chassis Colors Options:**



*To discuss color options, contact your local sales representative.*

**Geist Americas**

800.432.3219  
geistglobal.com

Geist DCIM  
1.877.449.4150  
geistglobal.com

**Geist Europe**

+44 (0) 1823.275100  
geistglobal.com

**Geist Asia**

China  
+86.755.86639505  
geistglobal.com

## Product Specification and Options:

Monitoring	Input power monitoring with Outlet switching. Circuit/Breaker current monitoring. Environmental monitoring via optional remote sensors. Daisy chain Ethernet connectivity. Local high visibility LED display.
Input Monitoring	Total Unit Monitoring (kWh, W, VA, PF) Phase (AB, BC, CA) Monitoring (kWh, W, VA, PF, V, A) Line (A, B, C) Monitoring (A)  Power Measurements Compliant with ANSI C12.1 and IEC 62053-21 at 1% Accuracy Class Requirements
Circuit Monitoring	Circuit / Breaker Monitoring (A)  Circuit/Breaker Current Measurements Independently Tested and Verified at 2% Accuracy
Remote Power Management	Individual Outlet Switching with Optional User Defined Time Delays and Sequential Power-up
VLC Support	Yes
Quantity Of Inputs	1
Voltage	200-240V Delta
Current	50A x 3 Phase DELTA
VA per Input (Load Capacity)	14.4kW (208V)
Frequency	50/60Hz
Over Current Protection	(6) 20A Double Pole Magnetic Breakers (5kAIC Rated)
Switch	Breaker/Switch Combination
Scrolling / Rotatable Digital Display	Yes
Indicators - LED(s)	48
Power Cable Wire Gauge	6/4
Power Cable Length	10ft / 3m
Power Entry Location	Bottom Front
Plug Type	California Style 50A, 250V, 3P/4W Twistlock
Combined Total Receptacle/Socket Quantity	48
Alternating Phase/Circuits	Yes
Receptacle/Socket Type #1	U-Lock IEC C13
- Quantity on Face	42
- Quantity per Breaker	7
- Quantity per Phase Combination	14
- U-Lock Color ID	6 Circuit = Orange, Green, Blue, Light Orange, Light Green, Light Blue
- Style	Individual
- Voltage per Receptacle/Socket	208V
Receptacle/Socket Type #2	U-Lock IEC C19
- Quantity on Face	6
- Quantity per Breaker	1
- Quantity per Phase Combination	2

- U-Lock Color ID	6 Circuit = Orange, Green, Blue, Light Orange, Light Green, Light Blue
- Style	Individual
- Voltage per Receptacle/Socket	208V
Network Connection	Dual 10/100Mbps Ethernet
Protocols Supported	DHCP, HTTP, HTTPS, IPv4, IPv6, LDAP, NTP, RSTP, SSH, SMTP, SNMP (v1/v2c/v3), Syslog
Data Access Formats	CSV datalog, JSON API, JSON datalog
USB Support	Yes
IP Reset Button	Yes
Hard Reboot Button	Yes
Remote Sensor RJ Connection Jacks	1 (Supports up to 16 Sensors)
Maximum Operating Temperature	60C / 140F
Heavy Steel - Powder Coat Finish	Black
Configuration	Zero U
7938 Vertical Mounting Bracket Kit	Yes
Toolless Mounting Hardware - Center to Center Spacing	61.25in and 64.75in / 1556mm and 1645mm
Made in the USA	Yes
Product Warranty	5-year limited warranty if registered within 120 days of purchase, otherwise warranty defaults to 3 years
Certification/Agency Approvals	FCC Part 15 Class A Conformance
Certification/Agency Approvals	RoHS Compliant
Certification/Agency Approvals	UL & c-UL Listed 60950
Chassis Dimensions (LxWxD)	75in x 3.7in x 2.6in / 1905mm x 94mm x 66mm
Shipped Weight	26lbs (11.79kg)

#### Geist Americas

800.432.3219  
geistglobal.com

Geist DCIM  
1.877.449.4150  
geistglobal.com

#### Geist Europe

+44 (0) 1823.275100  
geistglobal.com

#### Geist Asia

China  
+86.755.86639505  
geistglobal.com