

## 50012

**Model Number:** BRE160-0020/16  
**Category:** Basic  
**Sub Category:** Standard  
**Power Configuration:** 20A, 120V OR 208V, 1.9 or 3.3kW  
**Physical Configuration:** 19in / 483mm, Horizontal



**Description:** The 50012 functions as a basic power strip without built-in surge protection. This unit is ideal for installations in facilities with proper surge protection at the main electrical service entrance.

**Product Summary:** 50012 - Basic, Standard, 20A, 120/208V, Horizontal, (16) IEC C13, breakered, C20, Black Powder Coat.

**Plug Form:**



C20

**Receptacle:**



IEC C13  
(Quantity: 16)

**Chassis Colors Options:**



*To discuss color options, contact your local sales representative.*

**Geist Americas**

800.432.3219  
geistglobal.com

Geist DCIM  
1.877.449.4150  
geistglobal.com

**Geist Europe**

+44 (0) 1823.275100  
geistglobal.com

**Geist Asia**

China  
+86.755.86639505  
geistglobal.com

## Product Specification and Options:

Quantity Of Inputs	1
Voltage	120V or 208V
Current	20A
VA per Input (Load Capacity)	1.9 or 3.3kW
Frequency	50/60Hz
Over Current Protection	20A Double Pole Magnetic Breaker
Switch	Breaker/Switch Combination
Plug Type	IEC60320 C20 Power Inlet (cord sold separately)
Receptacle/Socket Type #1	IEC C13
- Quantity on Face	4
- Quantity on Rear	12
- Quantity per Breaker	16
- Style	1 Bank of 4; 2 Banks of 6
- Maximum Output per Receptacle/Socket	15A per receptacle bank
- Voltage per Receptacle/Socket	120V or 208V
Continuous Operating Temperature Range	10-45C / 50-113F
Heavy Steel - Powder Coat Finish	Black
Configuration	19in / 483mm Horizontal Rackmount
Adjustable Mount Brackets	Yes
Made in the USA	Yes
Product Warranty	5-year limited warranty if registered within 120 days of purchase, otherwise warranty defaults to 3 years
Certification/Agency Approvals	RoHS Compliant
Certification/Agency Approvals	UL & c-UL Listed 60950
Chassis Dimensions (HxWxD)	1.72in x 17in x 6.50in
Shipped Weight	4lbs (1.81kg)