

Lenovo L22e 65DEKCC1US

Product

Lenovo L22e-20

Region

US

Color

Black

Panel

Vertical Alignment

Display Size

21.5"

View Area

476.06x267.79 mm

Resolution

1920x1080

Aspect Ratio

16:9

Pixel Pitch

0.248x0.248 mm

Dot / Pixel Per Inch

102 dpi

Brightness

250 nits

Contrast Ratio

3000:1

Pixel Response Time

4 ms (extreme mode) / 6 ms/18 ms (typical/off mode)

Color Gamut

72%

View Angle (H / V)

178 / 178

Stand

Tilt Stand

Side Bezel Width

2 mm

Dimensions with Stand (HxWxD)

373.8x489.3x190 mm

Power Consumption (Typical / Maximum)

21W / 24W

Power Adapter

Integrated

Weight (Including Stand)

6.06 lb / 2.75 kg

Lenovo L22e-20

DISPLAY

Panel Size

21.5 inches

Screen Dimensions (H x V)

476.06 x 267.79mm

18.74 x 10.54 inches

Panel Type

VA

Backlight

WLED

Aspect Ratio

16:9

Resolution

1920 x 1080 pixels

Pixel Pitch (H x V)

0.248 x 0.248mm

Viewing Angle (H x V)

178°/178°

Response Time (gray to gray)

4ms (extreme mode)

6ms/18ms (typical/off)

Contrast Ratio (typical)

3000:1

Dynamic Contrast Ratio (typical)

3M:1

Color Gamut NTSC (CIE 1931)

72%

Color Support

16.7M

CONNECTIVITY

Video Input Signals

VGA + HDMI

Video Cable

VGA 1.8m cable

Audio Out

Yes

DIMENSIONS

Size Packed (D x H x W)

582 x 350 x 120mm/22.9 x 13.7 x 4.7 inches

Size Unpacked w/o stand (D x H x W) (Head Only)

41.5 x 296.8 x 489.3mm/1.63 x 11.68 x 19.26 inches

Weight Packed

4.26kg/9.40lbs.

Weight Unpacked

2.75kg/6.06lbs.

Weight (Monitor Head Only)

2.46kg/5.42lbs.

SPECIAL FEATURES

AMD FreeSync™

Yes

Anti-Glare

Yes

MECHANICAL

Tilt Angle (front/back)

-5°/22°

VESA Mount Capability

Yes

Kensington™ Lock Slot

Yes

Cable Management

Yes

Bezel Color

Raven Black

Bezel Width (side)

2mm

Bezel Width (top/bottom)

2.0/21.2mm

WHAT'S IN THE BOX

Monitor with stand

1 x Power cable

1 x VGA cable

Quick setup guide

CERTIFICATIONS

ENERGY STAR® Rating

7.0

EPEAT™

Gold

CCC

Yes

RoHS

Yes

ULE

Yes

TCO

7.0

Windows Certification

Windows 7, Windows 10

China Energy Efficiency Standard

Tier 2

Ambient Operating Temperature

0°C to 40°C

TÜV Low Blue Light

Yes



© 2018 Lenovo. All rights reserved. These products are available while supplies last. Prices shown are subject to change without notice. For any questions concerning price, please contact your Lenovo Account Executive. Lenovo is not responsible for photographic or typographic errors. Warranty: For a copy of applicable warranties, write to: Warranty Information, 500 Park Offices Drive, RTP, NC 27709, Attn: Dept. ZPYA/B600. Lenovo makes no representation or warranty regarding third-party products or services. Trademarks: Lenovo, the Lenovo logo, Rescue and Recovery, ThinkPad, ThinkCentre, ThinkStation, ThinkVantage, and ThinkVision are trademarks or registered trademarks of Lenovo. Microsoft, Windows, and Vista are registered trademarks of Microsoft Corporation. Intel, the Intel logo, Intel Inside, Intel Core, and Core Inside are trademarks of Intel Corporation in the U.S. and/or other countries. Other company, product, and service names may be trademarks or service marks of others.

Specifications may vary depending upon region.

Lenovo™

Lenovo™

Lenovo L22e

