



4K UHD / 3840 x 2160 Resolution / PCAP Touch Technology

I32ZI-OD-45PO

LARGE FORMAT

Technological advances and price decreases have increased the market for large 4k touch screen displays substantially. These innovative designs, comprised of 4k 32" displays and above, are creating opportunities in digital signage, corporate webinars and infotainment. Feel free to inquire about our large touch screen LCDs or engage us with your latest solution project and let our engineers position you for something big.



3840 x 2160
UHD



PCAP Touch
Technology



HDMI Digital
Input



DVI Digital
Input



Display Port
Input




LED
Backlight Unit




3-Year
Warranty


4K UHD / 32-Inch 10-Points PCAP Touch Monitor



INTERFACE & OSD



DIMENSION



FEATURES

- 32-Inch Screen Size
- 4K UHD / 3840 x 2160 Resolution
- 10-Points Projective Capacitive PCAP Touch Technology
- LED Backlight Unit
- Water and Dust Resistant
- Support Video Inputs: HDMI / DVI / DisplayPort (DP)
- 3-Year Warranty

SPECIFICATIONS



DISPLAY	
Screen Size	21.5 In
Resolution	1920 x 1080
Backlight	LED
Aspect Ratio	16 : 9
Viewing Angle	178° / 168°
Response Time	18ms
Brightness	250cd/m ²
Contrast Ratio	3000 : 1
Color Depth	16.7 M
Display Area (mm)	476.64 x 268.11mm
INTERFACE	
HDMI	1
DVI	1
VGA (15 Pin D-Sub)	1
Audio	1
USB (B-Type)	1
TOUCH TECHNOLOGY	
Material	2 mm Glass
Points / Type	10 Max / Projected Capacitive (PCAP)
Accuracy	2 mm
CABINET	
Material	Metal
Color	Black
POWER	
Consumption	22W
Electrical Ratings	12VDC ± 5% (Adapter Input AC 100V ~ 240V, 50/60Hz)
TEMPERATURE	
Operating	32° F ~ 104° F (0° C ~ 40° C)
Storage	-4° F ~ 140° F (-20° C ~ 60° C)
HUMIDITY	
Operating	20% ~ 80%
Storage	10% ~ 90%
DIMENSIONS (WxHxD)	
Inch (in)	21.3 x 13.2 x 1.7
Millimeter (mm)	542.5 x 334.5 x 43.7
WEIGHT	
Net Weight	13.2lbs (6.0kg)
COMPLIANT	
Certification	CE / FCC
VESA™	
Mount Size (mm)	100 x 100

Specifications subject to change without any notice