


## 38129

**Model Number:** 2VRELN160-103C13TL6  
**Category:** Basic  
**Sub Category:** Standard  
**Power Configuration:** 30A, 208V, 4.9kW  
**Physical Configuration:** 2U 19in / 483mm, Horizontal



**Description:** The 38129 functions as a basic power strip without built-in surge protection. This unit is ideal for installations in facilities with proper surge protection at the main electrical service entrance.

**Product Summary:** 38129 - Basic, Standard, 30A, 208V, Horizontal, (16) IEC C13, breakered, 10 ft power cord with L6-30P, Black Powder Coat.

**Plug Form:**



L6-30P

**Receptacle:**



IEC C13  
(Quantity: 16)

**Chassis Colors Options:**



*To discuss color options, contact your local sales representative.*

**Geist Americas**

800.432.3219  
geistglobal.com

Geist DCIM  
1.877.449.4150  
geistglobal.com

**Geist Europe**

+44 (0) 1823.275100  
geistglobal.com

**Geist Asia**

China  
+86.755.86639505  
geistglobal.com

## Product Specification and Options:

Quantity Of Inputs	1
Voltage	208V
Current	30A
VA per Input (Load Capacity)	4.9kW
Frequency	50/60Hz
Over Current Protection	(4) 15A Thermal Breakers
Switch	No
Power Cable Wire Gauge	10/3
Power Cable Length	10ft
Plug Type	NEMA L6-30P Twistlock
Receptacle/Socket Type #1	IEC C13
- Quantity on Face	16
- Quantity per Breaker Pair	8
- Style	Banks of 4
- Maximum Output per Receptacle/Socket	15A per receptacle bank
- Voltage per Receptacle/Socket	208V
Continuous Operating Temperature Range	10-45C / 50-113F
Heavy Steel - Powder Coat Finish	Black
Configuration	19in / 483mm Horizontal Rackmount
Flush Mount	Yes
Made in the USA	Yes
Product Warranty	5-year limited warranty if registered within 120 days of purchase, otherwise warranty defaults to 3 years
Certification/Agency Approvals	RoHS Compliant
Certification/Agency Approvals	UL & c-UL Listed Accessory 1950
Chassis Dimensions (HxWxD)	3.45in x 17in x 1.61in
Shipped Weight	8lbs (3.63kg)

### Geist Americas

800.432.3219  
geistglobal.com

Geist DCIM  
1.877.449.4150  
geistglobal.com

### Geist Europe

+44 (0) 1823.275100  
geistglobal.com

### Geist Asia

China  
+86.755.86639505  
geistglobal.com