

# CyberPower

## PR1000RT2UN SMART APP SINEWAVE UPS



Protect corporate and network servers, telecom installations, and VoIP systems.

The PR1000RT2UN is a New Smart App Sinewave rack/tower convertible UPS with line-interactive topology, surge protection, and battery backup. CyberPower's New Smart App Sinewave series has sine wave output to eliminate power gaps that can be detected by sensitive equipment and cause unexpected shutdowns.

The New Smart App Sinewave PR1000RT2UN improves battery life through battery equalization technology and Automatic Voltage Regulation (AVR), which corrects minor power fluctuations without switching to battery power. The new chassis design with an easy-to-access toolless front panel, color-coded rear panel, and captive screws for battery panel access make installations and battery changes simple and fast. The PR1000RT2UN also has a new LCD panel that rotates 90°, tilts for a better viewing angle, and provides information on 47 different settings including UPS stats, UPS setup and control management, and testing options.

### TYPICAL APPLICATIONS

- Servers
- Workstations
- Network Devices
- Telecom Equipment

### FEATURES

- 1000 VA/1000 W
- Line-Interactive Topology
- GreenPower UPS™
- 2U Rack Mount/Tower Convertible

## SPECIFICATIONS

### GENERAL

UPS Topology	Line-Interactive
Energy Saving	GreenPower UPS™ Bypass Technology
ENERGY STAR® Qualified	Yes
Active PFC Compatible	Yes


### INPUT

Voltage	100 - 125 VAC
Frequency	47 - 63 Hz
Input Voltage Range	70 - 155 VAC
Plug Type	NEMA 5-15 P
Plug Style	Right Angle, 45° Offset Right
Cord Length	10 FT

### OUTPUT

VA	1000
Watts	1000
Automatic Voltage Regulation	Double Boost, Single Buck
On Battery Voltage	100/110/120/125 Vac ± 5%
On Battery Frequency	50/60 Hz +/- 1%
On Battery Waveform	Sine Wave
Outlets - Total	8
Outlet Type	NEMA 5-15 R
Outlets - Critical Load	4
Outlets - Battery & Surge Protected	8

# PR1000RT2UN SMART APP SINEWAVE UPS



## SPECIFICATIONS CONT.

### OUTPUT CONT.

Rated Power Factor	1
Overload Protection	Internal Circuitry Limiting/ Circuit Breaker
Transfer Time	4ms Typical

### BATTERY

Runtime at Half Load (min)	9.5
Runtime at Full Load (min)	7
Battery Type	Sealed Lead-Acid
Battery Size	12 V / 7A H
Hot-Swappable	Yes
Replacement Battery	RB1270 X 4H
Battery Quantity	4
User Replaceable	Yes
Typical Recharge Time	3 Hrs
External Battery Pack Option	No

### SURGE PROTECTION & FILTERING

RJ11 / RJ45	1 - In, 1 - Out
Surge Suppression	2430
EMI/RFI Filtration	Yes

### MANAGEMENT & COMMUNICATIONS

Multifunction LCD Panel	47 Settings (27 Setup and Control Items + 20 Status Updates and Log Menus)
HID Compliant USB Port	Yes
Serial Port	Yes
EPO Port	Yes
Contact Closure	Yes
Management Cable	USB Cable, Serial Cable, EPO Cable

### MANAGEMENT & COMMUNICATIONS

ED Indicators	Power On, Line Mode, Battery Mode, Fault, Night Mode, Wiring Fault
Audible Alarms	Battery Mode, Low Battery, Overload, Overcharge, Overheat
Software	PowerPanel® Business Edition
SNMP/HTTP Remote Monitoring	Yes - RMCARD205 included

### PHYSICAL

Rack Size	2U
Form Factor	Rack/Tower
Dimensions (WxHxD) (in.)	17.1 x 3.4 x 16.2
Weight (lbs.)	50.1
Shipping Dimensions (WxHxD) (in.)	22.1 X 10.8 X 20.9
Shipping Weight (lbs.)	58

### ENVIRONMENTAL

Operating Temperature	32° F to 104° F (0° C to 40° C)
Operating Relative Humidity	0 - 95% Non-Condensing)
Storage Temperature	5° F to 113° F (-15° C to 45° C)
Maximum Operating Elevation	10,000 ft (3,000 m)
Maximum Storage Elevation	50,000 ft (15,000 m)
AC Mode Thermal Dissipation	47.4

### CERTIFICATIONS

Safety	UL1778, cUL107.1, FCC Class B
Environmental	RoHS Compliant

### WARRANTY

Product Warranty	Three-Years Limited
Connected Equipment Guarantee	Lifetime
CEG Amount	\$400,000