

## MultiSync® X551UHD

LCD 55" Ultra-High Definition Large Format Display

## Datasheet



### Unmatched richness of detail

Enjoy a new era of visual experience with an expansive digital canvas delivering pixel-free viewing. This 55 inch (139 cm) Ultra High Definition (UHD) screen is perfectly suited for reference applications where intense detail and colour accuracy is demanded. The 3840 x 2160 resolution facilitates both distance and proximity viewing with precise colour fidelity regardless of the viewing angle for a reality-like visual experience. Designed for 24/7 operation and offering high usage flexibility thanks to its wide connectivity, this screen provides future-proof investment security.

This state-of-the-art technology is ideal for any heavy duty applications including CAD/CAM, creative multimedia design, control room, medical review as well as high end retail signage applications.

## Benefits

**Stunning "pixel-free" ergonomic viewing** – delivered by an Ultra High Definition (3,840 x 2,160) Professional LED backlit S-PVA panel.

**Enhanced imaging performance** – advanced settings of all relevant visual parameters allow full control of brightness, colour, gamma and uniformity via the Spectraview Engine for precise, natural images.

**Reliable colour reproduction** – due to 10-bit colour performance, extreme viewing angles and hardware calibratable LUT, viewers benefit from consistently accurate image rendering.

**Mission-critical 24/7 ready operation** – with reliable, industry grade components and NEC trusted performance.

**Wide array of flexible application scenarios** – thanks to multi-source conferencing and efficient split-screen operation supported by a wide future-ready range of digital connectivity.

**Future Ready with OPS Cable Free Expansion** – upgrade the power of your display at any time while seamlessly integrating one of our various Slot-in PCs, signal interfaces and other OPS compatible products without the need for external cables or devices.

**Perfectly Scaled** – lower resolution content (e.g. FullHD) can be upscaled to UHD resolution via a bi-cubic 4x4 pixel interpolation algorithm in order to achieve smooth colours and clear edges.

**Free Download of Multi-Display Management Software** – with NaViSet Administrator 2 you can manage all your connected display devices from a centralised location.

**DICOM support** – for medical applications.

## Product Information

Product Name	MultiSync® X551UHD
Product Group	LCD 55" Ultra-High Definition Large Format Display
Order Code	60003677

## Display

Panel Technology	S-PVA with edge LED backlights
Active Screen Area (W x H) [mm]	1,209 x 680
Screen Size [inch/cm]	55 / 140
Brightness [cd/m²]	500, 300 Eco (shipment setting)
Contrast Ratio (typ.)	4000:1
Viewing Angle [°]	178 horizontal / 178 vertical (typ. at contrast ratio 10:1)
Response Time (typ.) [ms]	6 (grey-to-grey)
Haze Level [%]	25
Supported Orientation	Face Up; Landscape; Portrait

## Synchronisation Rate

Horizontal Frequency [kHz]	28 - 134
Vertical Frequency [Hz]	23 - 85

## Resolution

Native Resolution	3840 x 2160 at 60 Hz			
Supported on DisplayPort and HDMI	3840 x 2160 (24/30 Hz); 1920 x 1080; 1600 x 1200; 1360 x 768;	1280 x 1024; 1280 x 768; 1080i; 1080p;	1024 x 768; 800 x 600; 720p (50/60 Hz); 640 x 480;	480p (60 Hz)
Supported on DisplayPort only	3840 x 2160 (60 Hz)			
Supported on HDMI only	4096 x 2160 (24 Hz); 3840 x 2160 (25 Hz);	1360 x 768; 576i (50 Hz);	480i (60 Hz)	

## Connectivity

Input Video Digital	1 x DisplayPort (with HDCP); 2 x DVI-D (with HDCP); 4 x HDMI (with HDCP)
Input Audio Analogue	1 x 3,5 mm jack
Input Audio Digital	1 x HDMI; DisplayPort
Input Control	LAN 100Mbit; remote control wire (3,5mm jack); RS232
Output Audio Analogue	3,5mm jack
Output Control	LAN 100Mbit
Remote Control	LAN with SNMP; Remote Control IR (internal/external (optional) sensor); RS-232C (9-pin D-sub) Input

## Open Modular Intelligence

OPS Slot	Slot Technology: Open pluggable specification (NEC / Intel OPS standard)
Inrush Current [A]	max. 10
Power Consumption [W]	max. 61
Voltage / Current [V/A]	16/4

## Sensors

Ambient Light Sensor	Integrated, triggered actions programmable
Human Sensor	Optional, external, 4-5m range, triggered actions programmable
Temperature Sensor	Integrated, 3 sensors, triggered actions programmable
NFC Sensor	Integrated, 2cm range, free NEC Android App required

## Electrical

Power Consumption [W]	150 Eco (shipment setting), 240
Power Savings Mode [W]	< 0.5; < 0.5 (ECO Standby)
Power Management	VESA DPMS

## Environmental Conditions

Operating Temperature [°C]	+0 to +40
Operating Humidity [%]	20 to 80

## Mechanical

Dimensions (W x H x D) [mm]	Without stand: 1,250 x 721 x 78
Weight [kg]	Without stand: 27
Bezel Width [mm]	18.5
VESA Mounting [mm]	4 holes; 400 x 400 (FDMI); M8
Ingress Protection	IP40 (front); IP20 (back)

## Available Options

Accessories	Feet (ST-5220); Speaker (SP-RM1); Trolley (PDMHM-L); Wall mount (PDW S 32-55 PL)
OPS Slot	HD-SDI 1.5G,3G; HDBaseT receiver; Intel® Atom, Celeron and Core CPUs; OPS-2C HDMI + DP Interface; OPS-2C Quad 3G SDI

## Green Features

Energy Efficiency	Ambient light sensor; Annual energy consumption: 219 kWh (based on 4 operating hours per day); Carbon savings meter; ECOMode; Energy efficiency class: A; Human Sensor
Ecological Materials	Manuals on CD; Optional feet

## Additional Features

Special Characteristics	Carbon footprint meter; DICOM Simulation; NaViSet Administrator 2
Colour Versions	Black Front Bezel, Black Back Cabinet
Safety and Ergonomics	C-tick; CE; FCC Class B; PSB; RoHS; TÜV GS; UL/C-UL or CSA; VCCI
Pixel Failure Class	ISO 9241-307, Class 2
Audio	Integrated Speakers (10 W + 10 W); Optional Speakers (15 W + 15 W)
Shipping Content	CD-ROM (User Guides/Manuals); Display; DisplayPort Cable; Power Cable; Remote Control
Warranty	3 years warranty incl. backlight; additional services available; optional 4. + 5. year warranty extension
Operating Hours	24/7



CE



C-tick



FCC Class B



RoHS



TÜV GS



VCCI

This document is © 2018 NEC Display Solutions Europe GmbH.

All rights reserved in favour of their respective owners. All hardware and software names are brand names and/or registered trademarks of the respective manufacturers. All specifications are subject to change without notice. Errors and omissions are excepted. 05.12.2018