

# Product data sheet

Specifications



## APC SmartUPS Industrial 1300VA / 1300W, 120VAC In/Out RM Conformal Coated

XU1K3LLXRCC

### Overview

Lead time Usually in Stock

### Main

Main Input Voltage	120 V
Product or Component Type	Uninterruptible power supply (UPS)
Main Output Voltage	120 V
Kw Rating	1300 W
Rated power in VA	1300 VA
Output connector type	Hard Wire 3-wire (H N + E) 1
Number of cables	1
Provided equipment	Dust filter Integrated network management Rack mounting hardware Rack Mounting brackets Temperature Probe Web/SNMP Management Card

### Batteries & Runtime

Run Time	<a href="#">View Runtime Graph</a>
Battery Type	External battery system
Included Battery Modules	0
Battery Slots Empty	0
Battery Voltage	48V
Extendable Run Time	0

### General

Topology	Double Conversion Online
Number of power module free slots	0
Number of power module filled slots	0
Redundant	No

### Physical

Height	3.5 in (8.8 cm)
Width	17.008 in (43.2 cm)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Depth	10.2 in (26 cm)
Net Weight	22.05 lb(US) (10 kg)
Mounting preference	No preference
Mounting Mode	Rack-mounted
Two post mountable	0
USB compatible	No

## Input

Input Frequency	40 - 70 Hz auto-sensing
Number of input connectors	1 Hard Wire 3-wire (1PH+N+G)
Efficiency at full load	85...155 V
Maximum Input Current per Phase	21 A
Switching current capacity	30 A
Load power factor	From 0.7 leading to 0.7 lagging without any derating

## Output

Maximum configurable power in VA	1300 VA
Max Configurable Power (Watts)	1300 W
Output Frequency (sync to mains)	50/60 Hz +/- 3 Hz sync to mains
Waveform Type	Sine wave
Efficiency at full load	88 % in battery operation)
Crest factor	3 : 1
Bypass type	Internal Bypass (Automatic and Manual)

## Conformance

Product Certifications	CSA
------------------------	-----

## Environmental

Ambient Air Temperature for Operation	-40...165 °F (-40...74 °C)
Relative Humidity	0...95 % non-condensing
Operating altitude	0...10000 ft
Ambient Air Temperature for Storage	-40...185 °F (-40...85 °C)
Storage Relative Humidity	0...95 % non-condensing
Storage altitude	0...50000 ft (0.0000000000...15240.0000000000 m)
Acoustic level	55 dBA
IP degree of protection	IP20

## Communications & Management

Free slots	0
Alarm	Audible and visible alarms : prioritized by severity

## Surge Protection and Filtering

---

Surge energy rating	432 J
---------------------	-------

---

Let Through Voltage Rating	40 V
----------------------------	------

---

## Ordering and shipping details

---

GTIN	731304341352
------	--------------

---

Country of origin	PH
-------------------	----

---

## Packing Units

---

Unit Type of Package 1	PCE
------------------------	-----

---

Number of Units in Package 1	1
------------------------------	---

---

Package 1 Height	7.3 in (18.6 cm)
------------------	------------------

---

Package 1 Width	14.6 in (37 cm)
-----------------	-----------------

---

Package 1 Length	21.06 in (53.5 cm)
------------------	--------------------

---

Package 1 Weight	26.5 lb(US) (12 kg)
------------------	---------------------

---

## Contractual warranty

---

Warranty	3 years repair or replace
----------	---------------------------

---

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

**Eu Rohs Directive**

Not applicable, out of EU RoHS legal scope

---