

## Storage Solutions Designed for Surveillance

### PROMISE Vess™ A6000



#### Features

##### **Optimized for Surveillance**

Storage appliance optimized for IP video surveillance.

##### **Extensive VMS Support**

Certified/tested with the world's leading video management software.

##### **Midsized to Large-Scale Solutions**

Ideal for more than a hundred full-HD IP cameras, perfect for banking, retail, gaming, manufacturing, and more.

##### **Cost Effective & Scalable**

Integrated solution results in less management overhead; it's easy and economical to expand storage capacity using the Promise JBOD external storage series.

##### **Easy to Administer & Maintain**

Hot swappable drive bays, redundant power supplies, & One Plug Auto Service (OPAS) ensure Vess is incredibly easy to administer and maintain.



#### **Optimized for Video Surveillance**

The Vess A6000 Series storage appliance is specially engineered for IP video surveillance deployment on medium to large scale; ideally suited for surveillance systems in banks, malls, casinos, factories, warehouses, commercial, residential, governmental or private enterprises. The subsystems are capable of continuous recording and playback operation without dropping frames.

#### **Higher Capacity with Better Design**

Two options for large HDD capacity enclosures are available: a 3U 16-drive (Vess A6600) and 4U 24-drive (Vess A6800). Combined with Promise Technology knowhow creates an outstanding combination of performance and reliability for Midsized to Large-Scale surveillance deployments. For larger storage system requirements, the system is cost effective using the Promise JBOD products to extend capacity without the added expense of an additional RAID server.

#### **Reduces Deployment Costs and Complexity**

Support and equipment costs are reduced; without a separate RAID storage unit to manage, there is no longer a need for a server, controller cards, external cables, and a separate storage enclosure. Additionally, the Vess A6000 Series reduces interoperability conflicts caused when integrating different hardware.

#### **SMARTBOOST™ Technology**

PROMISE proprietary SMARTBOOST™ Technology provides the most stable and high performance storage solution for your surveillance system. Performance that can be limited by storage equipment bottlenecks is significantly improved by Promise SMARTBOOST™ Technology. With the optimized software features and FRU hardware design, you have the best stability and storage performance with the best C/P ratio.

#### **Reduce the complexity of Maintenance by OPAS**

One Plug Auto Service (OPAS), a feature unique to Promise's video surveillance solutions, offering user convenience, reduced complexity, lower maintenance cost and streamlined technical support. OPAS enables users to easily collect all the necessary logs and data used by the Promise support team to analyze.

## Technical Specifications



**Vess A6600**



**Vess A6800**

### Model

General Information		
Camera Range <sup>1</sup>	150	200
Form Factor	3U, 19" Rackmount	4U, 19" Rackmount
Number Of Drives	16 Drives (3.5")	24 Drives (3.5")
Drive Type	12Gbs SAS/ 6Gbs SATA @ 3.5", SSD capable @2.5"², Hot Swappable	
# of Controllers	Single	
System Processor	Intel® Core™ i3-7101E/ Intel Xeon E3-1275v5	Intel® Core™ i7-7700
System Memory	8GB Default (Max 64GB)	
I/O Interface	2x Gigabit Ethernet	
Internal Storage (M.2)	128GB	
Storage Expansion	Optional Promise SAS and iSCSI Storage	
Max # of HDDs Supported	Up to 136 drives through iSCSI/SAS JBOD expansion	Up to 144 drives through iSCSI/SAS JBOD expansion
Other Interfaces		
# of USB Ports	4x USB 3.0, 2x USB 2.0	
PCI Express Ports	1x8-lane gen3	
Graphics	D-sub x 1, DVI x 1, HDMI x 1	
Microphone	5x 3.5 mm + 1xSPDIF Audio Jack	
RAID Operational Feature		
RAID Levels	0, 1, 1E, 3, 5, 6, 10 (0+1), 30, 50, 60. Any combination can exist at the same time	
Hot Spares	Multiple global or dedicated hot-spare drives with revertible option	
Max. LUNs per System/Array	256/32	
Software		
OS Supported (64-bit)	Windows 10, WS 2016	
Management Tools	Graphical UI/SNMP via Ethernet, CLI via Ethernet or Graphics, OPAS Service via USB, SDK or API for Integration	
Appliance Mode	Surveillance Optimization @ Arrays in Normal and Degrade	
Event Notification	Email, SNMP, Buzzer, LEDs	
System Information		
AC Input	100 ~ 240 VAC, 60 ~ 50Hz	
Current (Maximum)	8-4A	
Power Supply	Redundant 550W for each power, Hot swappable N+1 Design (80 PLUS certified)	
Controller	Replaceable FRU design	
Temperature	5° ~ 40°C (-40° ~ 60°C non-operational)	
Dimensions (H x W x D)	131 x 503 x 447 mm (5.1 x 19.8 x 17.6 in)	173 x 503 x 447 mm (6.8 x 19.8 x 17.6 in)
Weight	System W/O HDD: 16.11kg System W/ HDD: 26.84kg	System W/O HDD: 19.26 kg System W/ HDD: 35.36 kg
Safety/EMI	CE, FCC, VCCI, RCM, BSMI, KC, (EMI Class A), CB³, cTUVus⁴	
Warranty and Support		
Warranty	3 year limited warranty⁵	
Optional Accessories	Sliding Rail, 4/8/16 GB DDR4 Memory	

<sup>1</sup> The ideal camera range were the test output with fully populated enclosure and 16GB memory under 1080P/30FPS/5Mbps, H.264

<sup>2</sup> For 2.5" SSD/HDD it will need to use different optional carriers.

<sup>3</sup> CB Report is tested according to IEC/EN 60950-1 and IEC/EN 62368-1

<sup>4</sup> cTUVus label marking is tested according to UL 62368-1 and CAN/CSA-C22.2 NO. 62368-1.

<sup>5</sup> Available to purchase the extra 2 years warranty to total 5 years warranty.

\*The final spec may be vary without further notice, please check with Promise website for the latest information

Contact us



© 2018 PROMISE Technology, Inc. All Rights Reserved. PROMISE, the PROMISE logo, VTrak, SmartStor, SuperTrak, FastTrak, VessRAID, Vess, PerfectPATH, PerfectRAID, SATA150, ULTRA133 VTrak S3000, BackTrak, HyperCache, HyperCache-R, HyperCache-W, DeltaScan and GreenRAID are registered or pending trademarks of PROMISE Technology, Inc. in the U.S. and other countries. All other trademarks are the property of their respective owners. Information regarding products, services and offerings may be superseded by subsequent documents and are subject to change without notice. For the latest information and specifications regarding PROMISE Technology, Inc. and any of its offerings or services, please contact your local PROMISE office or the corporate headquarters. Visit [www.promise.com](http://www.promise.com) for more information on PROMISE products. P/N: G6130000000077

2018 August

visit [www.promise.com](http://www.promise.com) for more information on PROMISE products