


## Best Surveillance Storage for SMB/Client Viewer

### Vess A3120



#### Features

##### Optimized for Surveillance

Storage appliance optimized for IP video surveillance.

##### Small Installation & SMB

Ideal for less than 64ch full-HD IP cameras, perfect for banking, retail, prison, hotel, and more.

##### Easy to Administer & Maintain

Hot swappable drive bays, and One Plug Auto Service (OPAS) ensure Vess is easy to administer and maintain.

#### Promise Alliance Partners



#### Optimized for Video Surveillance

PROMISE proprietary SMARTBOOST™ Technology provides the most stable and high performance storage solution for your system. Promise SMARTBOOST™ Technology significantly improves performance that is otherwise limited by storage equipment bottlenecks. SMARTBOOST™ Technology provides the best stability and performance with the best C/P ratio.

#### Storage Appliances + Client Viewer provides Wider Applications

PROMISE Vess A3120 is a Storage Appliance for SMB/small installation video surveillance recording. It includes a Client Viewer for applications that require 24/7 monitoring. It is certified for several VMS for a complete surveillance system solution, using varied software features across multiple VMS.

#### Built-In GPU for better IVA Performance

Vess A3120 speeds up the graphic card performance and other processing using a built-in GPU, Intel Media SDK and thoroughly tested Graphic card implementation. Intelligent Video Analytics (IVA) has placed increased performance demands on surveillance systems; Vess A3120 handles basic recording AND better performing IVA tasks simultaneously.

#### 4K Resolution Streaming Supported

4K camera support is an essential feature for areas that require high resolution camera monitoring. The Vess A3120 features 4K camera streaming for local display to provide high definition imaging of crucial areas.

#### Reduce the complexity of Maintenance by OPAS

One Plug Auto Service (OPAS) is a unique feature of Promise Vess App solutions that provides user convenience, reduces complexity for maintenance, and streamlines technical support. OPAS enables users to collect all the necessary logs and data used by the Promise support team to analyze the status of Vess A-Series Storage appliances.

## Technical Specifications



### Model

General Information	
Camera Range <sup>1</sup>	64
Form Factor	1U, 19" Rackmount
Number Of Drives	4 Drives (3.5")
Drive Type	6Gbs SATA @ 3.5"
# of Controllers	Single
System Processor	Intel® Core™ i3-7101E
System Memory	4GB x 2 Default (Max 32GB)
I/O Interface	2 x Gigabit Ethernet
Internal Storage (M.2)	128GB
Storage Expansion	Optional Vess SAS and iSCSI Storage
Max # of HDDs Supported	Up to 112 drives through iSCSI/SAS JBOD expansion
Other Interfaces	
# of USB Ports	5 x USB 3.0, 2 x USB 2.0
PCI Express Ports	1 x 8-lane Gen3
Graphics	1 x VGA, 1x HDMI, 1x Display Port
Serial Interfaces	1 x Serial Port
Audio I/O	3 x 3.5mm Audio Jack and SPDIF
RAID Operational Feature	
RAID Levels	0, 1, 1E, 3, 5, 6, 10, Any combination can exist at the same time
Hot Spares	Multiple global or dedicated hot-spare drives with revertible option
Max. LUNs per System/Array	256/32
Software	
OS Supported (64-bit)	Windows 10,
Management Tools	Graphical UI/SNMP via Ethernet, CLI/CLU via Ethernet or Graphics, OPAS Service via USB, SDK or API for Integration
Appliance Mode	Surveillance Optimization @ Arrays in Normal and Degrade
Event Notification	Email, SNMP, Buzzer, LEDs
System Information	
AC Input	100 ~ 240 VAC, 47 ~ 63Hz
Current (Maximum)	7A
Power Supply	350W Single ATX
Temperature	5° ~ 40°C (-40° ~ 60°C non-operational)
Dimensions (H x W x D)	44.2 x 446.4 x 398 mm
Weight	System W/O HDD: 6.48 kg System W/ HDD: 9.16 kg
Safety/EMI	CE, FCC, VCCI, RCM,(EMI Class A), cULus
Warranty and Support	
Warranty	3 year limited warranty
Optional Accessories	Sliding Rail, 4/8/16 GB DDR Memory

<sup>1</sup>The ideal camera ranges were output of fully populated enclosure by pure recording and 8GB memory under 30FPS, H.264, 5Mbps Bitrate and 1080P resolution

\*The final spec may vary without further notice, please check with Promise website for the latest information

Contact us



© 2018 PROMISE Technology, Inc. All Rights Reserved. PROMISE, the PROMISE logo, VTrak, SmartStor, SuperTrak, FastTrak, VessRAID, Vess, PerfectPATH, PerfectRAID, SATA150, ULTRA133 VTrak S3000, BackTrak, HyperCache, HyperCache-R, HyperCache-W, DeltaScan and GreenRAID are registered or pending trademarks of PROMISE Technology, Inc. in the U.S. and other countries. All other trademarks are the property of their respective owners. Information regarding products, services and offerings may be superseded by subsequent documents and are subject to change without notice. For the latest information and specifications regarding PROMISE Technology, Inc. and any of its offerings or services, please contact your local PROMISE office or the corporate headquarters.

Visit [www.promise.com](http://www.promise.com) for more information on PROMISE products. P/N: G6130A312000000

2018 August