



ezCinema Tab-Tension Series

Product Brochure



ezCinema Tab-Tension

Elite Screens ezCinema Tab-Tension is a free-standing portable projection screen that is offered now with a tab-tension system. It swiftly pulls up and retracts using a "scissor-backed" free-standing mechanism that requires no extra tools, accessories or effort. This is the perfect "projector screen in a box" for portable presentations on the go.

Screen Material

- MaxWhite® 2 (matte white) 1.1 Gain front projection material
- Wide viewing angle allows viewers to see a clear picture with equal brightness over a full 180° angle.
- ISF Certified for accurate color reproduction
- Black masking borders absorb projector overshoot while enhancing visual contrast
- Black material backing reduces light penetration for enhanced image brightness
- Available in the following diagonal sizes and aspect ratios:
 - 90" / 100" in 4:380" / 92" in 16:9

Design & Operation

- Easy to transport and set up for traveling presentations (carrying bag included)
- Lightweight yet durable aluminum casing protects the screen during transport & storage
- Tab-tension designs keeps screen material flat for ultra/short throw projector presentations
- Folding handle enables a quick and swift pull-up operation
- Scissor-backed design permits screen to deploy and retract effortlessly
- Rotating base feet provide added stability

Quality & Reliability

- GREENGUARD® and GREENGUARD® Gold (UL 2818) Certified for safe air quality emissions
- 2-year limited manufacturer's warranty, and 3-year warranty for ENR-G - Education, Non-profit, Religious and Government/ Military organizations
- Lifetime Tech Support with Elite's Professional Service Team through Email, Web Chat or Call Toll-Free



ezCinema Tab-Tension Series

Model	Screen Diag. & Aspect Ratio	View Height (in)	View Width (in)	N.W. (lbs.)	G.W. (lbs.)	N.W. (Kgs)	G.W. (Kgs)	Packing Dimension (LxHxW)	Gain	Screen Material	Case Color
FT90XWV	90" (4:3)	53.9	72.0	27.0	34.7	12.3	15.8	94.9"x7.1"x7.5"	1.1	MaxWhite® 2	Black
FT100XWV	100" (4:3)	59.8	79.9	29.8	38.1	13.5	17.3	104.7"x7.1"x7.5"	1.1	MaxWhite® 2	Black
FT80XWH	80 (16:9)	39.4	69.7	26.5	34.2	12.0	15.5	92.5"x7.1"x7.5"	1.1	MaxWhite® 2	Black
FT92XWH	92" (16:9)	45.3	79.9	28.9	36.6	13.1	16.6	104.7"x7.1"x7.5"	1.1	MaxWhite® 2	Black

ezCinema Tab-Tension Dimensions Table

Model	Screen Diag. & Aspect Ratio	View Width (A1)	View Height (A2)	Screen Width (B1)	Screen Height (B2)	Bottom Black Border (B3)	Overall Case Length (C1)	Top Bar Length (C2)	Overall Height (C3)	Feet Length	L/R Borders (D1)	D2	Top Black Border (D3)	E1	Distance Between Feet (E2)
FT90XWV	90" (4:3)	72.0	53.9	82.3	93.7	38.6	91.3	90.2	96.9	17.0	1.2	5.1	1.4	22.8	45.7
FT100XWV	100" (4:3)	79.9	59.8	89.8	91.3	29.9	101.2	100.0	94.5	17.0	1.2	5.1	1.4	21.7	57.7
FT80XWH	80 (16:9)	69.7	39.4	79.9	77.2	36.2	89.4	87.8	80.3	17.0	1.2	5.1	1.4	22.0	45.3
FT92XWH	92" (16:9)	79.9	45.3	89.8	83.9	37.0	101.2	100.0	87.0	17.0	1.2	5.1	1.4	21.7	57.7

Unit: inch

Model	Screen Diag. & Aspect Ratio	View Width (A1)	View Height (A2)	Screen Width (B1)	Screen Height (B2)	Bottom Black Border (B3)	Overall Case Length (C1)	Top Bar Length (C2)	Overall Height (C3)	Feet Length	L/R Borders (D1)	D2	Top Black Border (D3)	E1	Distance Between Feet (E2)
FT90XWV	90" (4:3)	1830	1370	2090	2380	980	2320	2290	2460	432	30	130	35	580	1160
FT100XWV	100" (4:3)	2030	1520	2280	2320	760	2570	2540	2400	432	30	130	35	552	1466
FT80XWH	80 (16:9)	1770	1000	2030	1960	920	2270	2230	2040	432	30	130	35	560	1150
FT92XWH	92" (16:9)	2030	1150	2280	2130	940	2570	2540	2210	432	30	130	35	552	1466

Unit: mm

Note: Data Error ±1". The listed measurements are for general reference only. Please contact Elite Screens to verify product design and dimensions before attempting to integrate its products with any structural or furniture modification. Although a manufacturer may offer product advice, it may be taken or disregarded at the integrator's discretion. Elite Screens will not be held responsible or be otherwise liable for faulty installations.

