


YOUR PRODUCT. YOUR IDENTITY.

Choose from one of our 16 colors and personalize by branding with your own logo.



TEMPERATURE MANAGEMENT | Two built in cooling fans help to keep devices from overheating.




EASY ACCESS | Rear doors provide easy access to networking and cabling area.



INTELLIGENT POWER | Power manager continuously analyzes device power requirements, concentrating on devices that require power the most.



INDUSTRIAL GRADE | 5 in. wheels with both directional and brake locking casters, for ultimate maneuverability.



SECURITY | Secure devices with two 3-point locking doors and durable padlock included with the cart.

SPECIFICATIONS

<p>Construction USA-sourced steel Manufactured in Franklin Park, IL</p> <p>Device Compatibility Up to 15 in.</p> <p>Power AC: 120V AC, 12A, 50/60Hz</p> <p>Warranty 7 year electrical and mechanical warranty</p>	<p>Shipment Includes:</p> <ul style="list-style-type: none"> • Link® Cart - Ships fully assembled • Power cord • Programmable combination padlock <p>Safety</p> 
---	--

DIMENSIONS

	MDMLAP24NR	MDMLAP32NR
DEVICE CAPACITY	24 2 shelves	32 2 shelves
CART DIMENSIONS	34.5 x 25 x 43 in.	48 x 24 x 43 in.
SLOT DIMENSIONS	1.4 x 15.5 x 11.9 in.	1.7 x 15.5 x 11.9 in.
WEIGHT	172 lbs.	251 lbs.
ADAPTER ACCESS	Rear Door	

DIMENSIONS ARE EXPRESSED WIDTH X DEPTH X HEIGHT

DESIGNED AND BUILT
IN THE USA

Link® Cart - MDMLAP32NR





