



# HPE ProLiant ML350 Gen10 Server

## ProLiant ML Servers



### What's new

- Support for Intel Xeon Scalable processors – full stack.
- 2600 MT/s HPE DDR4 SmartMemory RDIMM/LRDIMM offering 8, 16, 32, 64 or 128 GB.
- Security through firmware and standard chassis features.
- Re-designed shorter chassis with multiple drive cage options for upgrade, including 8 SFF Express Bay to support NVMe solid

### Overview

Do you need a robust server for your SMB and remote offices? HPE ProLiant ML350 Gen10 server delivers a secure dual-socket tower server with performance, expandability, and proven reliability making it the choice for expanding SMBs, remote offices of larger businesses, and enterprise data centers. HPE ProLiant ML350 Gen10 leverages the Intel® Xeon® Scalable processors with up to 71% [1] performance gain and 27% increase in cores [2], along with the 2666 MT/s HPE DDR4 SmartMemory supports up to 3.0 TB and 11% [3] faster than 2400 MT/s. The shorter re-designed rackable chassis with multiple upgrade options provides flexibility that can expand as

---

state drives.

- Graphic process unit (GPU) support for graphic-intensive applications such as Virtual Desktop Infrastructure (VDI) and machine learning.
- Build a fully functional server with ClearOS™ Software from HPE that is just right for you at no upfront cost. For more information, check the ClearOS link on the right.

your business needs grow. It supports 12 Gb/s SAS, NVMe SSD, embedded 4x1GbE NIC with a broad range of graphics and compute options. Supported by the HPE Pointnext industry-leading service organization, HPE ProLiant ML350 Gen10 server helps you transform to a digital business with more agility and all within your limited IT budget.

## Features

### Perform with Unmatched Versatility

HPE ProLiant ML350 Gen10 supports up to two Intel Xeon Scalable processors, starting from Bronze through Platinum, 4 cores expanding up to 28 core processors offering unparalleled performance.

Up to 24 DIMM slots to support the 2600 MT/s HPE DDR4 SmartMemory, reducing data loss and downtime with the HPE Gen10 technology licensed Fast Fault Tolerance feature while increasing workload performance and power efficiency.

It supports a wide range of solutions from Azure to Docker to ClearOS along with the traditional operating systems.

GPU expansion supports up to four units to accelerate performance in VDI applications and machine learning for financial services, surveillance and security, educational and scientific research, as well as retail and medical imaging.

### Expand When Your Business Needs Grow

HPE ProLiant ML350 Gen10 delivers expandability with a wide range of drive upgrade options. Supporting 8 to 24 SFF or 16 SFF when mixed with optional 8 NVMe PCIe solid state drives, 4 to 12 LFF hot plug or non-hot plug drive options protecting your IT investment in hybrid environment.

Large expansion capacity with (8) PCIe slots, (6) USB ports, 5U rack conversion, and power supply options.

Embedded 4x1GbE and the choice of PCIe standup 1GbE, 10GbE or 25GbE adapters provide you the flexibility of networking bandwidth and fabric so you can scale and adapt to different needs as your business grows.

### Security Innovations

HPE ProLiant ML350 Gen10 is one of the HPE industry standard servers with major firmware anchored directly into the silicon security protection built in across the server lifecycle starting with Silicon Root of Trust.

Millions of lines of firmware code run before server operating system boots. With Runtime Firmware Validation, enabled by HPE iLO Advanced Premium Security Edition, the server firmware is checked every 24 hours verifying validity and credibility of essential system firmware.

Secure Recovery allows server firmware to roll back to the last, known-good state or factory settings after detection of compromised code.

Additional security options are available with Trusted Platform Module (TPM) to prevent unauthorized access to the server and reliably store artifacts used to authenticate the server.

### **Industry Leading Services and Ease of Deployment**

The HPE ProLiant ML350 Gen10 comes with a complete set of HPE Pointnext services, delivering confidence, reducing risk, and helping customers realize agility and stability.

Services from HPE Pointnext simplify all stages of the IT journey. Advisory and Transformation Services professionals understand customer challenges and design an effective solution. Professional Services enable rapid deployment of solutions and Operational Services provide ongoing support.

Services provided under Operational Services include: HPE Flexible Capacity, HPE Datacenter Care, HPE Infrastructure Automation, HPE Campus Care, HPE Proactive Services and multi-vendor coverage.

HPE IT investment solutions help you transform to a digital business with IT economics that align to your business goals.

## Technical specifications

## HPE ProLiant ML350 Gen10 Server

<b>Processor family</b>	Intel® Xeon® Scalable 8100 series Intel® Xeon® Scalable 6100 series Intel® Xeon® Scalable 5100 series Intel® Xeon® Scalable 4100 series Intel® Xeon® Scalable 3100 series
<b>Processor core available</b>	28 or 26 or 24 or 22 or 20 or 18 or 16 or 14 or 12 or 10 or 6 or 8 or 4, depending on model SKU
<b>Processor cache</b>	38.50 MB L3 - 8.25 MB L3, depending on model SKU
<b>Processor speed</b>	3.6 GHz, maximum depending on processor SKU
<b>Power supply type</b>	HPE Flexible Slot Redundant Power Supply modules 500W / 800W / 1600W, depending on model SKU, or HPE Standard 500W Non-Hot-Plug/non-RPS Power Supply
<b>Expansion slots</b>	8-slots (x16, x8, x16, x8, x16, x8, x16, x8) as standard in 2P model. For detail reference QuickSpecs.
<b>Maximum memory</b>	3.0 TB with 128 GB DDR4 DIMM
<b>Memory, standard</b>	16 GB (1 x 16GB) RDIMM or depending on model SKU
<b>Memory slots</b>	24 DIMM slots
<b>Memory type</b>	HPE DDR4 SmartMemory
<b>Memory protection features</b>	Advanced ECC Memory Online Spare Mode Memory Lock Step Mode
<b>Included hard drives</b>	None Ship Standard
<b>System fan features</b>	Standard 2 fans, none-hot-plug Optional 4 additional fans, hot-plug and N+1 redundancy Reference QuickSpecs for config. detail.
<b>Network controller</b>	HPE Ethernet 1Gb 4-port 369i Adapter
<b>Storage controller</b>	1 HPE Smart Array S100i and/or 1 HPE Smart Array P408i-a and/or 1 HPE Smart Array E208i-a, depending on model SKU
<b>Minimum dimensions (H x W x D)</b>	46.25 x 64.8 x 17.4 cm
<b>Weight</b>	21 kg
<b>Infrastructure management</b>	HPE iLO Standard with Intelligent Provisioning (embedded), HPE OneView Standard (requires download) (standard) HPE iLO Advanced, HPE iLO Advanced Premium Security Edition, and HPE OneView Advanced (optional)
<b>Warranty</b>	3/3/3 - Server Warranty includes three years of parts, three years of labor, three years of onsite support coverage. Additional information regarding worldwide limited warranty and technical support is available at: <a href="http://h20564.www2.hp.com/hpsc/wc/public/home">http://h20564.www2.hp.com/hpsc/wc/public/home</a> . Additional HPE support and service coverage for your product can be purchased locally. For information on availability of service upgrades and the cost for these service upgrades, refer to the HPE website at <a href="http://www.hp.com/support">http://www.hp.com/support</a>

**Additional resources**

**QuickSpecs**

[hpe.com/h20195/v2/GetDocument.aspx?](http://hpe.com/h20195/v2/GetDocument.aspx?docname=a00021852enus)

[docname=a00021852enus](http://hpe.com/h20195/v2/GetDocument.aspx?docname=a00021852enus)

**HPE Pointnext**

**HPE Pointnext** leverages our breadth and depth of technical expertise and innovation to help to accelerate digital transformation. A comprehensive portfolio that includes—Advisory, Professional, and Operational Services is designed to help you evolve and grow today and into the future.

**Operational Services**


- **HPE Flexible Capacity** is a new consumption model to manage on-demand capacity, combining the agility and economics of public cloud with the security and performance of on-premises IT.
- **HPE Datacenter Care** offers a tailored operational support solution built on core deliverables. It includes hardware and software support, a team of experts to help personalize deliverables and share best practices, as well as optional building blocks to address specific IT and business needs.
- **HPE Proactive Care** is an integrated set of hardware and software support including an enhanced call experience with start to finish case management helping resolve incidents quickly and keeping IT reliable and stable.
- **HPE Foundation Care** helps when there is a hardware or software problem offering several response levels dependent on IT and business requirements.

**Advisory Services** includes design, strategy, road map, and other services to help enable the digital transformation journey, tuned to IT and business needs. Advisory Services helps customers on their journey to Hybrid IT, Big Data, and the Intelligent Edge.

**Professional Services** helps integrate the new solution with project management, installation and startup, relocation services, and more. We help mitigate risk to the business so there is no interruption when new technology is being integrated in the existing IT environment.

Buy now:

**Call to action url**



Make the right purchase decision. Click here to chat with our presales specialists.



**Sign up for updates**



[1] Intel measurements. Up to 71% performance increase of Intel Xeon Platinum vs. previous generation E5 v4 average performance based on key industry-standard benchmark calculations comparing 2-socket Intel Xeon Platinum 8180 to E5-2699 v4 family processors. Any difference in system hardware or software design or configuration may affect actual performance. May 2017.

[2] Up to 27% performance increase of Intel Xeon Platinum vs. previous generation comparing 2-socket Intel Xeon Platinum 8180 (28 cores) to E5-2699 v4 (22 cores). Calculation 28 cores/22 cores= 1.27 = 27%. May 2017.

[3] The Gen10 2666 MT/s memory speed is 11% faster than that of Gen9 2400 MT/s, enabling faster server performance.

© Copyright 2018 Hewlett Packard Enterprise Development LP. The information contained herein is subject to change without notice. The only warranties for Hewlett Packard Enterprise products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. Hewlett Packard Enterprise shall not be liable for technical or editorial errors or omissions contained herein.

Intel and Intel Xeon are trademarks of Intel Corporation in the U.S. and other countries. ClearOS is either registered trademark or trademark of ClearCenter Corporation in the United States and/or other countries. All other third-party trademark(s) is/are property of their respective owner(s).

Image may differ from actual product  
PSN1010192786USEN, September 23, 2018.