



EonStor GS Family

Enterprise-Class Unified Storage Integrating SAN, NAS and Cloud



For more details

HIGHLIGHTS

UNIFIED STORAGE

- Consolidate SAN, NAS and cloud in a single system to enjoy powerful storage features and simplify deployment and management

EFFICIENCY

- Integrated cloud based storage reduces the cost of deploying applications from the cloud
- EonStor GS family makes efficient use of available bandwidth and greatly speeds up data extend when uploading data to the cloud with its data reduction technology
- With various built-in services including proxy, LDAP, syslog and VPN server to assist enterprises simplify their IT environment deployment.

EXCEPTIONAL COST PERFORMANCE

- High Block/file level Performance, it delivers up to 700K IOPS, 23,000MB/s block and 17,000MB/s CIFS bandwidth.
- Future-proof expansion solution offers ample data capacity of up to 444 drives.
- Comprehensive data services, including SSD Cache and automated storage tiering improve performance and speed up data access.
- Support for all-flash and hybrid configurations provides flexibility of choice to meet your needs.
- Select from a wide range of product series and multiple host options.

The volume of digital data currently being produced is growing at unprecedented rates, in big part due to our increasing demand for unstructured data types such as files, images and videos, which push the boundaries of storage capacity and performance. Because of this, many organizations are making cloud storage, with its cost-effective flexibility and infinite scalability, an integral part of their strategy. Now more than ever, choosing a local storage solution that can easily integrate with cloud services is a must.


EonStor GS family is a unified storage solution that incorporates remote cloud storage into local applications to offer the best of both worlds – unlimited cloud storage and high performance local storage – as well as automatic data lifecycle management, to allow SMBs and SMEs running local SAN/NAS applications to easily and cost-effectively integrate and expand their storage architecture into cloud services.

Powerful All-around High Performance & Efficiency

Based on much improved hardware and firmware, EonStor GS family can handle file level protocols including CIFS/SMB, NFS, AFP and FTP; block level protocols such as Fiber Channel, iSCSI and SAS.

By integrating all of these protocols and harnessing the power of Intel's multicore CPU, EonStor GS family delivers not only outstanding flexibility but also incredible performance in two configurations: all-flash and hybrid. As an all-flash system, it delivers up to 700K IOPS, 23,000MB/s block and 17,000MB/s CIFS bandwidth. Moreover, by offering hybrid features such as SSD Cache, protocol translation between local NAS/SAN and cloud storage services, and automated storage tiering, EonStor GS family guarantees exceptional performance at every level of operation.

This great performance and efficiency can also be found in our cloud storage integration thanks to deduplication and compression features, which ensure the efficient use of bandwidth to effectively extend data to the cloud and lower overall costs.



CLOUD READY

- The EonStor GS can integrate with cloud storage, and data can be optimally allocated between EonStor GS and Cloud through our smart algorithms, so users can enjoy the best performance and the safest storage.
- EonStor GS offers comprehensive cloud integration functions for users to choose from: Cloud Tiering, Cloud Cache and Cloud Backup.
- Support for private and public cloud services enables users to choose the option that best suits their budget or data security requirements

AVAILABILITY & RELIABILITY

- SMB 3.0 failover and multipathing support .
- Dual controllers and non-single-point-of-failure hardware design ensure system continuity in case of faults.
- Cache protection with Super capacitor and Flash to ensure data safety
- IDR support ensures all hard drives are healthy to prevent from rebuild

DATA PROTECTION & SECURITY

- Whether inactive or mid transfer, data is always encrypted to ensure full protection from malicious attacks

SIMPLICITY

- EonOne management interface provides a single control center for system management and resources monitoring


SYMMETRIC ACTIVE-ACTIVE CONTROLLERS

- Symmetric active-active controllers
- Automatically reconnected I/O during path failure

Infinite Storage Capacity on Cloud

One of the key benefits of cloud storage solutions is their unlimited scalability and flexible “scale on demand” model, which allows you to expand your storage capacity as needed, without upfront investment, to fit your capacity requirements as they evolve.

By integrating Intelligent Cloud Gateway Engine and supporting a wide range of both private cloud and public cloud services, including Amazon, Azure, and Google, the EonStor GS offers various cloud functions such as Cloud Tiering, Cloud Cache and Cloud Backup to make the most of cloud's advantages. These functions perfectly combine local and cloud storage, automatically and optimally allocating data, while saving setup and maintenance costs in the process.



Comprehensive Data Protection and Security

As security is of utmost importance when it comes to data storage in the cloud, the EonStor GS family provides AES 256bit Encryption for data-in-flight and data-at-rest, as well as self-encrypting drives (SED) compatibility, ensuring data is always protected from malicious threats. Furthermore, with integrated SSL, links between server and client are also encrypted.

Security threats are by no means the only concern when it comes to safeguarding data. Unexpected disk failures, natural disasters and power outages all up the risk of data loss. EonStor GS family ensures this risk is minimal with its integrated backup functions such as Intelligent Drive Recovery (IDR), snapshot, local replication, remote replication and file-level rsync.

The system supports built-in SMB 3.0 failover and multipathing to handle failures. Also, designed with redundant dual controllers and non-single-point-of-failure hardware components, it ensures business continuity at all times.

Symmetric active-active controllers

EonStor GS supports symmetric active-active controller configuration to minimize administrative effort and boost operation efficiency. Hosts can access the same LUNs simultaneously via both controllers. I/O are more equally distributed across both controllers and all paths, effectively minimizing costly path management time. In the event of a path failure, I/O can automatically continue through the remaining paths with little or no failover.

PHYSICAL SPECIFICATIONS

EonStor GS Series

Specifications (per system)	GS 1000Gen2	GS 2000 GS 2000T ^{*1}	GS 3000 GS 3000T ^{*1}	GS 4000 GS 4000T ^{*1}
Form factor	2U 12-bay	✓	✓	
	2U 24-bay	✓	✓	✓
	2U 25-bay			✓
	3U 16-bay	✓	✓	
	4U 24-bay	✓	✓	✓
	4U 60-bay			✓
Storage controller	Dual-redundant/ Single upgradable to redundant			
Max drives ⁹	444	864	900	864
Max SSD cache pool	1.6TB	3.2TB		3.2TB
Cache backup techniques	Super capacitor + Flash module			
Power supply unit ⁴	Power supply: Two redundant 460W; Voltage and Frequency: 100-240 Vac, 50-60Hz		Power supply: Two redundant 530W;(GS 3060L:1200W) Voltage and Frequency: 100-240 Vac, 50-60Hz	
CPU	2x Intel Avoton (Atom) 4 Core	2x Intel Broadwell-DE (Pentium) 2 Core/ 4 Core	2x Intel Broadwell-DE (Xeon) 4 Core/ 6 Core	
Cache memory ^{2,5}	8GB, 16GB, 32GB, 64GB	8GB, 16GB, 32GB, 64GB, 128GB	8GB, 16GB, 32GB, 64GB, 128GB, 256GB	
Max. number of host board	2	4		4
Onboard SAS expansion ports	2 x 12Gb/s SAS wide ports	2 x 12Gb/s SAS wide ports	4 x 12Gb/s SAS wide ports	
Expansion board ⁷	0	2		2
Onboard converged ports ¹⁵	0	0	0	16
Onboard iSCSI ports (10Gb RJ-45)	0	0	4	0
Onboard iSCSI ports (1Gb RJ-45)	8	8	4	0
Host board ports	2 x 16Gb/s FC ports ¹⁰ 4 x 8Gb/s FC ports ¹⁰ 2 x 10GbE/iSCSI ports (RJ-45) 2/4 x 10GbE/iSCSI ports (SFP+) 4 x 1GbE/iSCSI ports 2 x 12Gb/s SAS ports 4 x 10GbE FCoE ports 2 x 40GbE/iSCSI ports(QSFP)		2/4 x 16Gb/s FC ports ¹⁰ 4 x 8Gb/s FC ports ¹⁰ 2 x 56Gb/s InfiniBand ports ⁸ 4 x 10GbE FCoE ports 2 x 40GbE/iSCSI ports (QSFP) 2 x 10GbE/iSCSI ports (RJ-45) 2/4 x 10GbE/iSCSI ports (SFP+) 4 x 1GbE/iSCSI ports 2 x 12Gb/s SAS ports	
Host board + onboard ports (max.)	16	24	24	32
Max. 8Gb/s FC ports ¹⁰	8	16	16	32
Max. 16Gb/s FC ports ¹⁰	4	16	16	24
Max. 56Gb/s InfiniBand ports	0	8	8	8
Max. 1 GbE/iSCSI ports	16	24	20	16
Max. 10 GbE/iSCSI (SFP+) ports ¹³	8	16	16	32
Max. 10 GbE/iSCSI (RJ45) ports	4	8	12	8
Max. 40GbE/iSCSI (QSFP) ports	0	8	8	8
Max. 10 GbE FCoE ports ¹³	4	16	16	32
Max. 12Gb/s SAS ports	4	8	8	8
Max. number of logical drives	32			
Max. logical drive capacity	512TB			
Configurable stripe size	16KB, 32KB, 64KB, 128KB, 256KB, 512KB, or 1024KB per logical drive			
Configurable write policy	Write-Back or Write-Through per logical drive. This policy can be modified.			
Max. size of pool	2PB			
Max. number of pools	32			
Max. number of volumes (per pool/ per system)	1024			
Max. number of LUNs mappable	4000			
Max. volume size	2PB			
Number of tags reserved for each Host-LUN connection	Up to 256			
Max iSCSI Initiators	832			
File Level	Max. file system size	2PB		
	Max. number of user accounts	20000		
	Max. number of user groups	512		
	Max. number of folder sharing(NFS/CIFS/AFP/FTP)	2048		
	Max. number of rsync jobs	1024		
	Max. number of rsync concurrent processes	64		
Max. number of connections for a folder (NFS/CIFS/AFP/FTP)	2048 per controller			
RAID options	RAID 0, 1 (0+1), 3, 5, 6, 10, 30, 50, 60			
Protocol support	File Level Protocol Block Level Protocol Object Level Protocol	CIFS/ SMB: Version 2.0/3.0, NFS: Version 2/3/4, AFP, FTP, FXP, WebDAV FC, FCoE, iSCSI, SAS Openstack Swift		
Cloud gateway	Support the integration with following cloud providers: Amazon S3, Microsoft Azure, Google Cloud Platform, Alibaba AliCloud			
Green design	<ul style="list-style-type: none"> 80 PLUS power supplies delivering more than 80% energy efficiency Intelligent multi-level drive spin-down 			
Regulatory	<ul style="list-style-type: none"> Electromagnetic Compatibility : CE, BSMI, FCC, KC Safety : UL, BSMI, CB, EAC 			

1. Model name "T" means high IOPS solution
2. GS 4000/3000/2000 Default: DDR4 4GBx2 with ECC per controller. GS 1000 Default: DDR3 4GBx2 with ECC per controller
3. GS 4000/3000/2000 Converged host board supports 4-port 10GbE iSCSI, 4-Port 8 Gb/s FC, 2-port 16Gb/s FC and 4-port 10GbE FCoE. GS 1000 Converged host board supports 4-port 10GbE iSCSI, 4-Port 8Gb/s FC and 2-port 16Gb/s FC.
4. Power is also supplied in redundant mode, allowing full operation with half the resources.
5. 8GB is for single controller models; 256GB is for redundant controller models.
6. GS 4000 onboard converged port supports 4-port 10GbE iSCSI, 4-Port 8 Gb/s FC, 2-port 16Gb/s FC and 4-port 10GbE FCoE

7. The expansion board can only be installed in the HB2 slot and has 2 x 12Gb/s SAS ports only connectable with expansion enclosures.
8. For Linux only, block level only.
9. GS 2000/3000/4000 support expansion board to double expansion enclosure capacity.
10. Supports point-to-point and switch mode.
11. AFP: Supports 255 share folders and 64 connections per folder.

Specifications (per system)	GS 5100	GS 5200
4U Form factor	✓	✓
Storage controller	Dual-redundant	
Max drives ⁹	1680	
Max SSD cache pool	3.2TB	
Cache backup techniques	BBU + Flash module	
Power supply unit ¹⁴	Power supply: Two redundant 1200W Voltage and Frequency: 100-127Vac, 200-240Vac. 47-63Hz	
CPU	2 x Intel Xeon E5 8-core	4 x Intel Xeon E5 8-core
Cache memory ^{22,5}	32GB, 64GB, 128GB, 256GB, 512GB	64GB, 128GB, 256GB, 512GB, 1024GB
Max. number of host board	4	16 ¹¹
Expansion board ¹⁷	4	4
Host board ports	2 x 10GbE/iSCSI ports (RJ-45) 4 x 10GbE/iSCSI ports (SFP+) ¹⁷ 4 x 1GbE/iSCSI ports 4 x 8Gb/s FC ports ^{7,9} 4 x 16Gb/s FC ports ⁹ 2 x 16Gb/s FC ports ^{7,9} 2 x 40GbE/iSCSI ports (QSFP) 2 x 56Gb/s InfiniBand ports ⁹ 4 x 10GbE FCoE ports ⁷	
Max. 8Gb/s FC ports ¹⁰	16	64
Max. 16Gb/s FC ports ¹⁰	16	64
Max. 56Gb/s InfiniBand ports	8	64
Max. 1 GbE/iSCSI ports	16	32
Max. 10 GbE/iSCSI (SFP+) ports ³	16	64
Max. 10 GbE/iSCSI (RJ45) ports	8	32
Max. 40GbE/iSCSI (QSFP) ports	8	64
Max. 10 GbE FCoE ports ³	16	32
Max. 12Gb/s SAS ports (for expansion enclosures)	8	8
Max. number of logical drives	32	
Max. logical drive capacity	512TB	
Configurable stripe size	16KB, 32KB, 64KB, 128KB, 256KB, 512KB, or 1024KB per logical drive	
Configurable write policy	Write-Back or Write-Through per logical drive. This policy can be modified.	
Max. size of pool	2PB	
Max. number of pools	32	
Max. number of volumes (per pool/ per system)	1024	
Max. number of LUNs mappable	4000	
Max. volume size	2PB	
Number of tags reserved for each Host-LUN connection	Up to 256	
Max iSCSI Initiators	832	
Max. file system size	2PB	
Max. number of user accounts	20000	
Max. number of user groups	512	
File Level	2048	
Max. number of folder sharing (NFS/CIFS/AFP ¹⁰ /FTP)	2048	
Max. number of rsync jobs	1024	
Max. number of rsync concurrent processes	64	
Max. number of connections for a folder (NFS/CIFS/AFP ¹⁰ /FTP)	2048 per controller	
RAID options	RAID 0, 1 (0+1), 3, 5, 6, 10, 30, 50, 60	
Protocol support	File Level Protocol CIFS/SMB: Version 2.0/3.0, NFS: Version 2/3/4, AFP, FTP, FXP, WebDAV Block Level Protocol FC, FCoE, iSCSI, SAS Object Level Protocol Openstack Swift	
Cloud gateway	Support the integration with following cloud providers: Amazon S3, Microsoft Azure, Google Cloud Platform, Alibaba AliCloud	
Green design	<ul style="list-style-type: none"> • 80 PLUS power supplies delivering more than 80% energy efficiency • Intelligent multi-level drive spin-down 	
Regulatory	<ul style="list-style-type: none"> • Electromagnetic Compatibility: CE, BSMI, FCC, KC • Safety: UL, BSMI, CB, EAC 	

1. The system supports a maximum of 1680 drives when each controller has two expansion boards and 840 drives when each controller has one expansion board.
 2. Power is also supplied in redundant mode, allowing full operation with half the resources.
 3. GS 5200 default: DDR4 8GB x 8 with ECC, GS 5100 default: DDR4 8GB x 4 with ECC.
 4. The two controllers must have identical slot settings.
 5. The expansion board can only be installed in slots HB9 and Hb10.
 6. For GS 5100, the host boards should be installed in HB7~8. For GS 5200, the host boards should be installed in HB1~8.

7. GS 5000 converged host board supports 4-port 10GbE iSCSI, 4-Port 8 Gb/s FC, 2-port 16Gb/s FC and 4-port 10GbE FCoE.
 8. For Linux only, block level only.
 9. Supports point-to-point and switch mode.
 10. AFP: Supports 255 share folders and 64 connections per folder.
 11. Deafult memory: 64GB (32GB for each controller), it is recommended to install 8 host boards (4 in each controller). To install up to 16 host boards, 128GB is required (64GB each)

GS 5000 Series

Form Factor	4U		
Models with default included Cloud Gateway License ¹	GS 5100RL		GS 5200RL
Supported drives ²	<ul style="list-style-type: none"> • 2.5" 10K/15K RPM SAS HDD • 2.5" SATA/SAS SSD 		
Max. drives number	1680		
Rack Support	4U, 19-inch rackmount		
Dimensions ³	447(W)x175(H)x577mm (D)		
Package Dimensions	591(W)x295(H)x800mm (D)		
Expansion enclosure(JBOD)	JB 3016A JB 3025BA JB 3060/3060L		JB 3024BA JB 3060 JB 3060L

GS 2000/3000/4000/2000T/3000T/4000T Series

Form Factor	2U 12-bay	3U 16-bay	4U 24-bay
Models with default included Cloud Gateway License ¹	Yes	GS 4016RC/SC GS 4016RTC/STC GS 3016RC/SC GS 3016RTC/STC GS 2016RC/SC GS 2016RTC/STC	GS 3024RC/SC GS 3024RTC/STC GS 2024RC/SC GS 2024RTC/STC
	No	GS 4016RCF/SCF GS 4016RTCF/STCF GS 3016RCF/SCF GS 3016RTCF/STCF GS 2016RCF/SCF GS 2016RTCF/STCF	GS 3024RCF/SCF GS 3024RTCF/STCF GS 2024RCF/SCF GS 2024RTCF/STCF
Supported drives ²	<ul style="list-style-type: none"> • 3.5" 7200 RPM NL SAS HDD • 3.5" 7200 RPM SATA HDD • 2.5" 10K/15K RPM SAS HDD • 2.5" SATA/SAS SSD 		
Max. drives number	852	856	864
Rack Support	2U, 19-inch rackmount	3U, 19-inch rackmount	4U, 19-inch rackmount
Dimensions ³	447(W)x88(H)x500(D)mm	447(W)x130(H)x500(D)mm	447(W)x175(H)x500(D)mm
Package Dimensions	780(W)x379(H)x588(D)mm	780(W)x423(H)x588(D)mm	780(W)x465(H)x588(D)mm
Expansion enclosure(JBOD)	JB 3012A JB 3060 JB 3060L	JB 3016A JB 3060 JB 3060L	JB 3016A JB 3060 JB 3060L

GS 2000/3000/4000/2000T/3000T/4000T Series

Form Factor	4U 60-bay	2U 24-bay	2U 25-bay
Models with default included Cloud Gateway License ¹	Yes	GS 4024RCB/SCB GS 4024RTCb/STCB GS 2024RCB/SCB GS 2024RTCB/STCB GS 3024RCB/SCB	GS 3025RCB/SCB GS 3025RTCB/STCB
	No	GS 4024RCBF/SCBF GS 4024RTCBF/STCBF GS 2024RCBF/SCBF GS 2024RTCBF/STCBF GS 3024RCBF/SCBF	GS 3025RCBF/SCBF GS 3025RTCBF/STCBF
Supported drives ²	<ul style="list-style-type: none"> • 3.5" 7200 RPM NL SAS HDD • 3.5" 7200 RPM SATA HDD • 2.5" 10K/15K RPM SAS HDD • 2.5" SATA/SAS SSD 	<ul style="list-style-type: none"> • 2.5" 10K/15K RPM SAS HDD • 2.5" SATA/SAS SSD 	
Max. drives number	900	864	445
Rack Support	4U, 19-inch rackmount	2U, 19-inch rackmount	
Dimensions ³	448(W)x176(H)x840(D)mm	447(W)x88(H)x500(D)mm	
Package Dimensions	620(W)x460(H)x1140(D)mm	780(W)x338(H)x588(D)mm	780(W)x340(H)x588(D)mm
Expansion enclosure(JBOD)	JB 3060L	JB 3024BA JB 3060 JB 3060L	JB 3025B JB 3060L

GS 1000 Gen2 Series

Form Factor	2U 12-bay	3U 16-bay	4U 24-bay	2U 24-bay
Models with default included Cloud Gateway License ¹	Yes	GS 1016R2C/S2C	GS 1024R2C/S2C	GS 1024R2CB/S2CB
	No	GS 1012R2CF/S2CF	GS 1016R2CF/S2CF	GS 1024R2CF/S2CF
Supported drives ²	<ul style="list-style-type: none"> • 2.5" 10K/15K RPM SAS HDD • 2.5" SATA/SAS SSD • 3.5" 7200 RPM NL SAS HDD • 3.5" 7200 RPM SATA HDD 			<ul style="list-style-type: none"> • 2.5" 10K/15K RPM SAS HDD • 2.5" SATA/SAS SSD
Max. drives number	432	436	444	444
Rack Support	2U, 19-inch rackmount	3U, 19-inch rackmount	4U, 19-inch rackmount	2U, 19-inch rackmount
Dimensions ³	447(W)x88(H)x500mm (D)	447(W)x130(H)x500mm (D)	447(W)x175(H)x500mm (D)	447(W)x88(H)x500mm (D)
Package Dimensions	780(W)x379(H)x588mm (D)	780(W)x423(H)x588mm (D)	780(W)x465(H)x588mm (D)	780(W)x338(H)x588mm (D)
Expansion enclosure (JBOD)	JB 3012A JB 3060 JB 3060L	JB 3016A JB 3060 JB 3060L	JB 3016A JB 3060 JB 3060L	JB 3024BA JB 3060 JB 3060L

1. **G**: Single controller **S**: Single controller(upgradable to dual controller) **R**: Redundant controller **T**: High IOPS solution **C**: Super capacitor **L**: One Drawer (for GS 3060); BBU (for GS 5000)
 2. For the latest compatibility details, refer to our official website for the latest EonStor GS Compatibility Matrix.
 3. Without chassis ears/protrusions

Data Service & Support

Data Service

Local Replication ² (Standard license is included by default and advanced is an optional license)	Snapshot	Snapshot images per source volume Snapshot images per system	Standard License: 64 / Advanced License: 256 Standard License: 128 / Advanced License: 4096																
	Volume Copy/Mirror	Replication pairs per source volume Replication pairs per system	Standard License: 4 / Advanced License: 8 Standard License: 16 / Advanced License: 256																
Thin Provisioning (default included)	"Just-in-time" capacity allocation optimizes storage utilization and eliminates allocated but unused storage space																		
Self-encrypting drives	Unique factory encryption secures data plus makes deletion simple and complete																		
Remote Replication(Block level) ⁴	Replication pairs per source volume: 8 Replication pairs per system: 64																		
Remote Replication(File Level)	Rsync with 128-bit SSH encryption between Infortrend EonStor GS, GSe and EonNAS																		
Automated Storage Tiering ¹	Two(2) or four(4) storage tiers based on drive types SSD supports																		
SSD Cache ¹	<ul style="list-style-type: none"> Accelerating data access for random read-intensive environments, such as OLTP Supports up to four SSDs per controller Recommended DIMM capacity for SSD Cache pool: <table border="0"> <tr> <td>DRAM:8GB</td> <td>Max SSD Cache Pool Size: 300GB</td> </tr> <tr> <td>DRAM:16GB</td> <td>Max SSD Cache Pool Size: 400GB</td> </tr> <tr> <td>DRAM:32GB</td> <td>Max SSD Cache Pool Size: 800GB</td> </tr> <tr> <td>DRAM:64GB</td> <td>Max SSD Cache Pool Size: 1,600GB</td> </tr> <tr> <td>DRAM:128GB</td> <td>Max SSD Cache Pool Size: 3,200GB</td> </tr> <tr> <td>DRAM:256GB</td> <td>Max SSD Cache Pool Size: 3,200GB</td> </tr> <tr> <td>DRAM:512GB</td> <td>Max SSD Cache Pool Size: 3,200GB</td> </tr> <tr> <td>DRAM:1024GB</td> <td>Max SSD Cache Pool Size: 3,200GB</td> </tr> </table> 			DRAM:8GB	Max SSD Cache Pool Size: 300GB	DRAM:16GB	Max SSD Cache Pool Size: 400GB	DRAM:32GB	Max SSD Cache Pool Size: 800GB	DRAM:64GB	Max SSD Cache Pool Size: 1,600GB	DRAM:128GB	Max SSD Cache Pool Size: 3,200GB	DRAM:256GB	Max SSD Cache Pool Size: 3,200GB	DRAM:512GB	Max SSD Cache Pool Size: 3,200GB	DRAM:1024GB	Max SSD Cache Pool Size: 3,200GB
DRAM:8GB	Max SSD Cache Pool Size: 300GB																		
DRAM:16GB	Max SSD Cache Pool Size: 400GB																		
DRAM:32GB	Max SSD Cache Pool Size: 800GB																		
DRAM:64GB	Max SSD Cache Pool Size: 1,600GB																		
DRAM:128GB	Max SSD Cache Pool Size: 3,200GB																		
DRAM:256GB	Max SSD Cache Pool Size: 3,200GB																		
DRAM:512GB	Max SSD Cache Pool Size: 3,200GB																		
DRAM:1024GB	Max SSD Cache Pool Size: 3,200GB																		
Cloud-integrated Solution ¹	<ul style="list-style-type: none"> Cloud Cache Cloud Fully Cache Cloud Tiering Cloud Backup 	A copy of frequently accessed data is kept on local storage and all data is also flushed to cloud All data is kept on local storage and all data is also flushed to cloud Frequently accessed data is kept on local storage and infrequently accessed data is migrated to cloud For cloud volumes, its snapshot can be backed up to cloud. When disaster occurs, you can operate disaster recovery based on the latest snapshots.																	
Access right management	<ul style="list-style-type: none"> User account management Quota management 	<ul style="list-style-type: none"> Group management Integration with Window[®] AD and LDAP 	<ul style="list-style-type: none"> Folder management - folder access control Folder encryption with AES 																
Availability and reliability	<ul style="list-style-type: none"> Redundant, hot-swappable hardware modules Trunk group support 	<ul style="list-style-type: none"> CacheSafe technology Device mapper support 	<ul style="list-style-type: none"> Multi-pathing support UPS Antivirus WORM³ 																
Management	<ul style="list-style-type: none"> Web-based EonOne management software Automated cache flush and caching mode operation per enclosure status Module status LED indicators: component presence detection & thermal sensors via I2C bus Storage Resource Management to analyze history records of resource usage Automate repeatable management tasks by flexible workflow 																		
Notification	Email, SNMP traps																		
Applications	File explorer • Proxy server • Syslog server • VPN server • SyncCloud • LDAP server																		
OS support	Microsoft Windows Server 2008 / 2008 R2 / 2012 / 2012 R2 , Microsoft Windows Hyper-V, Red Hat Enterprise, Linux, SUSE Linux Enterprise, Sun Solaris, Mac OS X, VMware, Citrix XenServer, OpenStack Cinder																		
Service and support	Standard service	3-year limited hardware warranty and 8x5 phone, web, and email support (Batteries are covered under warranty for 2 years)																	
	Upgrade/extension options	Replacement part dispatch on the next business day (up to 5 years) Advanced service: 24x7 phone, web, and email support + onsite diagnostics on the next business day (up to 5 years) Premium service: 24x7 phone, web, and email support + onsite diagnostics in 4 hours (up to 5 years) Extended standard service up to 5 years																	
	Infortrend Service Center	Request Support, Knowledge Base, Download Center, Licensing Service, and News																	

1. Optional

2. Available with Standard license and optional advanced license

3. For file level only

4. The maximum number of replication pair per source volume is up to 8, regardless of remote asynchronous/remote synchronous/local volume pairs.

Asia Pacific (Taipei, Taiwan)
Infortrend Technology, Inc.

Tel: +886-2-2226-0126
E-mail : sales.ap@infortrend.com

China (Beijing, China)
Infortrend Technology, Ltd.

Tel: +86-10-6310-6168
E-mail : sales.cn@infortrend.com

Japan (Tokyo, Japan)
Infortrend Japan, Inc.

Tel: +81-3-5730-6551
E-mail : sales.jp@infortrend.com

Americas (Sunnyvale, CA, USA)
Infortrend Corporation

Tel: +1-408-988-5088
E-mail : sales.us@infortrend.com

EMEA (Basingstoke, UK)
Infortrend Europe Ltd.

Tel: +44-1256-305-220
E-mail : sales.eu@infortrend.com

