



## FLEXVIEW SERIES IFP E-LIFT CART, WHITE BASE

|

### FEATURES & BENEFITS

The FlexView Series IFP Cart line is the paragon for interactive flat panel mounting in collaborative settings and signage applications. With a triumvirate of an unmatched systems approach, accessibility for all heights, and artful aesthetics that blend the technology into any space, these carts support exceptional AV experiences like no one else in the industry. The hallmark Middle Atlantic systems approach optimizes for maximum uptime and reliability with premium storage, passive thermal management and power distribution built in. The available height adjustable model provides accessible positioning for any user. Finally, the sleek, slim design delivers the finishing touch with beautiful material options and colors to elevate the aesthetics of carts to a whole new level. Supporting XL displays from 60"-102" with a robust weight capacity of 300lbs, the FlexView Series IFP Cart offering emerges as the optimal solution for seamlessly integrating with large VESA compatible, interactive displays and the 84" Microsoft Surface Hub.

#### Differentiated Features & Benefits:

- Superior capacity mounting for interactive flat panels or displays ranging from 60"-102", with a large, 1200x600 VESA pattern and a robust weight capacity of 300lbs
- Removable, tool-free Lever Lock™ for small device mounting as well as built-in power distribution
- 5 optional finishes in wood and textured, metal HPL colors pair perfectly with the black base for interesting design elements to complement the décor in any space
- Height adjustability from 40" to 60" to center of the display paired with the unimpeded, scalloped base ensures the e-lift design is compliant with ADA standard 803 for reachability, achieving up close display interaction at the desired ergonomic setting for any user
- Anti-collision sensor immediately halts, then reverses motion of display upon encountering an obstruction to avoid pinching fingers or damaging technology
- Finishes correspond with **Pre-configured technical furniture solutions**, providing cohesive designs for any learning or meeting space

#### Standard Features and Benefits:

- Heavy duty, locking 4" casters make mobility an ease while the UL rating ensures the safety of the solution
- Passive thermal management with ventilation in the top
- Simple and quick maintenance with easy-access key locked doors
- Accessory camera mounts and soundbar brackets available as well as leveling feet to quickly convert your cart to a stand

### SPECIFICATIONS

## GENERAL INFO

Finish: HPL

## ASSEMBLY/INSTALLATION INFORMATION

Mounting Hardware Included: Yes

## LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes

Greenguard: Yes

## DIMENSIONS

Mounting Depth Max: 24.46

Usable Depth: 4.3

Usable Width: 29.53

Max Screen Size: 102

Capacity Weight (US): 320

Depth (Metric): 880.62

Depth (US): 34.67

Height (Metric): 1752.09

Height (US): 68.98

Width (Metric): 1201.67

Width (US): 47.31

Product Weight (Metric): 136.08

Product Weight (US): 300

## TECHNICAL INFORMATION

Monitor Mounting: yes

UL Load Capacity: 320

Material: HPL Wood Finish