



# CG279X

## Your advantages



The CG279X is ideal for professionals working in video post-production and pre-printing. It covers up to 98% of the DCI-P3 colour space and up to 99% of the Adobe RGB colour space. The 27" ColorEdge pro-monitor also features a 16-bit 3D look-up-table for precisely controlling colour reproduction. An integrated sensor for hardware calibration ensures precise and automatic adjustment of brightness, white balance and hue curve. Once set up, the CG279X only has to be profiled once a year. The automatic self-calibration with a built-in calibration sensor delivers consistent colours in the meantime. It is possible to work with non-colour-critical applications without interruption while the recalibration is taking place. The integrated Digital Uniformity Equalizer (DUE) guarantees perfect brightness and colour purity on the entire display. The validation function can be used to measure and verify the precision of the monitor at any time. The CG279X is equipped with a USB Type C port, an HDMI port and a DisplayPort port, as well as four USB downstream ports. The new housing design with narrow bezels is particularly elegant.

- ✓ Wide gamut LCD with LED technology, contrast: 1300:1, brightness: 350 cd/m<sup>2</sup>
- ✓ Wide gamut covering 99% of the Adobe RGB colour space and 98% of the DCI-P3 colour space
- ✓ Integrated sensor and fully automatic self-calibration
- ✓ Colour precision ensured via 16-bit look-up-table and up to 10-bit colour reproduction
- ✓ Digital Uniformity Equalizer for perfect luminance distribution and colour purity
- ✓ Temperature-controlled adjustment of colour drift and brightness
- ✓ 3D LUT for exact hardware adjustment of brightness, white balance and gamma
- ✓ USB Type C, DisplayPort, DVI-D and HDMI inputs, four USB outputs
- ✓ Broadcast and film preset: BT.2020, BT.709, DCI, PQ\_DCI, PQ\_BT.2100, HLG\_BT.2100

## Features

### Excellent image quality for sharp images

The screen has an impressive contrast ratio of 1500:1 and a brightness of 350 cd/m<sup>2</sup>. The LCD panel with IPS (wide gamut) technology enables a viewing angle of 178 degrees, ensuring that hues and contrast remain stable for the viewer.



EIZO monitor



Conventional monitor



EIZO monitor



Conventional monitor

### HDR-Gamma-Support

In terms of the HLG and PQ tone curves, the CG279X meets the relevant standards for the display and processing of content in HDR (High Dynamic Range). The optimised gamma curves enable the content to closely resemble natural, human colour perception. Production and post-production professionals can count on a reliable representation with HDR tone curves for editing and colour grading.

### Wide gamut – vivid colours in line with industry standards

The wide-gamut monitor reliably reproduces 98% of the DCI P3 standard used in digital cinema and also supports the Rec. 2020 standard. The CG279X also covers 99% of the Adobe RGB gamut. When images recorded in RAW format are converted to AdobeRGB, the monitor reproduces these with absolute colour fidelity. The EIZO monitor also offers great advantages for printing: It covers almost the entire CMYK gamut (ISO coated and

U.S. Web Coated, for example). You see the later print result on screen and save yourself the proof stage.



Adobe RGB



sRGB

### True Black: Color depth for plastic images

Dark tones often appear faint or washed-out on LCD screens. True Black improves the contrast ratio and dark tones appear deeper – particularly when looking at the monitor from the side.




ColorEdge monitor



Conventional monitor

### 10 bit color depth: a billion colors in the finest grades

Thanks to the 10 bit color display based on a 16 bit LUT, you can utilize a huge color spectrum. This is made possible by the rapid DisplayPort and HDMI connections in combination with the frame rate control. A billion colors at your fingertips simultaneously. That is 64 times more colors than with an 8 bit display. The color gradations are finer and the color differences between adjacent colors are smaller. The enhanced grayscale range is equally important for post-production. With the 10 bit grayscale range activated, between 6% and 14% more grayscales are visible.




8 bit and 10 bit display

## Features

### Precise color rendering thanks to high-resolution 3D look-up table

The 3D LUT provides for the most precise tone value allocation possible and extremely exact color tone rendering, which is shown amongst other things in the gray scale. Brightness levels in relation to the image signal vary from module to module in LCDs and the color mixture (addition) of red, green, and blue also varies. This can be exactly determined and controlled only with the aid of specific measuring devices. EIZO therefore configures all of its monitors in the CG series and its colors and tone value curve in the factory. This results in a consistent color temperature over the entire gray scale. The result: The color reproduction is equal, precise, and reliable across each individual CG279X monitor.



The 3D look-up table also has the following benefits when working with films: Thanks to the ColorNavigation software included, you can emulate the colors of film material. This means you can see how the image will look when it is played. The 3D LUT also improves the additive mixture of color in the monitor (mixture of red, green, and blue). This is a key factor for displaying neutral gray tones correctly.

### Gamut presets for film and video production

Presets for the gamuts DCI P3, Rec. 709 and Rec. 2020 are precisely calibrated in the factory and ensure you work with the correct gamma values. Colour modes for PQ (DCI and Rec. 2100) and HLG (Rec. 2100) for the display of HDR content are also preset as factory defaults. Colour modes on the monitor can be easily changed at the touch of a key, and recalibrated when necessary using ColorNavigator.




Sample display

keys above the control panel. The backlight keys mean that the monitor can even be used in dark environments. This is particularly helpful in dark post-production studios.

### Stable brightness, no color deviation

The alpha and omega for exact image editing: constant brightness and color temperature. Patented electronics balance out brightness fluctuations that may arise due to extended periods of use and increased environmental and operating temperature. Thanks to a built-in thermometer, color deviations caused by fluctuations in room temperature are eliminated and automatically reduced. The color rendering remains absolutely constant over a long period of use, right from the start: because the warm-up time until brightness, color, and tone values have completely stabilized is just three minutes.



### Professional hardware calibration

Good image processing is only possible on well-calibrated monitors. The usual software calibration takes a long time and requires the user to have a certain level of technical expertise. The CG279X is supplied with ColorNavigator 6 hardware calibration software. With ColorNavigator, you can perform calibration quickly, easily, and with excellent colour precision: During calibration, the software directly accesses and saves to the look-up-table in the monitor hardware. You determine the relevant components such as white balance, gamma, brightness, and tone value curve according to your requirements. Calibration then runs automatically based on the default set during production and is therefore unique in terms of precision and speed. This also means that calibration can be performed by users in just a few steps, with no need for in-depth technical knowledge. Because the calibration takes place via the monitor hardware, it is performed without loss and independently of the computer and graphics board. The CG279X can also be smoothly integrated into an existing system.

Learn more about ColorNavigator

### Quick operation – even in dark rooms

Operation is easy and clear. The Button Guide, an overview function on the monitor, will show you the respective function

## Features

### Integrated sensor for self-calibration

An integrated calibration sensor ensures you achieve maximum colour accuracy. The sensor is perfectly aligned to the monitor, takes environmental influences such as light into account, and correlates the centre of the image with the edge of the image. This ensures an even result over the whole monitor.

The sensor is located in the bezel and is only extended when performing measurements. This means that no external calibration device is necessary, and the colour fidelity of the monitor is optimal at all times.

The CG279X is equipped with the latest sensor technology that enables recalibration during normal operation, allowing you to continue working with non-colour-critical applications while the monitor is calibrating. During calibration, the sensor only takes up a small area of the screen and does not present an obstacle. Calibration can also be performed fully automatically at definable times.



It does not get any simpler than this: You can use the ColorNavigator software or the on-screen menu to determine when you want monitor calibration to take place automatically. For example, you can schedule calibration to take place during your lunch break or overnight, with no PC connection required.

### Exact color reproduction ex works

Brightness levels in relation to the image signal vary from module to module in LCDs and therefore the color mixture of red, green, and blue also varies. This can be exactly determined and controlled only with the aid of specific measuring devices. Therefore, EIZO configures the CG279X and its colors and tone curves with

a widespread network of grid points and in each primary color. This results in a consistent color temperature over the entire gray scale.




### Constant tone value over the entire screen

Digital Uniformity Equalizer (DUE) controls all tone values over the entire monitor, pixel by pixel. The effect: color tones appear identical at each point on the screen, without the brightness fluctuations you experience in conventional LCDs. The DUE function also balances out the effects of fluctuations in ambient temperature on the color temperature and brightness. You will enjoy consistently even luminance distribution and perfect color purity. A real plus when touching-up images.

### Ergonomic and stable: the adjustable base


The CG279X has a flexible base to adjust the height, tilt, and rotation and supports both portrait and landscape use. The monitor can be tailored to the user's needs. For example, he can set a sitting position that is ergonomic for him (e.g. lowered to the bottom) or a position to show clients and colleagues something on the screen.



155 mm



Tilt up 35°, tilt down 5°]]°



172°



Rotation 90° (right) clockwise

## Features

### One monitor, many ports

It doesn't get simpler than this: Most end devices, such as PCs, laptops or cameras, can be connected directly to the monitor, thanks to its wide range of interfaces.

The existing USB-C interface can be used for regular upstream data transfers as well as to transmit DisplayPort video signals and audio signals. This means a computer with a USB-C port can be easily connected with just the one cable. A USB-B interface is also available as another upstream port. On the USB downstream side, the CG279X has two USB Type B and two USB Type A ports.

The CG279X supports a wide range of video formats via a DisplayPort input and HDMI. As a result, the monitor can be integrated into PC-based workflows and be used with HDMI feeds.

### Suitable for softproofing

The EIZO CG279X fulfills strict softproof requirements based on the draft ISO/CD 12646 standard. Fogra



Forschungsgesellschaft Druck e.V. came to that conclusion in the course of testing the monitor. The CG279X was therefore awarded the Fogra "FograCert Softproof Monitor" seal of quality. You will therefore be working on a tested, color-proof monitor.

### Protection against glare thanks to the monitor hood

The monitor hood reduces reflection and brightness on the screen and helps protect your eyes. It is easy to attach and reduces the amount of light that hits the screen from above and from the sides.



### Five-year warranty

In addition to the high demands placed on production and materials, EIZO also places the emphasis on quality assurance in all areas.



### Color and brightness warranty

From the date of purchase, the monitor is covered by a colour and brightness guarantee for up to 10,000 hours of monitor usage time. EIZO guarantees a brightness of 120 cd/sqm and a white balance of 5000 K to 6500 K.



# Specification

## General

Item no.	CG279X
Case colors	Black
Solutions	Photography, design & media
Product line	ColorEdge
EAN	4995047053606

## Display

Screen size [in inches]	27
Screen size [in cm]	68.4
Format	16:9
Viewable image size (width x height)	597 x 336
Ideal and recommended resolution	2560 x 1440
Pixel Pitch Horizontal [ mm ]	0.23 x 0.23
Resolution Supported	2560 x 1440, 1920 x 1200, 1600 x 1200, 1680 x 1050, 1280 x 1024, 1024 x 768, 800 x 600, 720 x 400, 640 x 480, 480i (@ 60 Hz), 480p (@ 60 Hz), 1080i (@ 60 Hz), 720p (@ 60 Hz), 1080p (@ 60 Hz), 576i (@ 50 Hz), 576p (@ 50 Hz), 1080i (@ 50 Hz), 720p (@ 50 Hz), 1080p (@ 50 Hz), 1080p (@ 30/25/24 Hz), 2560 x 1440 (@ 30 Hz)
Panel technology	IPS (Wide Gamut)
Max. viewing angle horizontal	178 °
Max. viewing angle vertical	178 °
Number of colors or grayscale	1.07 billion colors (display port, 10 Bit), 1.07 billion colors (HDMI, 10 Bit), 16.7 million colors (display port, 8 Bit), 16.7 million colors (HDMI, 8 Bit), 16.7 million colors (DVI, 8 Bit)
Max. color space	AdobeRGB (>99%), ISO Coated V2 (99%), sRGB (100%), Rec709 (100%), EBU (100%), SMPTE-C (100%), DCI P3 (>98%)
Max. brightness [typical] [in cd/m²]	350
Recommended brightness [in cd/m²]	120
Max. dark room contrast (typical)	1300:1
Typical response time [gray/gray alternation]	13 ms
Max. refresh rate [ in hertz ]	60
Backlight	LED

## Electric data

Power consumption (typical) [ in watt ]	32
Maximum Power Consumption [ in watt ]	111
Power Save Mode [ in watt ]	1
Power Consumption Off [ in watt ]	0
Energy-efficiency class	B
Annual Energy Consumption [ in kWh ]	62

Power Supply	AC 100-120 V / 200-240 V, 50/60 Hz
Power Management	DisplayPort Version 1.2a
Integrated power unit	✓

## Dimensions & Weights

Dimensions [ mm ]	638 x 416-571 x 264
Weight [ in kilograms ]	10.3
Swivel (right/left)	172 °
Incline forward/backward	5 ° / 35 °
Pivot	✓
Height Adjustment Range [ mm ]	155
Hole Spacing	VESA standard 100 x 100 mm

## Certification & Standards

Certification	Softproof-Monitor FograCert, CE, TÜV/GS, TÜV/Ergonomics, CB, cTUVus, FCC-B, CAN ICES-3 (B), VCCI-B, TÜV/S, RCM, EAC, RoHS, WEEE, PSE, TÜV/Color Accuracy (Quick Stability), ISO 9241-307 Pixel fault class 1**
---------------	--

## Features

Hardware calibration of brightness, white point, and gamma correction	✓
Integrated sensor for self-calibration	✓
Scheduler function for self-calibration	✓
Color palette / look-up table	278 trillion color tones / 16 Bit 2x 3D-LUT
HDR Gamma	HLG, PQ curve
Temperature color drift correction	✓
Brightness drift correction	✓
Digital Uniformity Equalizer	✓
Overdrive	✓
No flickering	✓
True Black	✓
3D LUT film emulation (10 bit log)	✓
Safe Area Marker (HDMI)	✓
I/P conversion (HDMI)	✓
Signal range amplifier (HDMI)	✓
Noise suppression (HDMI)	✓
RGB and CMYK color space emulation	✓
Color Blindness Simulation	✓
HDCP Decoder	✓
Gamut Clipping	✓
Preset color/grayscale modes	BT.2020, BT.709, DCI, PQ DCI, PQ BT.2100, HLG BT.2100, Adobe RGB, sRGB, Calibration, 1x free mode for user selection
OSD language	de, en, fr, es, it, se, ja, zh
Adjustment options	Brightness, Color temperature, Gamma, Colour gamut, Color saturation, Clipping, Gain, HLG system gamma, Picture expansion, Signal color system, Signal range, HDMI settings (noise reduction, film recognition), Signal format, Power save, Alignment, OSD information, Usage time, Indicator, Signal input, Key lock, Safe Area Marker, Safe Area Size, Aspect Marker, Aspect Settings, Border colour, XYZ Format, REC709 gamut warning, Media Emulation, DUE priority, Luminance Warning, Custom key, Reset
Button Guide	✓
Signal inputs	USB Type-C (DisplayPort Alt Mode, HDCP 1.3), DisplayPort (HDCP 1.3), HDMI (Deep Color, HDCP 1.4), DVI-D (HDCP 1.4)
USB Typ-C	✓
Video Signal	DisplayPort, HDMI (YUV, RGB)
Frequency	HDMI: 15-78 kHz/23-61 Hz Display Port: 26-89 kHz/23-61 Hz
Input Signal Identification	✓
USB hub	1 Up-Stream USB-C (15W Power delivery) / 1 Up-Stream USB-B / 2 Down-Stream USB-A, Rev. 3.1 Gen 1 / 2 Down-Stream USB-A, Rev. 2.0

## Software & Accessories

Accompanying software and other accessories are available for download or on a CD	ColorNavigator, ColorNavigator Network (upon request), Quick Color Match
Additional Supply	Power cord, USB, and signal cable (USB Type-C), Signal cable DisplayPort - DisplayPort, Quick guide, Calibration certificate, Light protection cover
Accessory	EIZO ScreenCleaner (for the best possible clean without scratching the monitor), HH200HS-K (HDMI (High Definition Multimedia Interface) cable to transfer digital video and audio signals.)

## Warranty

Warranty and service	5 years including on-site replacement service*
----------------------	--

## Terms

\* ) The length of the warranty for the LCD module is five years from the date of purchase or 30,000 operating hours, depending on which happens sooner.

\*\*) Zero pixel error guarantee for completely lit sub-pixels (partial pixels ISO 9241-307). Valid: six months from the purchase date.