

32-Port Cat5 KVM over IP Switch with Virtual Media - 1 Local & 1 Remote User, 1U Rack-Mount, TAA

MODEL NUMBER: **B064-032-01-IPG**



Cat5 KVM switch directly controls up to 32 computers and/or servers, including blade servers, at the same time.

Features

Control As Many As 32 Computers or Servers from Anywhere in the World

This NetDirector® Cat5 KVM switch offers BIOS-level access to multiple computers and servers in a complex, demanding IT environment. The B064-032-01-IPG provides complete control of up to 32 computers and/or servers directly, including blade servers, from a single monitor, USB keyboard and USB mouse. Dual redundant power supplies confirm the unit will continue running in the event one power supply fails, ensuring 24/7 reliability. A Laptop USB Console (LUC) port allows direct connection of a laptop for easy console operation of the KVM switch.

All-in-One Network Management for Critical Systems

The B064-032-01-IPG offers a comprehensive, cost-effective network management solution that installs in 1U of space in an EIA-standard 19-inch rack using the included hardware. No server-resident software is required, so server performance and reliability are never compromised. Flash-upgradable firmware over an Ethernet network fine-tunes compatibility with emerging standards.

Supports All Major Operating Systems and Most Web Browsers

The B064-032-01-IPG supports all major server platforms and VT100-based serial devices. Because compatibility is based on common hardware standards, rather than system software dependencies, almost any platform can be accommodated. Supported web browsers for users who log in remotely include Internet Explorer, Firefox, Mozilla, Safari, Opera and Netscape Navigator.

Simple Network Control That Gives You More Flexibility

This Cat5 KVM switch is designed to ease multi-server management in data centers, server rooms and other high-density environments. Built-in IP capability allows up to two users—one local and one remote—to access the network independently and simultaneously. An optional dial-in connection (modem port) is provided to ensure access in situations when the KVM switch is not available over the primary network. You may also select a connected computer using on-console pushbuttons, GUI (graphical user interface), OSD (on-screen display) or keyboard hotkey commands. An LED per KVM port indicates when a computer is connected to the port, when it is powered on and when it is selected.

High-Resolution On-Screen Display Offers Multi-Language Support

The advanced OSD with high-resolution video up to 1920 x 1200 (at 60 Hz) with 24-bit color depth

Highlights

- Up to 2 users (1 local, 1 remote) can control up to 32 computers/servers simultaneously
- Virtual Media allows access to remote storage, including DVD/CD drives and flash drives
- Dual redundant C14 power inlets keep the unit running in case one power supply fails
- Dedicated LUC port connects directly to a laptop for easy console operation
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Applications

- Maintain access to distant or difficult-to-access equipment from a more convenient location for one remote user and one local user
- Provide support and service to outsourced hardware
- Control multiple computers on a manufacturing line
- Keep mission-critical servers in a data center up and running 24/7

System Requirements

- Any major operating system
- Internet Explorer, Firefox, Mozilla, Safari, Opera or Netscape Navigator web browser
- Connected computers:



provides a GUI with management tools, including custom port labeling, auto-scanning and panel array mode. The OSD may be set to display in English, German, Russian, Japanese, traditional Chinese and simplified Chinese.

Allows Connection of Either PS/2 or USB Keyboard and Mouse

PS/2 and USB console ports are included. Only one keyboard/mouse combination may be connected at a time.

Supports Both IPv4 and IPv6 Addresses

The B064-032-01-IPG supports IPv4, Link Local IPv6 Address and IPv6 Stateless Autoconfiguration protocols. You may set the IP address manually or have it automatically assigned via DHCP server (the default method).

Heightened Security of Every Connection

The B064-032-01-IPG offers three levels of password protection (super administrator, administrator and user) to prevent unauthorized persons from gaining access to connected servers/computers. Remote authentication support is provided via RADIUS, LDAP, LDAPS and Active Directory. The B064-032-01-IPG also incorporates advanced encryption technologies: 1024-bit RSA, 56-bit DES, 256-bit AES and 128-bit SSL. It also supports high-grade FIPS 140-2 level 1 security standards.

Network-Wide Storage Media Access

Virtual Media capability allows any computer connected to the KVM via a B055-001-USB-V2, B055-001-UDP, B055-001-UDV or B055-001-UHD server interface unit to access DVD/CD drives, flash drives and other storage media from a remote computer, as if it were directly connected. This allows administrators to perform file transfers, install software and perform diagnostics across a network. Three USB ports are provided on the front panel for use with Virtual Media or USB peripheral devices.

Energy-Efficient Operation Prolongs the KVM's Lifespan

Temperature sensors automatically increase or decrease the speed of the unit's fans as necessary to ensure efficient cooling. This decreases the amount of energy consumed, while prolonging the life of the fans and KVM switch.

Free Management Software Included

Free NetDirector-AXS management software is available for accessing and controlling the B064-032-01-IPG. From a single interface, you can remotely access server ports and manage KVM settings. You can install this software from the included CD or download it at www.tripplite.com/support.

TAA-Compliant for GSA Schedule Purchases

The B064-032-01-IPG is compliant with the Federal Trade Agreements Act (TAA), which makes it eligible for GSA (General Services Administration) Schedule and other federal procurement contracts.

DisplayPort, DVI, VGA or HDMI port and USB or PS/2 keyboard/mouse port

- Remote console computers (web browser): 128-bit SSL encryption and Sun JRE v6 Update 3 or higher
- Remote console computers (non-browser Windows Client): Windows w/DirectX 7.0 or higher
- Remote console computers (Java Client): Sun JRE v.6 Update 3 or higher

Package Includes

- B064-032-01-IPG 32-Port IP KVM Switch
- (2) C5 to NEMA 5-15P detachable power cords
- RJ45 to DB9 adapter (F/M)
- USB-PS/2 combo console cable kit
- Grounding wire
- Foot pads
- Rack-mounting hardware
- CD w/owner's manual, Quick Start Guide and device files
- Quick Start Guide

Specifications

OVERVIEW	
UPC Code	037332236340
Max CPU	32
INPUT	
Voltage Compatibility (VAC)	100; 110; 120; 125; 127; 200; 208; 220; 230; 240



Input Frequency	50/60Hz
Input Current	1A
Power Input Receptacle	IEC-320-C14
Redundancy - Dual Power Inputs	Yes
USER INTERFACE, ALERTS & CONTROLS	
LED Indicators	PORT LEDS- GREEN (ONLINE), RED (SELECTED AND OFFLINE), ORANGE (SELECTED AND ONLINE); POWER 1 & 2 LEDS- BLUE; LINK 1 & 2 LEDS- RED (10MBPS), ORANGE (100MBPS), GREEN (1000MBPS)
PHYSICAL	
Unit Packaging Type	Box
Unit Dimensions (hwd / in.)	1.72 x 17.06 x 15.98
Unit Weight (lbs.)	7.75
Unit Weight (kg)	3.52
Material of Construction	Metal
Color	Black
Rackmountable	Yes
ENVIRONMENTAL	
Operating Temperature Range	32 to 122°F (0 to 50°C)
Storage Temperature Range	-4 to 140°F (-20 to 60°C)
Relative Humidity	0% - 80% RH, Non-Condensing
COMMUNICATIONS	
IP Remote Access	Yes
CONNECTIONS	
Ports	32
Computer/Server Ports	(x32) RJ45
PC/Server Connections	DVI; USB; VGA
Side A - Connector 1	(3) USB A (FEMALE)
Side A - Connector 2	(2) 3.5MM (FEMALE)
Side A - Connector 3	USB MINI-B 5-PIN (FEMALE)
Side B - Connector 1	(35) RJ45 (FEMALE)
Computer Keyboard and Mouse Interface	USB
Computer Monitor Interface	DVI-D Dual-Link; HD15
Console Keyboard and Mouse Interface	PS/2; USB



Console Monitor Interface	HD15
PORT EXPANSION	
Max Distance (Between any 2 Units)	164ft (50m)
Max Number of Ports (Entire Chain)	512
FEATURES & SPECIFICATIONS	
Autoscan (Y,N)	Y
Autoscan Duration	User-definable from 1 to 255 seconds; default of 5 seconds
Number of Users	2
NIAP-Certified Secure	No
On-Screen Display (OSD)	Yes
Port Selection	GUI; Hotkey; OSD; Pushbutton
Max Supported Video Resolution	1920 x 1200 @60 Hz
Driver Required	No
Authentication Supported	LDAP; LDAPS; RADIUS
Cat5 KVM Switch	Yes
Recommended Category Cable	Cat5/5e cables
Technology	Cat5/5e; PS/2; VGA/SVGA
REMOTE ACCESS	
Modem Port	Yes
CERTIFICATIONS	
Certifications	Tested to FCC, RoHS, REACH
WARRANTY	
Product Warranty Period (Worldwide)	3-year limited warranty

© 2019 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>