

NEC Infrared Touch Screen Displays



Advanced Interactive Collaboration Solution

The TSi touch interface is an Infrared (IR) based solution, which allows for a high accuracy interactive experience. The usage of IR technology allows for virtually any input to be detected (pen/stylus, user's fingers, palms, gloved fingers). The TSi touch interface is a full steel chassis integrated with anti-reflective tempered cover glass, which increases durability and optical clarity, while protecting the display.



Multi-Touch Screen

True multi-touch support with up to ten simultaneous touch points for all major operating systems



Ultra-Fast Response Time

Allows for split second reactions between touch point and screen. Rapid and smooth touch response



Superior Design

Full steel chassis combined with anti-reflective tempered glass provides additional protection to the LCD panel



Branding Free

Branding/logo free, not to divert attention from your brand and messaging



24/7 Commercial Grade Display

Commercial grade display with around the clock functionality



Easy to Clean

Water and dust resistant



HID Compliant




Maximum compatibility with numerous operating systems, plug-and-play



Customizable

Custom colors silk screening, and logos available

Solution Sizes Available



Specification	43"	50"	55"
Display Compatible	C431	C501	C551
Part Number	TSI43NNAFTACRZZ	TSI50NNAHTACRZZ	TSI55NNAJTACRZZ
Protective Glass	1/8" Anti-Reflective Cover Glass		
Viewing Angle	178x178 degrees		
Contrast Ratio	4000:1		
Touch Technology	Infrared		
Touch Points	10		
Response Time	16ms		
Touch Accuracy	+/- 1.5mm (Over 99% Area)		
Interface	Type A USB		
Communication	USB 2.0		
Power Supply Mode	Single USB connection (5v, 1A)		
Duty Cycle	24/7		
Panel Technology	AMVA3		
Aspect Ratio	16:9		
Native Resolution	1920x1080		
Brightness	400 nit		
Orientation	Portrait / Landscape / Face Up / Face Down		
VESA Configuration	300 x 300mm (M6 x 4-hole)		
Width/Height/Depth Including Monitor	39.58" x 23.34" x 2.41"	45.59" x 26.69" x 2.46"	50.41" x 29.62" x 2.64"
Weight Without Monitor	21.61 lbs	26.02 lbs	32.41 lbs
OS Support	Windows, Google Chrome, Android, Mac, Linux		