Cyber Power

OL6KRTHD SMART APP ONLINE UPS SERIES

Safeguard mission-critical servers, applications, and network equipment with this space saving design and double-conversion power protection

The CyberPower Smart App Online OL6KRTHD high-density design offers more power in less space. In fact, it can be configured into 2U of rack space or as a tower, compared to 3U and 4U for similar competitive UPS models – giving you more room to grow. The OL6KRTHD features double-conversion topology for seamless power protection and a pre-installed RMCARD205.

For monitoring, this UPS offers a new state-of-the-art, multi-function, color matrix LCD screen that is simple to set up and easy to use. The color-coded alerts provide clear status of the UPS and the screen orientation rotates automatically when placed into a tower configuration.

The OL6KRTHD ensures maximum efficiency and capacity output with a Power Factor rating (PF) of 1. The energy-saving GreenPower UPS[™] ECO Mode enables up to 96% efficiency while reducing power consumption and thermal dissipation. The variable 7-speed fan provides automatic thermal management, based on power load, to reduce noise.

The optional BP144VL2U01 Extended Battery Module (EBM) expands runtime and up to ten EBMs can be connected in a daisy-chain to the UPS for more backup power. Plus, it's all backed by a three-year warranty (including batteries) and a \$300,000 Connected Equipment Guarantee.

Typical Applications

- Core Network Equipment
- Hyperconverged Infrastructure (HCI)
- Server Rooms
- Server Virtualization Infrastructures
- Storage Systems
- VoIP Infrastructure

Features

- 6,000VA / 6,000W
- 2U Rack Size
- Double-conversion Topology
- Sine Wave Output
- Output: 200-240 ±2%
- Hardwire with NEMA L6-30P Plug Power Cord Option
- Outlets: 2 x NEMA L6-20R, 2 x NEMA L6-30R
- USB, Serial, SNMP, EPO ports
- Management software: PowerPanel® Business Edition
- GreenPower UPS™ Eco Power Mode
- Three-Years Limited Warranty

SPECIFICATIONS

GENERAL	
Energy Saving	Yes - ECO Mode Efficiency > 96%
Energy Star Certified	Yes
UPS Topology	Double Conversion
INPUT	
Input Voltage	200-240 VAC
Voltage Range	120 V to 139 V, 0% to 25% load 140 V to 159 V, 0% to 50% load 160 V to 179 V, 0% to 75% load 180 V to 280 V, 0% to 100% load
Frequency Range	40 Hz to 70 Hz (auto-sensing)
Input Power Factor	0.99
Cold Start	Yes

Yes
Hardwire with NEMA L6-30P Power Cord Option
10
3
6,000 (6 kVA) > w/ Hardwire Terminal 5,400 (5.4 kVA) - 240VAC > w/ Power cord 5,400 (5.4 kVA) - 230VAC > w/ Power cord 5,100 (5.1 kVA) - 220VAC > w/ Power cord 4,850 (4.85 kVA) - 208VAC > w/ Power cord 4,500 (4.5 kVA) - 200VAC > w/ Power cord
6,000 (6 kW) > w/ Hardwire Terminal 5,400 (5.4 kW) - 240VAC > w/ Power cord 5,400 (5.4 kW) - 230VAC > w/ Power cord 5,100 (5.1 kW) - 220VAC > w/ Power cord 4,850 (4.85 kW) - 208VAC > w/ Power cord 4,500 (4.5 kW) - 200VAC > w/ Power cord

OL6KRTHD SMART APP ONLINE UPS SYSTEM



SPECIFICATIONS CONT.

OUTPUT CONT.	
Rated Power Factor	1
Waveform (Battery Mode)	Sine wave
Nominal Voltage (Battery Mode)	200, 208, 220, 230, 240 V ±2% (configurable)
Output Frequency	50/60 Hz ±0.25 Hz (auto-sensing/configurable)
ECO Mode Bypass Voltage Range	±10%, ±15% (configurable)
Harmonic Distortion	THD <3% at linear load, <5% at non-linear load
Crest Factor	3:1
Outlets - Total	4
Outlets - Type	(2) NEMA L6-20R, (2) NEMA L6-30R
Overload Protection	Line Mode: 105% to 125% load for 1 min 126% to 150% load for 10 s
	Battery Mode: 105% to 130% load for 10 s 131% to 150% load for 2 s
Short Circuit Protection	UPS Output Cut off Immediately or Input Fuse / Circuit Breaker Protection
Bypass	Internal Bypass (Automatic and Manual)
Transfer Time	0 ms
BATTERY	
Runtime at Half Load	6.2 min
Runtime at Full Load	2.4 min
Battery Type	Sealed lead acid
Battery Size	12 V/6 Ah
Battery Quantity	12
User Replaceable	Yes - Qualified Personnel Only
Replacement Battery	(1) RB1260X12
Replacement Battery Hot Swappable	(1) RB1260X12 Yes
Hot Swappable	Yes
Hot Swappable Battery Equalization Technology	Yes

SURGE PROTECTION & FILTERING

Surge Protection	2430 Joules, IEC 61000-4-5 Level 3	
EMI/RFI Filtration	Yes	
MANAGEMENT & COM	MUNICATION	
LCD Control Panel	Multi-Function Color TFT-LCD Readout that Supports: (15) Types of UPS status, (7) Types of Controls, (20) Types of Set Up, (12) Event Logs, (11) Types of About, (4) Types of Diagnostics	
Rotatable LCD Control Panel Option	Yes	
Removable LCD Control Panel Option	No	
HID Compliant USB Port	Yes	
Serial Port	Yes	
Emergency Power Off (EPO) Port	Yes	
Dry Contacts	No	
Management Cable	USB Cable, Serial Cable	
LED Indicators	Power On (White)	
Audible Alarms	Battery Mode, Battery Low, Overload, UPS Fault	
Software	PowerPanel® Business Edition	
Expansion Slot	Yes - RMCARD205 pre-installed	
PHYSICAL		
Form Factor	Rack / Tower convertible (rotatable LCD)	
Enclosure Construction	Steel	
Front Panel Color	Black	
Rack Mounting Hardware	Included	
Rack Units	2U	
PHYSICAL DIMENSIONS		
Weight (lb)	92.4	
Weight (kg)	41.91	
Dimensions - (WxHxD) (in)	17 x 3.4 x 28.3	
Dimensions - (WxHxD) (mm)	432 x 86 x 719	
Rail Depth - Max. Mounting (in)	36.02	

©2022 Cyber Power Systems (USA), Inc. CyberPower is a registered trademark and brand of Cyber Power Systems (USA), Inc. All rights reserved. All other trademarks are the property of their respective owners. CyberPower reserves the right to change, without notice, marketing programs, product offerings and specifications. www.cyberpowersystems.com

OL6KRTHD SMART APP ONLINE UPS SYSTEM



SPECIFICATIONS CONT.

SHIPPING DIMENSIONS	
Dimensions (WxHxD, in)	23.6 x 8.5 x 43.3
Dimensions (WxHxD, mm)	599.44 x 215.9 x 1099.82
Weight (lb)	114.6
Weight (kg)	51.98
ENVIRONMENTAL	
Operating Temperature	32 °F to 104 °F (0 °C to 40 °C)
Operating Relative Humidity	0% to 90% non-condensing
Operating Elevation	0 ft to 10,000 ft (0 to 3,000 m)
Storage Temperature	-4 °F to 113 °F (-20 °C to 45 °C)
Storage Relative Humidity	0% to 95% non-condensing
Storage Elevation	0 ft to 50,000 ft (0 m to 15,000 m)
UPS Online Thermal Dissipation (100% load)	1613 BTU/h
Audible noise at 1m from surface of unit	43 dBA to 66 dBA (0% to 100% load)

CERTIFICATIONS		
Safety	UL 1778 5th Ed. CSA C22.2 NO.107.3-05 FCC Part 15 Class A	
Environmental	RoHS Compliant	
WARRANTY		
Product Warranty	3 Years Limited	
Extended 2-Year Warranty	Optional WEXT5YR-U20B	
Connected Equipment Guarantee	Lifetime	
CEG Amount	\$300,000	