# Cyber**Power** PR3000RT2UN SMART APP SINEWAVE UPS

### Protect corporate and network servers, telecom installations, and VoIP systems.

The PR3000RT2UN is a Smart App Sinewave rack/tower convertible UPS with line-interactive topology, surge protection, and battery backup. CyberPower's Smart App Sinewave series creates a sine wave output devoid of power gaps which could cause unexpected shutdowns of sensitive equipment.

The Smart App Sinewave PR3000RT2UN improves battery life through battery equalization technology and Automatic Voltage Regulation (AVR), which corrects minor power fluctuations without switching to battery power. The enhanced chassis design with an easy-to-access toolless front panel, captive screws for battery panel access, and color-coded rear panel make battery changes and installations simple and fast. The PR3000RT2UN also has an innovative LCD panel that rotates 90°, tilts for a better viewing angle, and provides information on 47 different settings including UPS stats, UPS setup and control management, and testing options. This model includes pre-installed RMCARD205 network management card for remote management and control via a standard web browser or network management system.

With a \$400,000 connected equipment guarantee and a three-year warranty, you can trust CyberPower's commitment to the quality of the PR3000RT2UN.

#### TYPICAL APPLICATIONS

- Department Servers
- Storage Devices
- VoIP Installations
- Network Devices
- Corporate Servers
- Telecom Installations

#### FEATURES

- 3000VA/3000W
- Line-Interactive Topology
- GreenPower UPS<sup>™</sup>
- Communication: USB, Serial SNMP, Relay, EPO
- PowerPanel<sup>®</sup> Business Edition Management Software
- Remote Management
- Energy Star<sup>®</sup> Certified
- Three Year Warranty

## **SPECIFICATIONS**

GENERAL		
UPS Topology	Line-Interactive	
Energy Saving	GreenPower UPS™ Bypass Technology	
ENERGY STAR® Certified	Yes	
Active PFC Compatible	Yes	
INPUT		
Voltage	100-120 VAC	
Frequency	47 - 63 Hz	
Input Voltage Range	75 - 149 VAC	
Plug Type	NEMA 5-30 P	
Plug Style	Right Angle, 0° Offset	
Cord Length	10 FT	

OUPUT		
VA	3000	
Watts	3000	
Automatic Voltage Regulation	Double Boost, Single Buck	
On Battery Voltage	100/110/120 ± 5%	
On Battery Frequency	50/60 Hz +/- 1%	
On Battery Waveform	Sine Wave	
Outlets - Total	9	
Outlet Type	8 x NEMA 5-20R; 1 x NEMA L5-30R	
Outlets - Critical Load	4	
Outlets - Battery & Surge Protected	9	



## PR3000RT2UN SMART APP SINEWAVE UPS





## **SPECIFICATIONS CONT.**

OUTPUT CONT.		
Rated Power Factor	1	
Overload Protection	Internal Circuitry Limiting/ Circuit Breaker	
Transfer Time	4 ms typical	
BATTERY		
Runtime at Half Load (min)	13.5	
Runtime at Full Load (min)	4.5	
Battery Type	Sealed Lead-Acid	
Battery Size	12V / 9AH	
Hot-Swappable	Yes	
Replacement Battery	RB1290X4J	
Battery Quantity	4	
User Replaceable	Yes	
Typical Recharge Time	3 hrs	
External Battery Pack Option	Νο	
SURGE PROTECTION &	FILTERING	
Network Protection RJ45	1 - In, 1 - Out	
Surge Suppression	2430	
EMI/RFI Filtration	Yes	
MANAGEMENT & COMM	IUNICATIONS	
Multifunction LCD Panel	47 Settings (27 Setup and Control Items + 20 Status Updates and Log Menus)	
HID Compliant USB Port	Yes	
Serial Port	Yes	
EPO Port	Yes	
Contact Closure	Yes	
Management Cable	USB Cable, EPO Cable	

#### MANAGEMENT & COMMUNICATIONS

LED Indicators	Power On, Line Mode, Battery Mode, Fault, Night Mode, Wiring Fault
Audible Alarms	Battery Mode, Low Battery, Overload, Overcharge, Overheat
Software	PowerPanel <sup>®</sup> Business Edition
SNMP/HTTP Remote Monitoring	Yes - pre-installed RMCARD205
PHYSICAL	
Rack Size	2U
Form Factor	Rack/Tower
Dimensions (WxHxD) (in.)	17.1 x 3.4 x 19.7
Weight (lbs.)	76.5
Shipping Dimensions (WxHxD) (in.)	22.1 × 10.8 × 24.4
Shipping Weight (lbs.)	84.4
ENVIRONMENTAL	
Operating Temperature	32° F to 104° F (0° C to 40° C)
Operating Relative Humidity	0 - 95% (Non-Condensing)
Storage Temperature	5° F to 113° F (-15° C to 45° C)
Maximum Operating Elevation	10,000 ft (3,000 m)
Maximum Storage Elevation	50,000 ft (15,000 m)
Online Thermal Dissipation	120.8 BTU/hr
CERTIFICATIONS	
Safety	UL1778, VCCI, FCC Class A
Environmental	RoHS Compliant
WARRANTY	
Product Warranty	Three-Years Limited
Connected Equipment Guarantee	Lifetime
CEG Amount	\$400,000