

Product data sheet

Specifications

Split Unit Ceiling Mount Evaporator 6KW 208-230/1/60



UCF0341I

⚠ Discontinued on: Oct 9, 2023

⚠ To be end-of-service on: Sep 19, 2030

⚠ Discontinued - Service only

Overview

Lead Time Special Order - Call for Quoted Lead Times

Main

Main Input Voltage 208 V
230 V

Communication Port Protocol Modbus

Provided Equipment Installation guide
Operations and maintenance manual

General

Compressor Type Scroll

Air Discharge Patterns Horizontal

Intake Air Rear Return

Air Flow 1088 ft³/min (513.48 l/s)

Piping Material Copper

Fluid Connection Type SWT

Physical

Color White

Height 12.99 in (33 cm)

Width 37.40 in (95 cm)

Depth 41.30 in (104.9 cm)

Net Weight 165.39 lb(US) (75.02 kg)

Mounting Preference No preference

Mounting Mode Not rack-mountable

Input

Minimum Circuit Amp Capacity 5 A

Input Frequency 60 Hz

Maximum Overcurrent Protection 15 A

Conformance

Product Certifications	ETL
------------------------	-----

Environmental

Operating Altitude	0...2000 ft
--------------------	-------------

Communications & Management

Control Panel	Multi-function LCD status and control console
---------------	---

Ordering and shipping details

Gtin	731304347989
------	--------------

Packing Units

Unit Type Of Package 1	PCE
------------------------	-----

Number Of Units In Package 1	1
------------------------------	---

Package 1 Height	21.69 in (55.1 cm)
------------------	--------------------

Package 1 Width	46.50 in (118.1 cm)
-----------------	---------------------

Package 1 Length	54.29 in (137.9 cm)
------------------	---------------------

Package 1 Weight	214.99 lb(US) (97.52 kg)
------------------	--------------------------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

[Learn more about Green Premium >](#)

Eu Rohs Directive

Not applicable, out of EU RoHS legal scope
