

MS140-300

Portable Medical Electronic Handrail Scale



- **Accuracy**— +/- 3 divisions
- **Capacity**— 660 lb x 0.2 lb; 300 kg x 0.1 kg; 660 lb x 5 oz
- **Construction**— Stainless steel weighing surface with mild steel foam covered handrails. Rigid base design.
- **Power**— Four AAA batteries or 9 VDC, 600mA wall mount adapter (both included)
- **Display**— Five digit 17 mm / 0.625" digits with seven segment LCD
- **Operator Keys**— On/Off/Zero, Tare, Unit, Hold/Print

VALUE IN
WEIGHING

MS140-300 Portable Medical Electronic Handrail Scale

Features

Simplicity of design and rugged construction are the key features of the MS140-300 Portable Medical Scale.

Featuring a 520 mm (L) x 520 mm (W) / 20.5" x 20.5", low-profile (65 mm (H) / 2.5" H) platform with sturdy handrails and padded grips, the MS140-300 digital scale was designed to be the perfect choice for clinics, health clubs, or even home use.

This medical scale has the ability to print weight data offering a real time saving device for doctor's offices, long-term care facilities, and other medical institutions.

Heavy-duty, yet lightweight & portable this scale is suitable for almost any application requiring accuracy and medium to heavy weight capacity. The repeatability is unbeatable and will offer years of continued usage. It comes with an easy-to-read LCD backlit display and operates on AC power. This medical scale is durable and reliable at an affordable price.



a division of Avery Weigh-Tronix, LLC

Brecknell

1000 Armstrong Dr., Fairmont, MN 56031
Toll free: 800-637-0529, Tel: 507-238-8702
Fax: 507-238-8271
e-mail: sales@brecknellscales.com
www.brecknellscales.com



Brecknell

Foundry Lane, Smethwick
West Midlands B66 2LP UK
Tel: +44 (0) 845 246 6717
Fax: +44 (0) 845 246 6718
Email: sales@brecknellscales.co.uk
www.brecknellscales.co.uk

Specifications

Unit: kg, lb, lb/oz

Serial Port: One (1) full duplex RS232 with cable

RS-232: Supplied complete with 10' cable (9 pin to 9 pin type connector, bi-directional full duplex)

Integrated Wheel Kit: For easy portability

Weight Hold: May be used to freeze and store the displayed weight so that you may attend to the patient's needs

Operating Temperature: 5° C to 35° C / 41° F to 95° F

Platform Dimension:

Scale: 520 mm (L) x 520 mm (W) x 1,135 mm (H)
20.5" L x 20.5" W x 44.25" H

Weighing Platform:

520 mm (L) x 520 mm (W) x 65 mm (H)
20.5" L x 20.5" W x 2.5" H

Indicator Dimension:

165 mm (L) x 30 mm (W) x 81 mm (H)
6.5" L x 1.2 W x 3.2" H

Product Weight: 19 kg / 42 lb

Packaging Dimension:

1168 mm (L) x 635 mm (W) x 152 mm (H)
46" L x 25" W x 6" H

Shipping Weight: 25 kg / 55 lb

Packaging Contents: Manual, platform, 3 piece handles, power supply, RS-232 cable, indicator, 3 hex wrenches and pull through string

Certifications: FCC compliance, UL/CUL power adapter

Product Code: 816965004829



Brecknell is part of Avery Weigh-Tronix. Avery Weigh-Tronix is a trademark of Illinois Tool Works group of companies whose ultimate parent company is Illinois Tool Works Inc ("Illinois Tool Works"). Copyright © 2018 Illinois Tool Works. All rights reserved. This publication is issued to provide outline information only and may not be regarded as a representation relating to the products or services concerned. This publication was correct at the time of going to print, however Avery Weigh-Tronix reserves the right to alter without notice the specification, design, price or conditions of supply of any product or service at any time.