

HP Z4 G4 Workstation (6TT36EA)



HP's best-selling performance workstation

Perfect for engineering, visualization and Machine Learning, HP's most popular workstation delivers disruptive performance for a wide spectrum of applications. With a choice of Intel® Xeon® or Core™ X processors, and support for dual extreme graphics, you get all you need, nothing more.



HP recommends Windows 10 Pro.

Feature-rich functionality

The Z4 is ahead of its time with more standard features than any other single processor HP workstation. With multiple configuration options, you can choose the perfect blend of components that meet your performance requirements.

Visualization powerhouse

Visualize your project anytime with the power to move seamlessly between 3D CAD, rendering and simulation applications. The Z4 can easily handle tasks that require high frequency processing, multiple cores and high-powered GPUs for an optimized design process.

HP's most secure workstations

Advanced security features come standard on every Z4. Rest assured your device, identity and data are safe with security software like HP Client Security Suite Gen3[2] and HP Sure Start Gen3[10] featuring a self-healing BIOS.

Featuring

Windows 10 Pro 64

Work without compromising on performance or security with Windows 10 Pro, powered by HP's collaboration and connectivity technology. [1]

Intel® Core™ i9 processor

Get high-end performance for intensive tasks like rendering and video editing with the Intel® Core™ i9 processor. [3]

Intel® Core™ X-Series processors

Experience disruptive price-performance on multi-threaded applications, or combined workflows such as simulation based design, with Intel® Core™ X-Series processors: the high-performance single-socket processors from Intel®. [8]

Graphics

Get serious about graphics and reach peak productivity with access to a breadth of NVIDIA® and AMD professional graphics from entry to high-end 3D. [4]

Storage

Install pro-grade storage hardware and elevate your storage-bound apps without sacrificing standard PCIe slots.

Specifications

Operating system	Windows 10 Pro 64
Processor family	9th Generation Intel® Core™ i9 processor
Processor	Intel® Core™ i9 9820X (3.3 GHz base frequency, up to 4.2 GHz with Intel® Turbo Boost Max Technology 3.0, 16.5 MB cache, 10 cores) ^[6,7]
Chipset	Intel® C422; Intel® X299 ^[26,27]
Memory	64 GB DDR4-2666 SDRAM (4 x 16 GB)
Memory Slots	8 DIMM
Internal Storage	512 GB HP Z Turbo Drive PCIe® SSD
Hard drive (2nd)	2 TB 7200 rpm SATA
Internal drive bays	Two 2.5" or 3.5"
External drive bays	Two 5.25"
Optical drive	9.5 mm Slim DVD-Writer
Graphics	Integrated
Graphics (integrated)	Intel® UHD Graphics 630
Compatible displays	All HP Z Displays and HP DreamColor Displays are supported. For more information see www.hp.com/go/zdisplays .
Minimum dimensions (W x D x H)	38.6 x 16.9 x 44.5 cm
Minimum dimensions (W x D x H)	15.2 x 6.65 x 17.5 in
Weight	Starting at 10.2 kg (Exact weight depends on configuration.)
Weight	Starting at 22.4 lb (Exact weight depends on configuration.)
Keyboard	HP USB Business Slim Keyboard
Pointing device	HP USB Optical Mouse
Ports	1 headset connector; 4 USB 3.1 (1 charging) (The Intel® Core™ X-Series processor configurations only have one RJ45 port and 5 Rear USB 3.1 Gen 1 ports available. The serial port is optional.)
Expansion slots	2 PCIe 3 x4, 2 M.2 PCIe 3 x4, 1 PCIe x8, 2 PCIe x16 (for Intel® Xeon® W configurations); 2 PCIe 3 x4, 1 M.2 PCIe 3 x4, 1 PCIe x8, 2 PCIe x16 (for Intel® Core™ i9-X and Core™ i7-9800X configurations); 2 PCIe 3 x4, 1 M.2 PCIe 3 x4, 1 PCIe x8 (mechanical only), 1 PCIe x16 (x8 electrical), 1 PCIe x16 (for other Intel® Core™ i7-X configurations)
Ports	1 headset connector; 2 USB 3.1 Gen 2 Type-C™; 2 USB 3.1 Gen1 (1 charging)
Ports	1 audio-in; 1 audio-out; 1 PS/2 keyboard port; 1 PS/2 mouse port; 1 serial; 2 RJ-45 (1 GbE); 6 USB 3.1 Gen 1
Power	1000 W internal power supply, up to 90% efficiency, active PFC ^[22]
Environmental	Low halogen
Security management	Full volume encryption; HP Keyed Cable Lock Kit; HP Secure Erase; HP Sure Start Gen3; Kensington lock slot; Secure authentication; TPM 2.0 certified; HP Device Access Manager; HP Sure Click; HP BIOSphere Gen3; HP Client Security Manager Gen3; HP MIK/SCCM Gen2; Self Encrypting Drive (SED) ^[7,14,15,17,18,28]
Warranty	On-site limited warranty and service with 3 year limited warranty and service offering delivers on-site, next business-day service for parts and labor and includes free telephone support 8 am - 5 pm. Global coverage ensures that any product purchased in one country and transferred to another, non-restricted country will remain fully covered under the original warranty and service offering. 24/7 operation will not void the HP warranty.

Accessories and services

No Recommended Accessories and Services

Messaging Footnotes

[1] Not all features are available in all editions or versions of Windows. Systems may require upgraded and/or separately purchased hardware, drivers, software or BIOS update to take full advantage of Windows® functionality. Windows 10 is automatically updated, which is always enabled. ISP fees may apply and additional requirements may apply over time for updates. See <http://www.windows.com>.

[2] HP Client Security Suite Gen3 requires Windows and Intel® or AMD 7th Gen processors.

[3] Multicore is designed to improve performance of certain software products. Not all customers or software applications will necessarily benefit from use of this technology. Performance and clock frequency will vary depending on application workload and your hardware and software configurations. Intel's numbering, branding and/or naming is not a measurement of higher performance.

[8] Windows 10 Pro is preinstalled. Windows 7 is not supported on the Intel® Core™ X - Series processor configurations. Configurations with the Intel® Core™ X processors support only a subset of the full features of the Z4 G4 system, including, but not limited to: memory type and maximum memory, PCIe slot configurations, M.2 storage capacity, GbE interface and manageability features. Please refer to the product QuickSpecs for complete details.

Technical Specifications Footnotes

[6] Multi-core is designed to improve performance of certain software products. Not all customers or software applications will necessarily benefit from use of this technology. Performance and clock frequency will vary depending on application workload and your hardware and software configurations. Intel's numbering is not a measurement of higher performance.

[7] Intel® Turbo Boost performance varies depending on hardware, software and overall system configuration. See <http://www.intel.com/technology/turboboost/> for more information.

[14] HP BIOSphere G3 requires Intel® 7th generation processors.

[15] HP Secure Erase: For the methods outlined in the National Institute of Standards and Technology Special Publication 800-88 "Clear" sanitation method.

[17] HP MIK/SCCM - HP Manageability Integration Kit can be downloaded from <http://www.hp.com/go/clientmanagement>.

[18] HP Keyed Cable Lock Kit is available only as an aftermarket option.

[22] 465W and 750W power supply options are only available for Intel® Xeon® configurations.

[26] Choice of Intel Core X processor family will affect other configuration choices and system feature set availability; refer to the product QuickSpecs for details.

[27] Intel® C422 for Intel® Xeon® configurations, Intel® X299 for Intel® Core™ X configurations.

[28] HP Sure Click is available on most HP PCs and supports Microsoft® Internet Explorer, Google Chrome, and Chromium™. Supported attachments include Microsoft Office (Word, Excel, PowerPoint) and PDF files in read only mode, when Microsoft Office or Adobe Acrobat are installed.

Copyright © 2019 HP Development Company, L.P. The only warranties for HP products are set forth in the express limited warranty statements accompanying such products. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

Intel, Xeon, Thunderbolt and Intel vPro are trademarks of Intel Corporation or subsidiaries in the U.S. and/or other countries. Bluetooth is a trademark of its proprietor and used by HP Inc. under license. USB Type-C™ and USB-C™ are trademarks of USB Implementers Forum. ENERGY STAR is a registered trademark of the U.S. Environmental Protection Agency. DisplayPort™ and the DisplayPort™ logo are trademarks owned by the Video Electronics Standards Association (VESA®) in the United States and other countries. AMD and Radeon are trademarks of Advanced Micro Devices, Inc. NVIDIA. The NVIDIA logo and Quadro are trademarks and/or registered trademarks of NVIDIA Corporation in the U.S. and other countries. Red Hat(R) is a registered trademark of Red Hat, Inc. in the United States and other countries. Linux® is the registered trademark of Linus Torvalds in the U.S. and other countries. All other trademarks are the property of their respective owners.

