

ThinkPad P1

SIMPLY SPECTACULAR



THE POWER YOU NEED, THE MACHINE YOU WANT

Is it better to be powerful or mobile? Lenovo™ asked this question, and with the ThinkPad® P1 Gen 2, the answer can be both. With the perfect combination of workstation know-how, ultra-premium stylish design and true mobility, the ThinkPad P1 removes the tradeoff of sacrificing looks for power.

Now with a vibrant 4K OLED display, the ThinkPad P1 allows you to experience true-to-life images and video with expanded contrast, brilliant colors, and stunning detail.

FEATURES



9th Generation Intel® Xeon® and Core™



Up to NVIDIA® Quadro® T2000



15.6" OLED Touch Display with Dolby Vision HDR



Thin & Light



64GB DDR4 Memory



4TB of PCIe NVMe SSD Storage

Lenovo™

Lenovo™ Options & Accessories



ThinkVision® P44w Monitor



ThinkPad® Thunderbolt™
Workstation Dock



ThinkPad Professional
15.6" Backpack

Lenovo ThinkPad P1 Gen 2 Specifications

PERFORMANCE

Processor

9th Gen Intel® Xeon® and Core™

Operating System

Windows 10 Pro for Workstations

Windows 10 Pro

Windows 10 Home

Ubuntu® Linux (pre-load)

Redhat® Linux (certified)

Graphics

Up to NVIDIA® Quadro® T2000

Camera

HD Camera with ThinkShutter

Hybrid IR¹ Camera with ThinkShutter

Total Memory

Up to 64GB DDR4

Memory DIMM Capacity

8GB / 16GB / 32GB ECC & non-ECC
2 SoDIMM slots

Total Storage

Up to 4TB NVMe SSD

Raid

0, 1

Battery

80WHR

Power Supply

135W Slim

CONNECTIVITY

Ports

(2) USB-A 3.1 Gen 1*, 1 Always On
(2) USB-C Thunderbolt™ 3
(1) HDMI 2.0
(1) Mini Gigabit Ethernet
(1) Mic/Headphone Combo Jack
(1) Smart Card Reader¹

WLAN

Intel Wi-Fi 6 AX200 (Gig+) +
Bluetooth® 5.1 vPro

Media Card Reader

4-in-1 SD Card Reader

ThinkShield

dTPM 2.0
Touch Fingerprint Reader
ThinkShutter
Kensington Lock Slot

SOFTWARE

Windows 10 Preloads

Lenovo Vantage

ISV CERTIFICATIONS

ArcGIS®, AutoCAD®, CATIA®, Creo®,
Inventor®, Microstation®, NX®,
PDMS®, Revit®, Solid Edge®,
SolidWorks®, Vectorworks®

DESIGN

Display

15.6" Display

4K (3840 x 2160)

- OLED Touch, 400nit,
Dolby Vision HDR

- LCD IPS 500nit,
Dolby Vision HDR

FHD (1920 x 1080) IPS

- 300nit or 500nit, 72% NTSC

Keyboard

ThinkPad Precision Keyboard,
Backlit and Spill Resistant

Dimensions (WxDxH)

(mm): 361.8 x 245.7 x 18.4

Weight

Starting at 3.74lbs (1.7kg)

GREEN CERTIFICATIONS

EPEAT™
Energy Star 7.1
Greenguard
RoHS Compliant



For full list of accessories and options, please visit:
<https://accsmartfind.lenovo.com>

¹ Optional

* The actual transfer speed of the USB 3.1 Gen1 will vary and, depending on many factors, such as the processing capability of host and peripheral devices, file attributes and other factors related to system configuration and your operating environments, will be slower than a speed of 5Gbit/s.

RECOMMENDED SERVICES

Lenovo™ offers a comprehensive portfolio of services to support and protect your ThinkPad® investment— so you can focus on your business, not your IT.

Premier Support

Bypass phone menus and scripted troubleshooting to access advanced-level technicians with the expertise needed to quickly diagnose and solve problems.

Warranty Upgrades—Onsite and Next Business Day

Maximizes PC uptime and productivity by providing convenient, fast repair service the next business day.

Warranty Extensions (1 to 5 years total duration)

This fixed-term, fixed-cost service helps you accurately budget for PC expenses, protect your valuable investment, and potentially lower the cost of ownership over time.

© 2019 Lenovo. All rights reserved. These products are available while supplies last. Prices shown are subject to change without notice. For any questions concerning price, please contact your Lenovo Account Executive. Lenovo is not responsible for photographic or typographic errors. Warranty: For a copy or warranty regarding third-party products or services. Trademarks: Lenovo, the Lenovo logo, Rescue and Recovery, ThinkPad, ThinkCentre, ThinkStation, ThinkVantage, and ThinkVision are trademarks or registered trademarks of Lenovo. Microsoft, Windows, and Vista are registered trademarks of Microsoft Corporation. AMD, the AMD Arrow logo, and combinations thereof are trademarks of Advanced Micro Devices, Inc. in the United States and/or other jurisdictions. Other company, product, and service names may be trademarks or service marks of others.

