

# Specifications

## Flex

1536 Round Ottoman

### Frame

- Core is comprised of EPS (Expanded Polystyrene) on .75" engineered hardwood platform base

### Foam

- CFC-free, Bio-Flex™ Hybrid includes soy-based foam
- Top surface: 3" thick, 1.8 Density, 36 CFR
- Vertical surfaces: .5" thick, 1.5 Density, 45 CFR

### Upholsteries

- Standard fabrics Cal 117 rated and tested for high wear (most more than 30,000 double rubs Wyzenbeek Wire Mesh test).
- Woven Cryptons treated with Perma Block or vinyls with Blockade/Nano-cide which are anti-bacterial, anti-microbial and mildew resistant
- See individual swatches for technical specifications
- Also accepts leather, faux leather and vinyl upholsteries

### Exterior

- Fully Upholstered top and sides
- Non-marring, black .75" H non-adjustable, cylindrical glides



### Dimensions

- Overall: 36"D x 18"H

### Warranty

- Limited Lifetime
- Meets or exceeds ANSI/BIFMA 5.4 Lounge Seating Tests

### Ships

- Fully Assembled by Truck
- Ship Weight: 25 lb
- Ship Cubes: 40
- Freight Class: 200

### Environmental & Sustainability Materials & Resources



Standard material use in products in accordance with the following standards:

- LEED for Commercial Interiors EA Credit 2.1, 50% Construction Waste Diversion (1 point)
- LEED for Commercial Interiors EA Credit 2.2, 75% Construction Waste Diversion (1 point)
- ANSI/BIFMA e3-2011e (level®) Credit 5.10.2, 100% solid waste diversion
- LEED for Commercial Interiors EA Credit 3.3, Resource Reuse 30%, Furniture & Furnishings (1 point)
  - HPFI Lifetime warranty and Second Life program applicable for reuse
- ANSI/BIFMA e3-2011e (level®) Credit 5.9.4, Extended Product Responsibility - HPFI Second Life program ensures reuse of usable product
- LEED for Commercial Interiors MR Credit 5.1, Regional Materials 20% (1 point) - HPFI products are manufactured in High Point, NC and may contribute this point based on project location.