

## OVERVIEW

Upgradeable Unit Level EC Monitored rPDUs provide reliable power distribution to critical IT equipment while delivering a comprehensive view of input level power usage via remote network access. Includes environmental monitoring capabilities to obtain real-time environmental metrics. Upgrade the hot-swappable monitoring device on select units to leverage new technologies and accommodate changing business needs.

### Benefits

- Reliable power distribution with local and remote power monitoring options offer quick access to critical power usage information to evaluate energy usage trends and maximize uptime.
- Environmental monitoring capabilities with the addition of optional environmental sensors ensure users have critical infrastructure data at their fingertips to prevent climate-related equipment failure and system downtime.
- Gather comprehensive power data at the palm of your hand with the use of the Vertiv VLC mobile app.
- Fault-Tolerant Daisy Chaining with RSTP simplifies intelligent rPDU connectivity and ensures data is reported even when a break in the network chain occurs. Supports up to 40 rPDUs.
- Every unit is 100% tested for reliability and functionality.



## Part #: NI30063L

**Model Number:** MN03E8W1-24P6H8-5CS15A0A10-S

**Category:** Monitored

**Sub Category:** Unit Level EC

**Power Configuration:** 50A, 208V DELTA, 14.4kW

**Physical Configuration:** 72in / 1829mm, Vertical

### Product Summary:

NI30063L - rPDU, Monitored Unit Level EC, 50A, 208V DELTA, 14.4kW, Vertical, (6) Locking IEC C13, (18) Locking IEC C19, 10ft power cord with 3P+E CA, Black Powder Coat.

### Monitoring:

Input and per Phase power monitoring with Circuit/Breaker current monitoring. Environmental monitoring via optional remote sensors. Daisy chain Ethernet connectivity. Local high visibility LED display.

### Plug Form:



3P+E CA

### Receptacle:



Locking IEC C13  
(Quantity: 6)



Locking IEC C19  
(Quantity: 18)

### Chassis Color Options:



To discuss color options, contact your local sales representative.

## Product Specification and Options

## System Features

<b>Monitoring</b>	Input and per Phase power monitoring with Circuit/Breaker current monitoring. Environmental monitoring via optional remote sensors. Daisy chain Ethernet connectivity. Local high visibility LED display.
<b>Monitoring Level 1</b>	Aggregate - Total Unit Monitoring (kWh, W, VA, PF)  Power Measurements Compliant with ANSI C12.1 and IEC 62053-21 at 1% Accuracy Class Requirements
<b>Monitoring Level 2</b>	Phase (AB, BC, CA) Monitoring (kWh, W, VA, PF, V, A) Line (A,B,C) Monitoring (A)  Power Measurements Compliant with ANSI C12.1 and IEC 62053-21 at 1% Accuracy Class Requirements
<b>Monitoring Level 3</b>	Circuit / Breaker Monitoring (A)  Circuit/Breaker Current Measurements Independently Tested and Verified at 2% Accuracy
<b>VLC Support</b>	Yes
<b>Quantity Of Inputs</b>	1
<b>Voltage</b>	200-240V Delta
<b>Current</b>	50A x 3 Phase DELTA
<b>VA per Input (Load Capacity)</b>	14.4kW (208V)
<b>Frequency</b>	50/60Hz
<b>Over Current Protection</b>	(6) 20A Double Pole Magnetic Breakers
<b>Switch</b>	Breaker/Switch Combination
<b>Scrolling / Rotatable Digital Display</b>	Yes
<b>Power Cable Wire Gauge</b>	6/4
<b>Power Cable Length</b>	10ft
<b>Power Entry Location</b>	Bottom Front
<b>Plug Type</b>	California Style 50A, 250V, 3P/4W Twistlock
<b>Combined Total Receptacle/Socket Quantity</b>	24
<b>Receptacle/Socket Type #1</b>	U-Lock IEC C13
- Quantity on Face	6
- Quantity per Breaker	1
- Quantity per Phase Combination	2
- U-Lock Color ID	6 Circuit = Orange, Green, Blue, Light Orange, Light Green, Light Blue
- Style	Individual
- Voltage per Receptacle/Socket	208V
<b>Receptacle/Socket Type #2</b>	U-Lock IEC C19
- Quantity on Face	18
- Quantity per Breaker	3
- Quantity per Phase Combination	6
- U-Lock Color ID	6 Circuit = Orange, Green, Blue, Light Orange, Light Green, Light Blue
- Style	Individual
- Voltage per Receptacle/Socket	208V

<b>Internal RMS Voltage Sensor</b>	Yes
<b>Internal RMS Current Sensor</b>	Yes
<b>Network Connection</b>	Dual 10/100Mbps Ethernet
<b>Protocols Supported</b>	DHCP, HTTP, HTTPS, IPv4, IPv6, LDAP, NTP, RADIUS, RSTP, SSH, SMTP, SNMP (v1/v2c/v3), Syslog, TACACS+
<b>Data Access Formats</b>	CSV datalog, JSON API, JSON datalog
<b>USB Support</b>	Yes
<b>IP Reset Button</b>	Yes
<b>Hard Reboot Button</b>	Yes
<b>Serial Connection</b>	RS232 via RJ45
<b>Remote Sensor RJ Connection Jacks</b>	1 (Supports up to 16 Sensors)
<b>Maximum Operating Temperature</b>	60C / 140F
<b>Heavy Steel - Powder Coat Finish</b>	Black
<b>Configuration</b>	72in / 1829mm Vertical Rackmount
<b>7938 Vertical Mounting Bracket Kit</b>	Yes
<b>Toolless Mounting Hardware - Center to Center Spacing</b>	61.25in and 64.75in
<b>Country of Origin</b>	USA, TAA Compliant
<b>Product Warranty</b>	5-year limited warranty if registered within 120 days of purchase, otherwise warranty defaults to 3 years
<b>Certification/Agency Approvals</b>	FCC Part 15 Class A Conformance
<b>Certification/Agency Approvals</b>	RoHS Compliant
<b>Certification/Agency Approvals</b>	UL & c-UL Listed 60950
<b>Chassis Dimensions (LxWxD)</b>	72in x 2.25in x3.44in
<b>Shipped Weight</b>	30lbs (13.61kg)