

Lenovo C32q-20 65F8GCC1US

Product

Lenovo C32q-20

Machine Type

65F8

Region

NA

Color

Black

Panel

In-Plane Switching

Display Size

31.5"

View Area

698.112x392.688 mm

Resolution

2560x1440

Aspect Ratio

16:9

Pixel Pitch

0.272x0.272 mm

Dot / Pixel Per Inch

93.2 dpi

Brightness

250 nits

Contrast Ratio

1000:1

Pixel Response Time

4 ms

Color Gamut

80%

View Angle (H / V)

178 / 178

Stand

Tilt

Side Bezel Width

13.9 mm / 22.8 mm (Top / Bottom)

Dimensions with Stand (HxWxD)

508.6x729.7x256.1 mm

Power Consumption (Typical / Maximum)

35W / 45W

Power Adapter

Integrated

Weight (Including Stand)

15.79lb / 7.16kg

Warranty

1-year

ENERGY STAR

ENERGY STAR 7.0

TCO

None

EPEAT

None

Presets / User Settings

20

On Screen Display

OSD, 8 Languages

USB Port

None

Speaker

None

Camera

None

Low Blue Light / Eye Comfort

Low Blue Light

Multiple Input

HDMI, DP

Monitor Cable

HDMI

End of Support

CPU / Platform

None / None

Display Ram / Storage / Card Slot

None / None / None

Wireless / Ethernet / Bluetooth

None / None / None

Touch Screen / Digitizer Pen / Battery

None / None / None

Operating System

Support Windows 7, Windows 10

Ann Date (mm/yy)

08/19

Notes:

California Electronic Waste Recycling Fee

In California, per state law, Lenovo charges an electronic waste recycling fee on this covered device at the time of sale of the product. For more information, go to: <https://www.calrecycle.ca.gov/Electronics/Consumer>

L WWW.LENOVO.COM

Lenovo may not offer the products, services or features discussed in this document in other countries. Lenovo may withdraw an offering at any time. Information is subject to change without notice. Consult your local representative for information on offerings available in your area.

Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors.

Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.

<https://psref.lenovo.com>

Visit psref website for the latest version of Product Specifications Reference.

© Lenovo, 2020. All rights reserved.



Lenovo C32q-20



DISPLAY

Panel Size

31.5-inch

Screen Dimensions (W x H)

698.112 x 392.688 mm

Panel Type

In-Plane Switching

Backlight

WLED

Aspect Ratio

16:9

Resolution

2560 x 1440

Refresh Rate

75 Hz

Pixel Pitch (H x V)

0.272 x 0.272 mm

Viewing Angle (H x V @ CR 10:1)

178° / 178°

Response Time (min)

4ms

Contrast Ratio (typical)

1000:1

Brightness (typical)

250 cd/m²

Color Gamut NTSC (CIE 1931)

72%

Color Support

1.07 Billion

Sync Technology

FreeSync™

Anti-Glare

Yes

CONNECTIVITY

Video Input Signals

HDMI 1.4 + DP1.2

Audio Out

Yes

DIMENSIONS

Size Packed (D x H x W) (mm/inch)

870 x 203 x 600 mm /
34.2 x 7.9 x 23.6 inches

Size Unpacked w/stand (D x H x W) (mm/inch) (Lowest position)

256.1 x 508.6 x 729.7 mm /
10 x 20 x 28.7 inches

Size Unpacked w/stand (D x H x W) (mm/inch) (Highest position)

256.1 x 508.6 x 729.7 mm /
10 x 20 x 28.7 inches

Size Unpacked w/o stand (D x H x W) (mm/inch) (Head Only)

53.8 x 432.8 x 729.7 mm /
2.1 x 17 x 28.7 inches

Weight Packed

10.51 kg / 23.18 lbs.

Weight Unpacked

7.16 kg / 15.79 lbs.

Weight (Monitor Head Only)

6.1 kg / 13.45 lbs.

MECHANICAL

Tilt Angle (front/back)

-5° / 22°

VESA Mount Capability

100 x 100 mm

Kensington™ Lock Slot

Yes

Bezel Color

Raven Black

Bezel Width (Side)

13.9 mm

Bezel Width (top/bottom)

13.9 mm / 22.8 mm

China Energy Efficiency Standard

CEL G1

TÜV Low Blue Light

Yes

Ambient Operating Temperature

0°C to 45°C



WHAT'S IN THE BOX

Monitor with stand

1 x Power cable

1 x HDMI cable

Quick setup guide

CERTIFICATIONS

EU RoHS

Yes

CCC

Yes

Windows Certification

Windows 7, Windows 10

Depending on many factors such as the processing capability of peripheral devices, file attributes, and other factors related to system configuration and operating environments, the actual transfer rate using the various USB connectors on this device will vary and is typically slower than the data rates as defined by the respective USB specifications: - 5 Gbit/s for USB 3.1 Gen1; 10 Gbit/s for USB 3.1 Gen2 & 20 Gbit/s for USB 3.2.

© 2019 Lenovo. All rights reserved. These products are available while supplies last. Prices shown are subject to change without notice. For any questions concerning price, please contact your Lenovo Account Executive. Lenovo is not responsible for photographic or typographic errors. Warranty: For a copy of applicable warranties, write to: Warranty Information, 500 Park Offices Drive, RTP, NC 27709, Attn: Dept. ZPYA/B600. Lenovo makes no representation or warranty regarding third-party products or services. Trademarks: Lenovo, the Lenovo logo, Rescue and Recovery, ThinkPad, ThinkCentre, ThinkStation, ThinkVantage, and ThinkVision are trademarks or registered trademarks of Lenovo. Microsoft, Windows, and Vista are registered trademarks of Microsoft Corporation. Intel, the Intel logo, Intel Inside, Intel Core, and Core Inside are trademarks of Intel Corporation in the U.S. and/or other countries. Other company, product, and service names may be trademarks or service marks of others.

Specifications may vary depending upon region.

Lenovo C32q-20

Lenovo

