



The highly secure thin client optimized for workplace productivity

Tackle your hybrid local and virtual computing workloads with the HP t640 Thin Client. Help keep your data and device safe across your workflows with built-in security features. Choose the right fit for your specific users and environment with a range of subsystem options.



Maximize what you can accomplish

Empower your workforce with performance that conquers every task—an AMD Ryzen™ R1505G processor[1], high-speed, responsive system memory, and native support for up to three UHD/4K displays.

Refined security

Encrypt data as it flows between the system memory and processor, protect firmware, and lock down access with an inherently secure thin client that has AMD Memory Guard, an embedded OS, and a NIST SP800-193 component.

Modern flexibility

Select from up to 35 different subsystem options, including wired or wireless networking and support for legacy peripherals. Conveniently position the thin client in up to six different orientations with an integrated VESA mount.[2]

Specifications

Operating system	Windows 10 IoT Enterprise for Thin Clients 64
Memory	8 GB DDR4-2400 MHz RAM (2 x 4 GB)
Memory Slots	2 SODIMM
Internal Storage	64 GB Flash memory
Audio	Internal amplified speaker system for basic audio playback
Minimum dimensions (W x D x H)	3.5 x 19.6 x 19.6 cm (Vertical orientation.)
Minimum dimensions (W x D x H)	1.24 x 7.71 x 7.71 in (Vertical orientation.)
Weight	1 kg (Weight will vary depending on configuration.)
Weight	2.2 lb (Weight will vary depending on configuration.)
Keyboard	HP USB Slim Business Keyboard
Pointing device	HP USB optical mouse
Ports	1 headphone/microphone combo; 1 USB 3.1 Gen 1; 1 USB 3.1 Type-C™ Gen 2; 1 USB 3.1 Gen 2
Ports	1 audio-in; 2 USB 2.0; 2 USB 3.1 Gen 1; 3 DisplayPort 1.2
Protocols	Citrix® HDX; Microsoft RFX/RDP; VMware Horizon® View™ through RDP/PCoIP, and Blast Extreme
Power	45 W smart external power adapter
Ecolabels	ENERGY STAR® certified
Sustainable impact specifications	Low halogen
Software included	HP Device Manager; HP Easy Shell; HP Easy Tools; HP Smart Zero Client Services; HP ThinUpdate; HP True Graphics; Microsoft SCCM/EDM Agent
Browser supported	Internet Explorer (for models with Windows 10 IoT Enterprise LTSC 2019); Mozilla Firefox (for models with HP ThinPro)
UPC number	(ABA) 193905522828; (ABB) 193905523283; (ABC) 193905523191; (ABD) 193905523078; (ABE) 193905523122; (ABF) 193905523177; (ABU) 193905523207; (ABZ) 193905523245; (AC8) 194441032789; (UUG) 193905523061

Top Recommended Displays, Accessories and Services

EliteDisplays

HP EliteDisplay E243 23.8-inch Monitor	1FH47AA
HP EliteDisplay E243d 23.8-inch Docking Monitor	1TJ76A8
HP EliteDisplay E243d 23.8-inch Docking Monitor	1TJ76AA

Keyboard and Mouse Kits

HP Wireless Business Slim Keyboard and Mouse	N3R88AA
--	---------

Mice

HP USB 1000dpi Laser Mouse	QY778AA
----------------------------	---------

Keyboards

HP USB Business Slim Keyboard	N3R87AA
-------------------------------	---------

Power Supplies

HP Thin Client 45W Power Supply	Y3U71AA
---------------------------------	---------

PC Locks

HP Keyed Cable Lock 10 mm	T1A62AA
---------------------------	---------

Mounting Kits

HP Quick Release Bracket 2	6KD15AA
HP Thin Client Mounting Bracket	2FT00AA

Messaging Footnotes

[1] Multicore is designed to improve performance of certain software products. Not all customers or software applications will necessarily benefit from use of this technology. Performance and clock frequency will vary depending on application workload and your hardware and software configurations. AMD's numbering is not a measurement of clock speed.

[2] Mounting hardware sold separately.

Technical Specifications Footnotes

No Technical Specifications Footnotes

Copyright © 2021 HP Development Company, L.P. The only warranties for HP products are set forth in the express limited warranty statements accompanying such products. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

AMD and Radeon are trademarks of Advanced Micro Devices, Inc. DisplayPort™ and the DisplayPort™ logo are trademarks owned by the Video Electronics Standards Association (VESA®) in the United States and other countries. Wi-Fi® is a registered trademark of Wi-Fi Alliance®.

AMD and Radeon are trademarks of Advanced Micro Devices, Inc. DisplayPort™ and the DisplayPort™ logo are trademarks owned by the Video Electronics Standards Association (VESA®) in the United States and other countries. Wi-Fi® is a registered trademark of Wi-Fi Alliance®.

