



**Hewlett Packard**  
Enterprise

# HPE ProLiant DL160 Gen10 4208 1P 16GB-R 8SFF 500W PS Server (P19560-B21)

## ProLiant DL Servers



### What's new

- Supports the second generation Intel® Xeon® Scalable processor family.
- HPE InfoSight provides a cloud-based analytics tool that predicts and prevents problems before your business is impacted.
- HPE Small Business Solutions are complete solutions and workload optimized built on ProLiant servers, providing the foundational on-premises component for

### Overview

Are you searching for a dense server with exceptional value to run on-premises and hybrid cloud solutions?

The secure 2P 1U HPE ProLiant DL160 Gen10 server delivers the right balance of performance, storage, reliability, manageability and efficiency in a dense and compact chassis, to meet the needs of growing businesses of a diverse set of customers – from SMB to service providers running wide range of workloads at a compelling price point.

---

the Hybrid Cloud.

- Available aggressively priced SMB offer models regionally released as “Smart Buy Express” in the U.S. and Canada, “Top Value” in Europe, and “Intelligent Buy” in Asia Pacific.

## Features

### Scalability and Efficiency in a Dense Design

Supports 1st and 2nd generation Intel® Xeon® Scalable processors, up to 24 cores and up to 150W.

Deploy mid-level virtualization, IT/ web infrastructure for SMBs and small enterprises.

Right balanced server to support multiple workloads.

### Agile, Secure Infrastructure Management for Accelerating IT Service Delivery

HPE iLO 5 enables the world’s most secure industry standard servers with HPE silicon root of trust technology to protect your servers from attacks, detect potential intrusions and recover your essential server firmware securely.

Features include iLO Security Dashboard that helps detect and address possible security vulnerabilities and Workload Performance Advisor that provides server tuning recommendations for better server performance.

Millions of lines of firmware code run before the server OS boots and with Runtime Firmware Verification, enabled by HPE iLO Advanced. The server firmware is checked every 24 hours verifying validity and credibility of essential system firmware.

Secure Recovery allows server firmware to roll back to the last known good state or factory settings after detection of compromised code.

Additional security options are available with Trusted Platform Module (TPM) to prevent unauthorized access to server and securely stores artifacts used to authenticate the server platforms while the Intrusion Detection Kit logs and alerts when the server hood is removed.

### Industry-Leading Serviceability and Simplified Deployment

HPE ProLiant DL160 Gen10 server comes with a complete set of services offered by HPE Pointnext, delivering confidence, reducing risk, and helping customers realize agility and stability.

Services from HPE Pointnext simplify the stages of the IT journey. Advisory and Transformation Services professionals understand customer challenges and design an enhanced solution. Professional Services enables rapid deployment of solutions and Operational Services provides ongoing support.

HPE IT investment solutions help you transform to a digital business with IT economics that align to your business goals.

**Technical specifications****HPE ProLiant DL160 Gen10 4208 1P 16GB-R 8SFF 500W PS Server**

<b>Product Number (SKU)</b>	P19560-B21
<b>Processor Name</b>	Intel® Xeon® Scalable 4208 (8 core, 2.1 GHz, 85W)
<b>Processor core available</b>	8 core
<b>Processor cache</b>	11 MB L3
<b>Processor speed</b>	2.1 GHz
<b>Power supply type</b>	1 HPE 500W Flex Slot Platinum hot plug power supply
<b>Expansion slots</b>	3 PCIe 3.0, for detailed descriptions please reference the QuickSpecs
<b>Memory, standard</b>	16 GB (1 X 16 GB) RDIMM
<b>Memory type</b>	HPE DDR4 SmartMemory
<b>Included hard drives</b>	None ship standard, 8 SFF drives supported.
<b>Optical drive type</b>	None
<b>System fan features</b>	3 standard single rotor hot swap fans
<b>Network controller</b>	HPE embedded 2-port 1 GbE Ethernet adapter
<b>Storage controller</b>	HPE Smart Array S100i
<b>Minimum dimensions (H x W x D)</b>	4.29 x 43.46 x 61.49 cm
<b>Weight</b>	10.97 kg minimum, 13.92 kg maximum
<b>Infrastructure management</b>	HPE iLO Standard with Intelligent Provisioning (embedded), HPE OneView Standard (requires download), Optional- HPE iLO Advanced, and HPE OneView Advanced (require licenses)
<b>Warranty</b>	3/3/3 Server Warranty includes 3-Year Parts, 3-Year Labor, 3-Year Onsite support with next business day response. Additional HPE support and service coverage for your product can be purchased locally. For information on availability of service upgrades and the cost for these service upgrades, refer to the HPE website at <a href="http://www.hpe.com/support">http://www.hpe.com/support</a>

**For additional technical information, available models and options, please reference the QuickSpecs**

## HPE Pointnext

**HPE Pointnext** leverages our breadth and depth of technical expertise and innovation to help to accelerate digital transformation. A comprehensive portfolio that includes – Advisory, Professional, and Operational Services is designed to help you evolve and grow today and into the future.


### Operational Services

- **HPE Flexible Capacity** is a new consumption model to manage on-demand capacity, combining the agility and economics of public cloud with the security and performance of on-premises IT.
- **HPE Datacenter Care** offers a tailored operational support solution built on core deliverables. It includes hardware and software support, a team of experts to help personalise deliverables and share best practices, as well as optional building blocks to address specific IT and business needs.
- **HPE Proactive Care** is an integrated set of hardware and software support including an enhanced call experience with start to finish case management helping resolve incidents quickly and keeping IT reliable and stable.
- **HPE Foundation Care** helps when there is a hardware or software problem offering several response levels dependent on IT and business requirements.

**Advisory Services** includes design, strategy, road map, and other services to help enable the digital transformation journey, tuned to IT and business needs. Advisory Services helps customers on their journey to Hybrid IT, Big Data, and the Intelligent Edge.

**Professional Services** helps integrate the new solution with project management, installation and startup, relocation services, and more. We help mitigate risk to the business so there is no interruption when new technology is being integrated in the existing IT environment.

### Chat online



**Hewlett Packard  
Enterprise**

© Copyright 2019 Hewlett Packard Enterprise Development LP. The information contained herein is subject to change without notice. The only warranties for Hewlett Packard Enterprise products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. Hewlett Packard Enterprise shall not be liable for technical or editorial errors or omissions contained herein.

Intel and Intel Xeon are trademarks of Intel Corporation in the U.S. and other countries. All other third-party marks are property of their respective owners.

Image may differ from the actual product  
PSN1012087629UKEN, November 03, 2019.