

# ThinkPad E14 20RA004YUS

## Product

ThinkPad E14

## Region

NA

## Country/Region

USA

## Machine Type

20RA

## TopSeller

TopSeller

## Processor

Intel Core i5-10210U (4C / 8T, 1.6 / 4.2GHz, 6MB)

## Graphics

Integrated Intel UHD Graphics

## Chipset

Intel SoC Platform

## Memory

1x 8GB DIMM DDR4-2666

## Storage

256GB SSD M.2 2242 PCIe NVMe 3.0x2

## Display

14" FHD (1920x1080) IPS 250nits Anti-glare

## Multi-touch

None

## Ethernet

100/1000M

## Optical

None

## WLAN + Bluetooth

RTL8822CE 11ac, 2x2 + BT5.0

## WWAN

None

## SIM Card

None

## Smart Card Reader

None

## Monitor Cable

None

## Bundled Accessories

None

## Case Material

Aluminum (Top), PC / ABS (Bottom)

## Camera

720p with ThinkShutter

## Microphone

2x, Array

## Color

Black

## Keyboard

Non-backlit, English

## Fingerprint Reader

Touch Style

## NFC

None

## TPM

Discrete TPM 2.0

## Battery

Integrated 45Wh

## Power Adapter

65W USB-C

## System Management

None

## Operating System

Windows 10 Pro 64, English

## Bundled Software

None

## Base Warranty

1-year, Depot

## Bundled Service

None

## EAN / UPC

194632394382

## End of Support

2025-12-08

## Announce Date

2019-11-08

## Recommended Services

### Good

3Y Premier Support Upgrade from 1Y Depot/CCI (5WS0T36151)

## Notes:

**Battery life** is an estimated maximum. Actual battery life may vary based on many factors, including screen brightness, active applications, features, power management settings, battery age and conditioning, and other customer preferences.

## California Electronic Waste Recycling Fee

In California, per state law, Lenovo charges an electronic waste recycling fee on this covered device at the time of sale of the product. For more information, go to: <https://www.calrecycle.ca.gov/Electronics/Consumer>



[WWW.LENOVO.COM](http://WWW.LENOVO.COM)

Lenovo may not offer the products, services or features discussed in this document in other countries. Lenovo may withdraw an offering at any time. Information is subject to change without notice. Consult your local representative for information on offerings available in your area.

Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors.

Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.



<https://psref.lenovo.com>

Visit psref website for the latest version of Product Specifications Reference.

© Lenovo, 2019. All rights reserved.



# ThinkPad E14 Platform Specifications

Product Specifications Reference (PSREF)

Processor	10th Generation Intel® Core™ i3 / i5 / i7 Processor								Dimensions	Case Material		Dimensions (WxDxH)				
	Processor Number	# of Cores	# of Threads	Base Frequency	Max Turbo Frequency	Cache	Memory Types	Processor Graphics		Aluminum	12.80" x 9.13" x 0.70"; 325mm x 232mm x 17.9mm					
	i3-10110U	2	4	2.1 GHz	4.1 GHz	4MB	DDR4-2666	Intel UHD Graphics		PC/ABS	12.80" x 9.13" x 0.81"; 325mm x 232mm x 20.5mm					
	i5-10210U	4	8	1.6 GHz	4.2 GHz	6MB				Aluminum Display cover + PC/ABS Bottom	12.80" x 9.13" x 0.74"; 325mm x 232mm x 18.9mm					
	i7-10510U	6	12	1.8 GHz	4.9 GHz	8MB										
Graphics	i7-10710U								Weight	Case Material	Weight					
	Intel UHD Graphics in processor only or Intel UHD Graphics in processor and AMD Radeon RX 640 Graphics, 2GB GDDR5 memory; supports external digital monitor via HDMI or USB Type-C; supports three independent displays; Max resolution: 3840x2160@60Hz (USB Type-C); 3840x2160@30Hz (HDMI)									Aluminum	starting at 3.81 lb / 1.73 kg					
	Intel SoC (System on Chip) platform 16GB max / 2666MHz DDR4, one DDR4 SO-DIMM socket									PC/ABS	starting at 3.90 lb / 1.77 kg					
Chipset									Case color	Aluminum Display cover + PC/ABS Bottom	starting at 3.74 lb / 1.69 kg					
Memory										Black or silver						
Display										Case material	Display cover: Aluminum or PC/ABS plastic; Bottom: Aluminum or PC/ABS plastic					
Multi-touch									Smart card reader	None						
										Media reader	None					
										Ports	One USB 2.0, two USB 3.1 Gen 1 (one Always On), one USB 3.1 Type-C Gen 1 (with the function of Power Delivery and DisplayPort), HDMI 1.4b, Ethernet (RJ-45), headphone / microphone combo jack, security keyhole					
Storage									Monitor cable	* Depending on many factors, actual data transfer speed may be lower than theoretical speed						
										Bundled Accy	None					
										Camera	HD720p camera with optional ThinkShutter camera privacy, fixed focus					
Optical									Audio support	HD Audio, Synaptic® CX11880 codec / stereo speakers, 2W x 2, Dolby® Advanced Audio / dual array microphone, headphone / microphone combo jack						
										Keyboard	6-row, spill-resistant, multimedia Fn keys, optional LED backlight					
										UltraNav™	TrackPoint® pointing device and buttonless Mylar surface multi-touch touchpad					
Ethernet									Security	Power-on password, hard disk password, supervisor password, security keyhole						
										Security chip	Integrated model: discrete TPM 2.0, TCG Certified					
										System Mgt	Discrete model: firmware TPM 2.0 integrated in chipset					
WWAN									Fingerprint reader	None						
										NFC	Optional: Touch style fingerprint reader on power button					
										Battery	None					
SIM card									Max battery life	Integrated Li-ion 45Wh battery, supports Rapid Charge (charge up to 80% in 1hr) with 65W AC adapter						
										MobileMark® 2014:	12.8 hr					
										* Battery life varies significantly with settings, usage, & other factors						
WWAN									AC adapter	45W or 65W USB Type-C AC adapter						
										Operating system (optional)	One of the following, configurable by model:					
										<ul style="list-style-type: none"> <li>Windows® 10 Home 64</li> <li>Windows 10 Pro 64</li> <li>Windows 10 Pro in S mode</li> <li>No OS</li> </ul>						
WWAN									Limited warranty (optional)	<ul style="list-style-type: none"> <li>1-year mail-in repair service</li> <li>1-year depot repair service</li> <li>1-year depot with 2-year system board repair service</li> <li>1-year limited onsite service</li> </ul>						
										Mil-Spec test	MIL-STD-810G military testing (by the end of Dec. 2019)					
								Environment								
								EPEAT™ Silver; ENERGY STAR® 7.1; RoHS-compliant								

Note: The specifications above may not be available in all regions.

Lenovo  
December 2019



# ThinkPad E14

Lenovo



intel  
inside



intel  
inside



intel  
inside



intel  
inside



intel  
inside



intel  
inside