

# 25" Commercial Wall Mount Fan



## Model: WFNC-25

Medium sized commercial wall mount fan with powerful airflow. Ideal for schools, gyms, restaurants, warehouses, workshops and other commercial applications where it is desirable to have fan off the floor for space and safety reasons.



### FEATURES

#### High Velocity

- At high fan speed, delivers 6850 CFM air volume

#### Adjustable AirFlow

- Fan head is 30° tilt adjustable
- Selectable Oscillation Mode for wide area air circulation

#### All Metal Construction

- Designed for rugged commercial use. Sturdy steel wall mounting bracket
- Aluminum fan blades

# 25" Commercial Wall Mount Fan



## Model: WFNC-25

### PRODUCT OVERVIEW



**① Front Guard**  
All metal safety grill

**② Fan blades**  
Aluminum construction

**③ Wall Mount Attachment**  
Heavy duty steel bracket

### SPECIFICATIONS

#### Attributes

Fan Size: 25"  
Fan Speeds: 2 (Low & High)  
CFM Air Volume: 6850 CFM (High)  
Speed: 1100 RPM (High)  
Horsepower: 1/8  
Decibels: 67 / 70 dB (Low/ High)  
Material: All Metal (Aluminum Blades)  
Tilt Adjustable Head: Yes (up to 30°)  
Oscillation Control: Yes  
Safety Grill: Yes  
ON/ OFF: Pull Chain

#### Electrical Rating

Power Supply: 120V/ 60Hz  
Amperage: 1.5A (High)  
Power Consumption: 150W  
Certification: cULus

#### Dimensions & Weights

Unit (W x D x H):  
27.1" x 19.7" x 27.1" (690 mm x 501 mm x 690 mm)  
Unit Weight: 26.4 lbs (12.0 kg)

Box (L x W x H):  
28.35" x 6.9" x 36.6" (72 cm x 17.5 cm x 93 cm)  
Box Weight: 35.3 lbs (16 kg)

#### UPC CODE

Individual Box: 849023060574

#### Warranty

1 Year Limited