

**msi**®GRAPHICS CARD **GEFORCE® GTX 1660**  
**SUPER™ GAMING X**

GEFORCE



## SPECIFICATION

Model Name	GeForce® GTX 1660 SUPER™ GAMING X
Graphics Processing Unit	NVIDIA® GeForce® GTX 1660 SUPER™
Interface	PCI Express x16 3.0
Cores	1408 Units
Core Clocks	Boost: 1830 MHz
Memory Speed	14 Gbps
Memory	6GB GDDR6
Memory Bus	192-bit
Output	DisplayPort x 3 (v1.4) / HDMI 2.0b x 1
HDCP Support	2.2
Power consumption	125 W
Power Connectors	8-pin x 1
Recommended PSU (W)	450 W
Card Dimension(mm)	247 x 127 x 46 mm
Weight (Card / Package)	862g / 1460 g
Afterburner OC	Y
DirectX Version Support	12 API
OpenGL Version Support	4.5
Maximum Displays	3
VR Ready	Y
G-SYNC™ technology	Y
Adaptive Vertical Sync	Y
Digital Maximum Resolution	7680x4320

## CONNECTIONS



1. DisplayPort
2. HDMI

## FEATURE



### TORX FAN 3.0

Award-winning fan design combining two different fin designs for cool & quiet gaming.



### Mastery of Aerodynamics

Using groundbreaking aerodynamic techniques, the heatsink is optimized for efficient heat dissipation.



### ZERO FROZR

Eliminates fan noise by stopping the fans in low-load situations so you can focus on your game.



### CUSTOM PCB

An optimized PCB design with enhanced power delivery provides a solid base for high performance gaming.



### SOLID BACKPLATE

Increases toughness of the card to prevent bending while complementing the design.



### DRAGON CENTER

A consolidated platform that offers all software including MYSTIC LIGHT functionality for your MSI Gaming product.



### OC PERFORMANCE

MSI OC graphics cards are equipped with higher clock speeds out of the box for increased performance.



### MSI Afterburner

The ultimate overclocking software with advanced control options and real-time hardware monitor.