

PERFORMANCE**Processor**

MediaTek Helio A22 (4C, 4x A53 @2.0GHz)

Graphics

Integrated IMG PowerVR GE-class GPU

Chipset

MediaTek SoC Platform

Memory

2GB Soldered LPDDR3

Storage

16GB eMMC (eMCP)

Expandable Memory

microSD Card (up to 128GB, FAT32; 2TB, exFAT)

Card Reader

microSD Card Slot

Storage Support

- 16GB eMMC on systemboard
- microSD card, supports FAT32 up to 128GB, exFAT up to 2TB

Camera

Front 2.0MP / Rear 5.0MP

Microphone

Mono

Speakers

Single front speaker, Dolby® Audio™

Sensors

WLAN models:

Accelerometer (G) sensor

Vibration Motor

No support

Battery

Integrated 5000mAh (Min.) / 5100mAh (Typ.)

Max Battery Life

Standby: 2 wks

Online video playback: 12 hr

Browsing: 18 hr

Charging Time

Over 3.3 hr to fully charged

Power Adapter

5V / 1A

DESIGN**Display**

8" HD (1280x800) IPS 350nits Glossy, Touch

Touchscreen

10-point Multi-touch

Case Material

Metal (Back Cover)

Pen

No support

Dust and Water Resistant

IP5X

Dimensions (WxDxH)

199.1 x 121.8 x 8.15 mm (7.84 x 4.79 x 0.32 inches)

Weight^[1]

Around 305 g (0.67 lbs)

Case Color

Iron Grey

SOFTWARE**Operating System**

Android™ 9 (Pie) or Later

CONNECTIVITY**WLAN + Bluetooth®**

11ac 1x1 + BT5.0

WWAN

None

VoiceCall

No

Standard Ports

- 1x Micro-USB 2.0 (support data transfer, charging, Lenovo® T-hub and OTG)
- 1x Headphone / microphone combo jack (3.5mm)

Optional Ports (configured)

1x microSD Card Slot

SERVICE**Base Warranty**

1-year, Mail-in with 1-year Battery

ACCESSORIES**Bundled Accessories**

None

CERTIFICATIONS**Green Certifications**

- ENERGY STAR® 8.0
- RoHS compliant

Other Certifications

TÜV Rheinland® Low Blue Light (Software Solution)

MODEL

Product : Lenovo® TB-8505F

TopSeller : Yes

Announce Date : 2019-11-12

EAN / UPC / JAN : 194632330779



To see more note information, please link to

https://psref.lenovo.com/Detail/Tab_M8_HD_2nd_Gen?M=ZA5G0132US

• Lenovo reserves the right to change specifications or other product information without notice.

• Battery life is an estimated maximum. Actual battery life may vary by hardware or system settings, active applications, battery conditioning, etc.

• California Electronic Waste Recycling Fee In California, per state law, Lenovo charges an electronic waste recycling fee on this covered device at the time of sale of the product. For more information, go to: <https://www.calrecycle.ca.gov/Electronics/Consumer>

Premium Care - Advanced Support from Real People. Real Fast.



REAL PERSON

Choose how you want to reach us – through phone, chat, or email – our expert technicians will take care of your device issues.



REAL FAST

Highly trained technicians will provide you real-time solutions, whatever the issue, on your first contact. If the issue can't be solved remotely, our team will schedule a repair via depot / carry-in support to resolve your issue.



HASSLE FREE

'Getting started' and 'how-to' assistance for hardware and software. Easy solutions that are simple to reach – that's how Premium Care delivers you the ideal support experience.

Accidental Damage Protection One - Protection for your Tablet from the unexpected.

Avoid the hassles of unexpected damage & repair costs. With coverage for drops, spills, electric surges, and broken LCD screens, accidental damage protection makes it easy to repair to your Tablets, permitting a single repair during the coverage period.

Base Warranty - Included with the system you purchase with default 1-year coverage window.

Lenovo Warranty Extensions & Upgrades (up to 3 years duration)

- Gain complete peace of mind by extending your base warranty to up to 3 years and minimize unexpected repair costs.

- Pick up & return courier / Depot support
- Replaceable unit service*

*Applicable in some regions only. Please check with your local services team for more details.

Lenovo may not offer the products, services or features discussed in this document in all regions. Lenovo may withdraw an offering at any time. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.



Lenovo

PSREF
Product Specifications
Reference