

# Dual M.2 PCIe SSD Adapter Card - x8 / x16 Dual NVMe or AHCI M.2 SSD to PCI Express 3.0 - M.2 NGFF PCIe (M-Key) Compatible - Supports 2242, 2260, 2280 - RAID & JBOD - Mac & PC

Product ID: PEX8M2E2



Upgrade your system speed and performance with this Dual M.2 PCIe SSD Adapter. It lets you add two high performance, enterprise-class PCIe 3.0 M.2 SSDs (NVMe and AHCI) into the PCIe 8-lane or larger slot of your desktop workstation or server.

## Boost System Performance

The expansion card lets you take full advantage of the fast performance and compact size of PCIe M.2 internal solid-state drives. With the M.2 PCIe based drives in place, the adapter increases your storage capacity and gives your computer a significant speed boost, enhancing data transfer rates.

## Access two M.2 PCIe SSDs simultaneously

The dual M.2 to PCIe expansion card employs a high-speed ASM2824 switch, allowing you to access two drives at the same time. Since the adapter card does not rely on PCIe bifurcation, it can easily be integrated into all systems, new and legacy.

The M.2 PCI express adapter also gives you the flexibility to access your M.2 PCIe SSDs individually. Or, you can utilize software RAID to build a RAID array to add redundancy or enhance system performance.

## Wide System Compatibility

The adapter connects directly to your computer motherboard to support two PCIe M.2 SSDs through a x8 PCIe expansion slot. The adapter is compatible with PCIe 3.0 motherboards and is backward compatible with PCIe 2.0 and PCIe 1.0.

## Supports a Wide Range of PCIe M.2 SSDs

The PCIe M.2 NGFF (M Key) adapter supports PCIe 3.0 NVMe and PCIe-AHCI M.2 SSDs including 2242, 2260, and 2280 drives, supporting the most common drive sizes: 42, 60, and 80 mm lengths.

## Easy to Install

The expansion card comes with a full-profile bracket pre-installed, and includes a half-height / low-profile bracket, for installation in small form-factor computers.

## Vented Brackets

Vented brackets on the PCIe M.2 NGFF SSD adapter card increases air flow to assist in heat dissipation.

The TAA compliant PEX8M2E2 is backed by a StarTech.com 2-year warranty and free lifetime technical support.

### Certifications, Reports and Compatibility



### Applications

- Connect two PCIe M.2 SSDs to your desktop computer or server to boost system speed and increase internal data storage
- Get ultra-fast data access, ideal for high-performance workstations
- Install your operating system on an M.2 PCIe based drive for fast access, while keeping larger platter drives available for bulk storage

### Features

- **HIGH PERFORMANCE:** Install 2 PCIe 3.0 M.2 SSDs (NVMe or AHCI) into your workstation or server for read/write speeds up to 3GB/s and 2.8GB/s for single-drives or 2.4GB/s and 1.42GB/s (per drive) for 2
- **WIDE COMPATIBILITY:** Dual M.2 PCIe SSD adapter card was extensively tested to ensure compatibility w/ Samsung 970 evo, 950 Pro, SM951, & other 2242, 2260, 2280mm PCIe M-Key M.2 NGFF SSDs (NVMe or AHCI)
- **BACKWARD COMPATIBILITY:** Compatible w/ PCIe 1.0 & 2.0 and x8 or x16 slots, PCIe bifurcation is not required. Works with all workstation and server OS's such as Windows, Linux, and macOS incl. legacy.
- **RAID FUNCTIONALITY:** M.2 PCI Express adapter lets you use SSDs individually or in a storage pool using OS or 3rd party RAID software & supports RAID 0, 1, SPAN, JBOD for tiered/hybrid storage
- **VENTED DUAL-PROFILE BRACKETS:** Pre-installed full profile bracket with low-profile (half-height) bracket in box & vented design for better cooling, avoiding drive throttling and improving reliability.

<b>Hardware</b>	Warranty	2 Years
	Bus Type	PCI Express
	Chipset ID	ASMedia - ASM2824
	Compatible Drive Types	M.2 (PCIe, AHCI, M-Key, NGFF)
		M.2 (PCIe, NVMe, M-Key, NGFF)
	Drive Installation	Fixed
	Drive Size	22m - M.2 NGFF
	Interface	PCI Express x8
	Number of Drives	2
	Supported Drive Height(s)	2242
2260		
2280		
<b>Performance</b>	Hot Swap Capability	No
	Insertion Rating	60 cycles
	MTBF	3336103 hours
	Type and Rate	PCI Express 3.0 (8 Gbps)
<b>Connector(s)</b>	Drive Connectors	2 - M.2 (PCIe, M-Key, AHCI/NVMe, NGFF)
	Host Connectors	1 - PCI Express x8 Male
	Other Interface(s)	2 - IDC (2 pin, Motherboard Header)
<b>Software</b>	OS Compatibility	OS independent; No software or drivers required
<b>Environmental</b>	Humidity	15% ~ 90% RH
	Operating Temperature	0°C to 70°C (32°F to 158°F)
	Storage Temperature	-25°C to 70°C (-13°F to 158°F)
<b>Physical Characteristics</b>	Color	Red
	Product Height	69.000
	Product Length	6.3 in [15.9 cm]
	Product Width	16.000
	Weight of Product	88.000
<b>Packaging Information</b>	Package Height	1.6 in [40 mm]
	Package Length	8.5 in [217 mm]

	Package Width	6.2 in [157 mm]
	Shipping (Package) Weight	7.1 oz [201 g]
<b>What's in the Box</b>	Included in Package	1 - x8 PCI Express to Dual M.2 PCIe SSD Adapter 1 - Low-Profile Bracket 1 - Full-Profile Bracket (Pre-installed) 2 - SSD Standoff and Installation Screws 1 - Quick-Start Guide

Product appearance and specifications are subject to change without notice.