

GV-SD3732-IR (33x) 3 MP H.265 Low Lux WDR Pro Outdoor IR IP Speed Dome



- 1/2.8" progressive scan low lux CMOS sensor
- Min. illumination at 0.003 lux
- Triple streams from H.265, H.264 or MJPEG
- Up to 30 fps at 2048 x 1536, 60 fps at 1920 x 1080
- 33x optical zoom and unlimited digital zoom
- Intelligent IR
- IR distance up to 150 m (500 ft)
- Day and night function (with removable IR-cut filter)
- Two sensor inputs and one alarm output
- Wide Dynamic Range Pro (WDR Pro)
- Vandal resistance (IK10 for metal casing)
- Ingress protection (IP66)
- Wide temperature tolerance (-40°C ~ 70°C / -40°F ~ 158°F)
- Support for TV-out
- Two-way audio
- Built-in micro SD card slot (SDHC/SDXC, Class 10) for local storage
- DC 24V / AC 24V
- Pan 360° endlessly
- Tilt from -15° to 90°
- Pan and tilt speed of up to 300°/sec and 240°/sec, respectively
- PTZ movement (Preset, Auto Pan and Patrol)
- PTZ patrol by schedule
- Smart settings (Cross line, Intrusion, Auto tracking)
- Intelligent Mark
- Auto focus
- 3D noise reduction
- Motion detection
- Privacy mask
- ONVIF (Profile G, S, T) conformant

Introduction

The GV-SD3732-IR is an outdoor network PTZ camera that offers 33x optical zoom and unlimited digital zoom, capable of showing smooth live view with great details. This camera can simultaneously deliver three video streams in resolutions up to 2048 x 1536 at 30 fps. In low-light environments, night vision is enhanced with its high-power LEDs, which allow up to 150 m (500 ft) effective IR distance. The camera can process scenes with contrasting intensity of lights and produce clear image using the built-in WDR Pro. The GV-SD3732-IR supports H.265 video codec to achieve better compression ratio while maintaining high quality pictures at reduced network bandwidths.


Wide surveillance coverage is made possible with 360° endless panning and -15° $^{\sim}$ 90° tilting capacity. PTZ functions such as Preset, Auto Pan, and Patrol can be programmed and activated by schedule. The GV-SD3732-IR supports pan/tilt speeds ranging from a fast patrol of 240° per second to a slow ramble of 0.1° per second with 0.1° pan accuracy for fast and accurate tracking ability.

GV-SD3732-IR February 4, 2020

^{*} No memory card slot & local storage function for Argentina



Dimensions



Specifications

Specifications			
Camera			
Image Sensor		1/2.8" progressive scan low lux CMOS	
Optical Zoom		33x	
Digital Zoom		Unlimited	
Picture Elements		2048 (H) x 1536 (V)	
Minimum	Color	0.003 Lux (F1.6, AGC ON)	
Illumination	IR ON	0 Lux	
Electronic Shutter		Auto / Manual (1/6 ~ 1/100000 sec)	
White Balance		Auto / Manual	
Iris Control		Auto / Manual	
AGC control		Auto / Manual	
S/N Ratio		55 dB	
WDR		WDR Pro	
Dynamic Range		Up to 120 dB	
Optical Lens			
Megapixel		Yes	
Day / Night		Yes (with removable IR-cut filter)	
Focal Length		4.5 ~ 148.5 mm	
Maximum Aperture	2	F/1.6	
Horizontal FOV		62.93° ~ 3.51°	
	Focus	Auto / Manual	
Operation	Zoom	33x	
	Iris	Auto / Manual	
IR LED Quantity		10 IR LEDs	
Max. IR Distance		150 m (500 ft)	
Video			
Video Compression	l	H.265, H.264, MJPEG	
Video Streaming		Triple streams from H.265, H.264 or MJPEG	
Main Stream		2048 x 1536 (Default), 1920 x 1080	
Video Resolution	Sub Stream	1920 x 1080, 1280 x 720, 720 x 576, 704 x 288, 640 x 360 (Default), 352 x 288	
	Third Stream (Closed by Default)	720 x 576, 704 x 288, 640 x 360, 352 x 288	
Frame Rate		30 fps at 2048 x 1536 (60 / 50 Hz), 60 fps at 1920 x 1080 (60 / 50 Hz) * The frame rate and performance may vary depending on the number of connections and data bitrates (different scenes).	
Video Analytics		Motion Detection, Tampering Alarm, Audio Detection, Cross Line, Intrusion, Object	

- 2 -



Audi		Moving, Object Left, Face Detection, People Counting, Auto Tracking *Tampering alarm, audio detection, cross line, intrusion, object moving, object left, face detection, people counting and auto tracking are only accessible through the camera's Web interface, which can be used to trigger alerts such as e-mail and FTP	
Audio			
Audio Compressi	on	G.711	
Audio Support		Two-way Audio (external microphone and speaker required)	
Network			
Interface		10/100 Ethernet	
Protocol		802.1x, ARP, DHCP, DDNS, DNS, DynDNS, FTP, HTTP, HTTPS, ICMP, IGMP, IPv4, NTP, PPPoE, QoS, RTCP, RTP, RTSP, SMTP, SNMP, TCP, UDP, UPnP, ONVIF (Profile G, S, T)	
Mechanical			
	Power	3-pin terminal block (DC 24V / AC 24V, 2.5A)	
	Ethernet	10/100 Base-T, RJ-45 connector	
Connectors	Audio	1 in (Audio In Wire); 1 out (Audio Out Wire) *The Audio In port only supports microphones with power supply.	
Connectors	Local Storage	Micro SD card slot (SDHC / SDXC, Class 10) *UHS-I and UHS-II card types are not supported.	
	TV-Out	BNC connector	
	Digital I/O	I/O wires	
Operation			
Pan Travel		360° endless	
Tilt Travel		-15° ~ 90°	
Manual Speed	Pan	0.1° ~ 240°/s	
ivialidai Speed	Tilt	0.1° ~ 160°/s	
Preset Speed	Pan	300°/s	
rieset speed	Tilt	240°/s	
D	Max. Number	255	
Presets	Accuracy	0.1°	
	Max. Number	16	
Patrol	Max. Actions Allowed	32	
OSD		8	
Privacy Mask		24	
Proportional Pan	& Tilt	Auto (Pan and tilt speed proportional to zoom ratio)	
Automatic Functi		Preset, Patrol (Including Auto Pan)	
Mechanical Flip	011	Yes	
Digital Slow Shut	tor	On / Off	
Motion Detection		On / Off	
Wide Dynamic Ra		On / Off	
	anical IR Cut Filter	On / Off	
	arrical in Cut i liter	·	
Image Rotation		Normal, Flip Vertical, Flip Horizontal, 180°, 90° Clockwise, 90° Anti-clockwise 0 ~ 255	
3D Noise Reductio	OII	2 Inputs, dry contact, NO / NC	
Alarm	Digital I/O	1 Relay Output (1A 30V DC / 0.3A 125V AC)	
Aldilli	Reaction	Alarm Output, PTZ to Preset, Trigger Storage	
Conoral	Reaction	Alaim Output, P12 to Preset, Trigger Storage	
General Operating Temps	rature	-40°C ~ 70°C (-40°F ~ 158°F)	
Operating Temperature Fan-On		Constantly On	
Humidity		·	
Dimensions		20% ~ 90% (non-condensing)	
Weight		Ø 227 x 359.4 mm (8.94" x 14.15")	
		5.4 kg (11.9 lb)	
Power Consumption		24V AC / 24V DC	
Power Consumption		52.5 W	
Ingress Protection		IP66	
Vandal Resistance	e	IK10 for metal casing	
Regulatory		CE, FCC, RoHS, UL compliant	

GV-SD3732-IR February 4, 2020

- 3 -



Web Interface		
Installation Management	Web-based configuration	
Maintenance	Firmware upgrade through Web Browser or Utility	
Access from Web Browser	Live View, Playback, Video Recording, PTZ Control, Preset, Patrol, Image Quality, Bandwidth Control, Image Snapshot, Two-way Audio, Digital Zoom, 3D Positioning (Optical Zoom), Text Overlay, Image Masking, Intelligent Mark, Cross Line, Intrusion, Auto Tracking, PTZ Remote Control	
Language	Czech, English, French, German, Hungarian, Italian, Japanese, Polish, Portuguese, Russian, Spanish, Traditional Chinese	
Applications		
Software Supported	GV-VMS (V17.1.0.100), GV-DVR / NVR (V8.7.4.0), GV-Control Center (V3.5.0.0), GV-Recording Server / Video Gateway (V1.3.0.0), GV-Edge Recording Manager (V1.3.0.0), GV-Redundant / Failover Server (V1.1.0.0) *It is required to apply patch files to all the supported software except for GV-VMS (V17.1.0.100).	
Smart Device Access	cess GV-Eye for iOS and Android	
Live Viewing	Browser (IE, Edge, Chrome, Firefox, Safari), Mobile App	

Note:

- 1. Do not use clothes or any ordinary material to clean the camera cover since they may result in scratches.
- 2. Mind the following when using an inserted memory card for recording:
 - Recorded data on the memory card can be damaged or lost if the data are accessed while the camera is under physical shock, power interruption, memory card detachment or when the memory card reaches the end of its lifespan. No guarantee is provided for such causes.
 - The stored data can be lost if the memory card is not accessed for a long period of time. Back up your data periodically if you seldom access the memory card.
 - Memory cards are expendable and their durability varies according to the conditions of the installed site and how they are used. Back up your data regularly and replace the memory card annually.
 - To avoid power outage, it is highly recommended to apply a battery backup (UPS).
 - For better performance, it is highly recommended that you use a micro SD card of SDHC/SDXC, Class 10.
 - Replace the memory card when its read/write speed is lower than 6 MB/s or when the memory card is frequently undetected by the camera.
- 3. Specifications are subject to change without notice.

Packing List

- 1. GV-SD3732-IR Speed Dome
- 2. 24V AC Power Adapter
- 3. M4 Hex Key
- 4. Waterproof Rubber Set
- 5. Waterproof Guidelines
- 6. Download Guide
- 7. Warranty Card

Accessories

Model No.	Name	Details
GV-Mount104	Straight Tube Kit	Dimensions: 219 x 125 x 332 mm (8.6" x 4.9" x 13.1") Weight: 1.8 kg (3.97 lb)
GV-Mount105	Straight Tube and Junction Box Kit	Dimensions: 256 x 256 x 297 mm (10.1" x 10.1" x 11.7") Weight: 6.2 kg (13.67 lb)

- **4** -*GV-SD3732-IR February 4, 2020*



Model No.	Name	Details
GV-Mount210	Pendant Tube	Dimensions: 200 x 140 x 249 mm (7.9" x 5.5" x 9.80") Weight: 1.1 kg (2.43 lb)
GV-Mount208-3	Swan Neck Mount	Dimensions: 1043 x 519 x 256 mm (41.06 x 20.43 x 10.08") Weight: 10.6 kg (23.37 lb)
GV-Mount300-1	Convex Corner Adapter Kit	Dimensions: 238.6 x 395.2 x 210 mm (9.4" x 15.5" x 8.2") Weight: 4.27 kg (9.41 lb)
GV-Mount310-1	Concave Corner Adapter Kit	Dimensions: 111.2 x 369.9 x 210 mm (4.37" x 14.5" x 8.2") Weight: 2.96 kg (6.53 lb)
GV-Mount400-1	Pole Mount Bracket Kit (Ø 4" ~ 6")	Bracket: 68.4 x 240 x 163 mm (2.69" x 9.44" x 6.41") Weight: 1.70 kg (3.75 lb) Steel Strap Diameter: Ø 4" ~ 6"
GV-Mount410-1	Pole Mount Bracket Kit (Ø 6" ~ 7.5")	Bracket: $68.4 \times 240 \times 163 \text{ mm}$ (2.69" $\times 9.44$ " $\times 6.41$ ") Weight: 1.70 kg (3.75 lb) Steel Strap Diameter: Ø 6" \sim 7.5"
GV-Mount501	Convex Corner Box Mount	Dimensions: 136 x 256 x 256 mm (5.4 x 10.1 x 10.1") Weight: 4.8 kg (10.6 lb)

- 5 -



Model No.	Name	Details
GV-Mount702	Extension Tube	Four options are available. Dimensions: Ø 5.4 x 10 or 20 or 30 or 50 cm (Ø 2.1" x 3.9" or 7.9" or 11.8" or 19.7") Weight: 180 g or 390 g or 550 g or 800 g (0.4 lb or 0.86 lb or 1.21 lb or 1.76 lb)

- 6 -GV-SD3732-IR February 4, 2020