

# Chevron Plus

High Back  
Multi-Tilter  
MVL2371-3



## Features

- Fully adjustable G5 arms can raise + lower in height, widen to match shoulder breadth, and rotate to support forearms in various positions
- Sliding seat depth adjustment
- Height adjustable back (concealed ratchet)
- Integrated headrest
- Infinite position tilt lock control allows user to lock the chair at any angle for maximum comfort and support
- Independent, infinite position back and seat angle adjustment, including forward tilt
- Standard with hard floor casters
- Weight capacity of 300 lbs.

## Upholstery Options

Available in all grade 1 seating textiles or bonded leather/polyurethane combination



## Specifications

Dimensions.....26" W x 25" D x 46.5" H  
Weight.....48 lbs / 21.8 kg  
Volume.....10.5 ft<sup>3</sup> / 0.3 m<sup>3</sup>

## Ergonomic Features

[click here for more info](#)

Tension Adjustment	Arm Height
Tilt Lock	Waterfall Seat
Seat Height	Contoured Cushion
Back Height	Width Adjustable Arms
Seat Depth	Arm Rotation
Forward Seat Angle	Centre Tilt
Back Angle	



MEMBER  
BIFMA



All chairs in this series are tested to meet or exceed ANSI / BIFMA seating standards. These test procedures evaluate seating for function, safety, durability and structural adequacy. Your assurance of a quality product. As a result, all of this series' seating products proudly carry a Limited Lifetime Warranty. We have made every effort to ensure accuracy. Specifications are subject to change.

**BASICS**