

Basics Chevron Ultra

High Back 24 Hour
Multi-Tilter
TS1120-3



Features

- Heavy duty model for triple-shift applications
- Heavy duty mechanism and 3" W back upright
- Clear vinyl bumper guards included to protect the chair back
- Fully adjustable G5 arms can raise + lower in height, widen to match shoulder breadth, and rotate to support forearms in various positions
- High comfort seat made from Ultracell high density, highly resilient foam
- Sliding seat depth adjustment
- Independent, infinite position back and seat angle adjustment, including forward tilt
- Adjustable back height with 5 1/4" adjustability (concealed ratchet)
- Standard with hard floor casters
- Weight capacity of 350 lbs.

Upholstery Options

Available in all seating textiles



Specifications

Dimensions.....26" W x 25" D x 45" H
Weight.....64 lbs / 29.1 kg
Volume.....10.5 ft³ / 0.3 m³

[click here for more info](#)

Ergonomic Features

Tension Adjustment	Arm Height
Tilt Lock	Waterfall Seat
Seat Height	Contoured Cushion
Back Height	Width Adjustable Arms
Seat Depth	Arm Rotation
Forward Seat Angle	Centre Tilt
Back Angle	



MEMBER
BIFMA



All chairs in this series are tested to meet or exceed ANSI / BIFMA seating standards. These test procedures evaluate seating for function, safety, durability and structural adequacy. Your assurance of a quality product. As a result, all of this series' seating products proudly carry a Limited Lifetime Warranty. We have made every effort to ensure accuracy. Specifications are subject to change.

BASICS