


8-Port USB Smart Charging Station - USB-A Quick Charge 3.0, USB-A BC 1.2, USB-C PD Charging, 120W Max

MODEL NUMBER: U280-008-CQC-ST



Charges and organizes up to 8 mobile devices, ranging from smartphones and tablets to MacBooks and Amazon Kindles, at the same time.

Features

Flexible USB Smart Charging Station Charges Up to 8 Mobile Devices at the Same Time

At home or in the office, this USB charging station provides enough power and ports to keep your devices at high capacity. No more peering behind furniture to find an available outlet or unplugging one device to charge another. This compact charging station charges up to eight devices at the same time, including smartphones, tablets, MacBooks, Chromebooks and Amazon Kindles, at a maximum of 120W. It doesn't require a computer, so you can take it anywhere AC power is available.

Removable Brackets Allow Convenient and Customizable Storage

Five small and four large brackets are included to hold multiple devices during charging or to store them and keep them organized when not in use. The brackets easily insert into slots built into the charger's surface. You can customize storage space according to the number and size of the connected devices, ranging from smartphones and AirPods to larger laptops and tablets.

Provides Plenty of Power to Keep Your Devices at Capacity

Six BC 1.2-compliant USB-A ports are each capable of delivering up to 5V 2.4A (12W) of power*, enough for fast-charging most smartphones, tablets and other mobile devices. Built-in auto-sensing lets the port detect the connected device and automatically adjust the required power level accordingly for optimum charge and compatibility.

*When all ports are being used simultaneously the U280-008-CQC-ST can handle up to 5V 6.2A (31W). After 6.2A the unit will go into overload protection and drop the port causing the overload.

Quick Charge 3.0 Can Charge Up to 4 Times Faster than Conventional 5W Chargers

Another USB-A port features Qualcomm Quick Charge 3.0 Class A technology up to 12V 1.5A. Connect a QC 3.0-compatible device for speedy charging—up to 80% battery capacity in as little as 35 minutes.

USB PD 3.0 Charging Is Ideal for Laptops and Other Battery-Heavy Devices

For devices that are even more powerful, the USB-C port provides up to 20V 3A (60W) for battery-intensive devices like the MacBook Pro or Chromebook Pixel.

Adjustable Design Allows Deployment in 4 Different Configurations

Using the included detachable base and hardware, you can mount the charger to the wall or rest it vertically on a flat surface, such as a desk or workbench. You can also place it flat on a horizontal surface, or unfold it in order to install the included dividing brackets for organized charging.

Highlights

- 6 USB-A BC 1.2-compliant ports provide up to 5V 2.4A of charging power each
- USB-A Quick Charge 3.0 port provides up to 12V 1.5A to QC-compatible devices
- USB-C PD Charging port provides up to 20V 3A of charging power to compatible devices
- Protects connected devices with built-in safeguards against overheating and overvoltage
- Sets up in 4 different configurations, including wall-mount and flat with storage brackets

Applications

- Charge up to 8 smartphones, notebooks, tablets, Amazon Kindles or other USB devices at the same time
- Perfect for homes with busy families, dorm rooms and offices with multiple mobile devices

Package Includes

- U280-008-CQC-ST 8-Port USB Charging Station
- External power supply (Input: 100–240V, 50/60 Hz, 3.0A; Output: 20V 6A)
- Detachable C5 to NEMA 5-15P power cord, 5 ft.
- (9) Removable storage brackets
- Mounting stand
- Mounting hardware



Easy to Use with the Included Power Cord

To charge your USB devices, simply plug the included external dual-voltage (100V–240V) power supply into any standard NEMA 5-15R or 1-15R outlet, and connect your devices to the available USB ports. The charger protects against overheating, overcurrent and overcharging. A green LED indicates the unit is turned on and receiving AC power.

- Quick Start Guide

Specifications

OVERVIEW	
UPC Code	037332250612
Over Current Protection	Yes
OUTPUT	
Charging Ports / Amps	(1) 1.5A; (6) 2.4A; (1) 3A
Overload Protection	Yes
Charging Method	USB
INPUT	
Voltage Compatibility (VAC)	100; 110; 120; 125; 127; 200; 208; 220; 230; 240
External Power Supply Input Specs (V / Hz / A)	100-240V, 50/60Hz, 3.0A Max
External Power Supply Output Specs (V / A)	20V / 6A
External Power Supply Cord Length (ft.)	3
External Power Supply Cord Length (m.)	1
External Power Supply Plug(s)	NEMA 5-15P North America
External Power Supply Certifications	CCC; CE; GS; RoHS; TUV; cUL
Bus Powered	No
Product Length (in.)	6.97
Product Length (cm.)	17.7
Product Length (ft.)	0.58
Product Length (m.)	0.177
BATTERY	
Battery Charging (1.2 Port)	Yes
VOLTAGE REGULATION	
Overvoltage Correction	Yes



USER INTERFACE, ALERTS & CONTROLS	
LED Indicators	Green (Static) = Powered; Green (Flickering) = Overcurrent Protection, Attention required
CHARGING	
Overcharge Protection	Yes
Total Charging Amps	6
PHYSICAL	
Color	Black
Material of Construction	Plastic
Unit Dimensions (hwd / cm)	1.93 x 11.42 x 17.7
Unit Dimensions (hwd / in.)	0.76 x 4.5 x 6.97
Unit Packaging Type	Box
Unit Weight (kg)	0.56
Unit Weight (lbs.)	1.235
ENVIRONMENTAL	
Operating Temperature Range	41°F to 95°F (5°C to 35°C)
Storage Temperature Range	-4°F to 122°F (-20°C to 50°C)
Relative Humidity	20% ~ 80%
CONNECTIONS	
Number of Charging Ports	8
Ports	8
Side A - Connector 1	NEMA 5-15P
Side B - Connector 1	(7) USB A (FEMALE)
Side B - Connector 2	(1) USB Type-C (FEMALE)
FEATURES & SPECIFICATIONS	
USB Hub Ports	Yes
Number of USB Hub Ports	8
Driver Required	No
USB Power Delivery (PD) Charging Support	Yes
Quick Charge Compliant	3.0
Technology	USB
USB Power Delivery (PD) Charging Specification	2.0



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

CERTIFICATIONS	
Certifications	Tested to RoHS, REACH, FCC
WARRANTY	
Product Warranty Period (Worldwide)	3-year limited warranty

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>