

# ThinkCentre M75s SFF 11AV0017US

**Product**

ThinkCentre M75s SFF

**Region**

NA

**Country/Region**

USA

**Machine Type**

11AV

**TopSeller**

TopSeller

**Processor**

AMD Ryzen 7 PRO 3700 (8C / 16T, 3.6 / 4.4GHz, 4MB L2 / 32MB L3)

**Graphics**

AMD Radeon 520 2GB GDDR5

**Chipset**

AMD PRO 560 FCH

**Memory**

1x 8GB DDR4-2666

**Storage**

1x 512GB SSD M.2 2280 PCIe x4 NVMe Opal

**Optane Memory**

None

**Optional Bay**

None

**Front Access HDD**

None

**Optical**

DVD±RW

**Media Reader**

None

**Speaker**

1Wx1

**Ethernet**

Integrated 100/1000M

**WLAN + Bluetooth**

RTL8822CE 11ac, 2x2 + BT5.0

**Optional Rear Ports**

None

**Chassis Intrusion Switch**

None

**Chassis E-Lock**

None

**Kensington Cable Lock**

None

**Smart Cable Clip**

None

**Dust Filter**

None

**Carry Handle**

None

**Color**

Black

**Stand**

Stand

**Keyboard**

USB Traditional Keyboard, Black, English

**Mouse**

USB Calliope Mouse

**Power Supply**

210W 85%

**TUV Low Noise**

None

**Monitor Cable**

None

**System Management**

DASH

**Operating System**

Windows 10 Pro 64, English

**Bundled Software**

None

**Base Warranty**

3-year, Onsite

**Bundled Service**

None

**EAN / UPC / JAN**

194632345667

**End of Support**

2025-12-29

**Announce Date**

2019-11-29

**Recommended Services****Best**

4Y Lenovo Protect (Premier Support + Keep Your Drive + Accidental Damage Protection) (5PS0N73191)

**Better**

4Y Lenovo Support (Premier Support + Keep Your Drive) (5PS0N73243)

**Good**

3Y Premier Support Upgrade from 3Y Onsite (5WS0U26647)

**Notes:****California Electronic Waste Recycling Fee**

In California, per state law, Lenovo charges an electronic waste recycling fee on this covered device at the time of sale of the product. For more information, go to: <https://www.calrecycle.ca.gov/Electronics/Consumer>

[WWW.LENOVO.COM](https://www.lenovo.com)

Lenovo may not offer the products, services or features discussed in this document in other countries. Lenovo may withdraw an offering at any time. Information is subject to change without notice. Consult your local representative for information on offerings available in your area.

Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.



<https://psref.lenovo.com>

Visit psref website for the latest version of Product Specifications Reference.

© Lenovo, 2020. All rights reserved.



# ThinkCentre M75s-1 SFF Platform Specifications

Product Specifications Reference (PSREF)



Processor	AMD Athlon PRO and Ryzen 3 / 5 / 7 PRO series processor						Ethernet	Gigabit ethernet, Realtek RTL8111EPV, Wake on LAN®																																										
	<table border="1"> <thead> <tr> <th>Processor</th> <th>Cores / Threads</th> <th>Frequency (Base/Max)</th> <th>L2 / L3 Cache</th> <th>Memory Support (Up to)</th> <th>Integrated Graphics</th> </tr> </thead> <tbody> <tr> <td>Athlon PRO 300GE</td> <td>2 / 4</td> <td>3.4 / 3.4</td> <td>1MB / 4MB</td> <td>DDR4-2666</td> <td>Radeon Vega 3</td> </tr> <tr> <td>Ryzen 3 PRO 3200G</td> <td>4 / 4</td> <td>3.6 / 4.0</td> <td>2MB / 4MB</td> <td>DDR4-2933</td> <td>Radeon Vega 8</td> </tr> <tr> <td>Ryzen 5 PRO 3400G</td> <td>4 / 8</td> <td>3.7 / 4.2</td> <td>2MB / 4MB</td> <td>DDR4-2933</td> <td>Radeon Vega 11</td> </tr> <tr> <td>Ryzen 5 PRO 3600</td> <td>6 / 12</td> <td>3.6 / 4.2</td> <td>3MB / 32MB</td> <td>DDR4-3200</td> <td>None</td> </tr> <tr> <td>Ryzen 7 PRO 3700</td> <td>8 / 16</td> <td>3.6 / 4.4</td> <td>4MB / 32MB</td> <td>DDR4-3200</td> <td>None</td> </tr> <tr> <td>Ryzen 9 PRO 3900</td> <td>12 / 24</td> <td>3.1 / 4.3</td> <td>6MB / 64MB</td> <td>DDR4-3200</td> <td>None</td> </tr> </tbody> </table>						Processor	Cores / Threads	Frequency (Base/Max)	L2 / L3 Cache	Memory Support (Up to)	Integrated Graphics	Athlon PRO 300GE	2 / 4	3.4 / 3.4	1MB / 4MB	DDR4-2666	Radeon Vega 3	Ryzen 3 PRO 3200G	4 / 4	3.6 / 4.0	2MB / 4MB	DDR4-2933	Radeon Vega 8	Ryzen 5 PRO 3400G	4 / 8	3.7 / 4.2	2MB / 4MB	DDR4-2933	Radeon Vega 11	Ryzen 5 PRO 3600	6 / 12	3.6 / 4.2	3MB / 32MB	DDR4-3200	None	Ryzen 7 PRO 3700	8 / 16	3.6 / 4.4	4MB / 32MB	DDR4-3200	None	Ryzen 9 PRO 3900	12 / 24	3.1 / 4.3	6MB / 64MB	DDR4-3200	None	Ethernet (Opt.)	None
	Processor	Cores / Threads	Frequency (Base/Max)	L2 / L3 Cache	Memory Support (Up to)	Integrated Graphics																																												
	Athlon PRO 300GE	2 / 4	3.4 / 3.4	1MB / 4MB	DDR4-2666	Radeon Vega 3																																												
	Ryzen 3 PRO 3200G	4 / 4	3.6 / 4.0	2MB / 4MB	DDR4-2933	Radeon Vega 8																																												
	Ryzen 5 PRO 3400G	4 / 8	3.7 / 4.2	2MB / 4MB	DDR4-2933	Radeon Vega 11																																												
	Ryzen 5 PRO 3600	6 / 12	3.6 / 4.2	3MB / 32MB	DDR4-3200	None																																												
Ryzen 7 PRO 3700	8 / 16	3.6 / 4.4	4MB / 32MB	DDR4-3200	None																																													
Ryzen 9 PRO 3900	12 / 24	3.1 / 4.3	6MB / 64MB	DDR4-3200	None																																													
Manageability							DASH 10/1.1																																											
Security chip							Discrete TPM 2.0, TCG Certified																																											
Security features							<ul style="list-style-type: none"> <li>Security slot (in rear for optional Kensington® MicroSaver® cable)</li> <li>Padlock loop</li> <li>Smart USB protection, allows keyboard/ mouse only, blocks all storage devices</li> <li>Optional smart cable clip to physically lock both keyboard and mouse</li> </ul>																																											
							<ul style="list-style-type: none"> <li>Power-on password</li> <li>Administrator password</li> <li>Hard disk password</li> <li>Boot sequence control</li> <li>Boot without keyboard and mouse</li> <li>Individual USB port disablement</li> <li>Optional chassis intrusion switch</li> </ul>																																											
Memory	64GB max, UDIMM, DDR4-2666*, four 288-pin DIMM sockets, non-ECC, dual-channel capable * System board supports up to DDR4-2666 memory, and memory may clock down to DDR4-1866, DDR4-2133 or DDR-2400 for lower capacity of memory controller in processor						Keyboard	<i>Some:</i> Lenovo Traditional Keyboard (USB connector), black <i>Some:</i> Lenovo Calliope Wireless Keyboard (2.4GHz via USB receiver), black <i>Some:</i> Lenovo Keyboard (PS/2 connector), black (only available via special bid)																																										
Storage	<i>Some:</i> Hard Drive / SATA 6.0Gb/s, 2.5" or 3.5", 5400 rpm or 7200 rpm <i>Some:</i> M.2 SSD (2242 / 2280) / PCIe NVMe, PCIe 3.0 x2 or PCIe 3.0 x4						Mouse	<i>Some:</i> Lenovo Calliope Mouse (USB connector), black <i>Some:</i> Lenovo Fingerprint Mouse (USB connector), Windows Hello support, black <i>Some:</i> Lenovo Calliope Wireless Mouse (2.4GHz via USB receiver), black <i>Some:</i> Lenovo Mouse (PS/2 connector), black (only available via special bid)																																										
Optical	<i>Some:</i> DVD-ROM SATA 1.5Gb/s Drive, slim (9.0mm) <i>Some:</i> DVD Burner (DVD±RW), SATA 1.5Gb/s Drive, slim (9.0mm)						Mechanical	<ul style="list-style-type: none"> <li>SFF (8.4L), black color; metal case</li> <li>(WxDxH) 3.6" X 11.4" X 13.5"; 92.5mm X 290.5mm X 343.5mm</li> <li>Approx. 13.2 lb (6.0 kg), weight may vary by configuration</li> <li>Toolless cover, disk, optical, and extension card removal</li> <li>Optional dust filter</li> </ul>																																										
Onboard SATA	Three onboard SATA 6.0Gb/s connectors, RAID 0/1 support (RAID preset only available via special bid model)							Bay 1: Slim external ODD bay Bay 2: 3.5", internal, HDD/SSD Bay 3: 2.5", internal, HDD/SSD (bay only comes with 2.5" 2nd disk) Slot 1: low-profile (length < 150mm, height < 68mm), PCIe 3.0 x16 Slot 2: low-profile (length < 150mm, height < 68mm), PCIe 2.0 x1 Slot 3: low-profile (length < 150mm, height < 68mm), PCIe 2.0 x1 Slot 4: low-profile (length < 150mm, height < 68mm), PCI 3.0 M.2 card slots: two (one for WLAN, one for SSD)																																										
Media reader	Optional 7-in-1 media reader						Floor Stand	Optional system floor stand for vertical orientation																																										
Graphics	<b>AMD Radeon™ Graphics in processor</b> (only for some processors), uses main memory, DirectX® 12, one VGA, two DisplayPort™ (Onboard VGA and DP ports are only available on the models with integrated graphics), supports 3 independent displays, works along with AMD discrete graphics to support more displays; <i>Max resolution:</i> 4096x2160 (DP) @60Hz; <i>Some:</i> <b>AMD Radeon™ 520</b> , DirectX 12, 2GB GDDR5, PCIe 3.0 x8 adapter, two DisplayPort, 30 watts (Max); <i>Max resolution:</i> 4096x2160 (DP) @60Hz						Power supply	<i>Some:</i> 180 watts, autosensing, 85% PSU <i>Some:</i> 210 watts, autosensing, 85% PSU <i>Some:</i> 260 watts, autosensing, 92% PSU (only available via special bid)																																										
Monitor cable	Optional DP to VGA, DP to DVI-D (single link), DP to dual DP, or DP to HDMI 1.4						Limited warranty	<b>1-year or 3-year, limited onsite service</b> / service upgrades available																																										
Chipset	<b>AMD PRO 560 FCH</b>						Preload	<b>Preloaded operating system</b> <i>Some:</i> Windows 10 Pro 64-bit <i>Some:</i> Windows 10 Home 64-bit <i>Some:</i> Windows 10 IoT Enterprise <i>Some:</i> Linux Ubuntu																																										
Front ports* (Std.)	2x USB 3.1 Gen2, 2x USB 3.1 Gen1, 1x microphone (3.5mm), 1x headphone (3.5mm)						Environment	ENERGY STAR® 7.0*, EPEAT™ Silver rating* (*not for non-OS models); ErP Lot 3; RoHS-compliant, WEEE																																										
Front ports* (Opt.)	<i>Optional:</i> 1x media reader						Accessories	For compatible accessories, please go to <a href="http://smartfind.lenovo.com">http://smartfind.lenovo.com</a>																																										
Rear ports* (Std.)	2x USB 3.1 Gen1 (one support Smart Power-On), 2x USB 2.0, 1x serial (9-pin), 1x ethernet (RJ-45), 1x VGA**, 2x DisplayPort**, 2x PS/2 ports (keyboard / mouse); 1x line-in (3.5mm), 1x line-out (3.5mm), 1x microphone (3.5mm)																																																	
Rear ports* (Opt.)	<i>Optional:</i> 2x USB 2.0, 1x parallel (25-pin), additional video ports available on optional graphics card																																																	
	* Depending on many factors, actual data transfer speed may be lower than theoretical speed ** only available on the models with integrated graphics																																																	
Audio support	High Definition (HD) Audio, Realtek ALC662 / optional internal speaker (1 watt )																																																	
WLAN	<i>Some:</i> 11ac wireless, M.2 Card, Realtek RTL8822CE (dual band), Wi-Fi + Bluetooth 5.0 combo adapter, 2x2 <i>Some:</i> 11ac wireless, M.2 Card, Qualcomm Atheros QCA6174A (dual band), Wi-Fi + Bluetooth 4.2 combo adapter, 2x2 <i>Some:</i> 11ac wireless, M.2 Card, Intel Wireless-AC 9260 (dual band), Wi-Fi + Bluetooth 5.0 combo adapter, 2x2																																																	
Bluetooth™	<i>Some:</i> Bluetooth 4.2 / 5.0 wireless, integrated in Wi-Fi + BT combo adapter																																																	

Note: The specifications above may not be available in all regions.

Lenovo, March 2020

# ThinkCentre M75s SFF

