

OVERVIEW

Basic rPDUs deliver reliable power to critical IT equipment within a rack or cabinet.

Benefits

- Reliable rack power distribution.
- Every unit is 100% tested for reliability and functionality.
- Simple and convenient configuration options for cord lengths and chassis colors.
- Standard three-year warranty, upgraded to a five-year warranty with product registration.



Part #: U1076

Model Number: DU00X1R1-12CF17-1S02A9H00-S

Category: Basic

Sub Category: Standard

Power Configuration: Variable, Max 11.0kW

Physical Configuration: 19in / 483mm, Horizontal

Product Summary: rPDU, Basic Standard, Max 11.0kW, Variable Power Configuration, Horizontal, (12) Combination C13/C19, Universal Input, Black Powder Coat.

Plug Form:



Universal Input

Receptacle:



Combination C13/C19
(Quantity: 12)

Chassis Color Options:



To discuss color options, contact your local sales representative.

Product Specification and Options

System Features

Quantity Of Inputs	1
Maximum Input Power (Defined by Facility Side Cable)	48A Single Phase, 240V Max, 11.0kW 24A 3 Phase DELTA, 240V Max, 8.6kW 16A Three Phase WYE, 240/415V Max, 11.0kW
Frequency	50/60Hz
Over Current Protection	(3) 16A Double Pole Magnetic Breakers (10kAIC Rated)
Switch	Breaker/Switch Combination

Power Entry Location	Left Rear
Plug Type	Universal Inlet
Receptacle/Socket Type #1	Combination C13/C19
- Quantity on Face	12
- Quantity per Breaker	4
- Circuit Color ID	3 Circuit = Orange, Green, Blue
- Style	Banks of 6
- Voltage per Receptacle/Socket	Defined by Facility Side Cable
Maximum Operating Temperature	60C / 140F
Heavy Steel - Powder Coat Finish	Black
Configuration	1U
Adjustable Mount Brackets	Yes
Product Warranty	5-year limited warranty if registered within 120 days of purchase, otherwise warranty defaults to 3 years
Certification/Agency Approvals	CE Marked
Certification/Agency Approvals	RoHS Compliant
Certification/Agency Approvals	UL Listed 60950
Chassis Dimensions (HxWxD)	1.72in x 17in x 9in / 44mm x 432mm x 229mm
Shipped Weight	16lbs (7.26kg)