

OVERVIEW

Metered rPDUs deliver reliable power to critical IT equipment within a rack or cabinet. Includes a local LED display to view real-time power data.

Benefits

- Avoid accidental overloads when deploying or moving critical server equipment with instant access to power consumption metrics on the local digital display.
- The local LED display provides real-time power data for instant feedback when deploying or moving critical IT equipment.
- Every unit is 100% tested for reliability and functionality.
- Simple and convenient configuration options for cord lengths and chassis colors.
- Standard three-year warranty, upgraded to a five-year warranty with product registration.



Part #: 11383VH

Model Number: VRELCN080-103I44TL6

Category: Metered

Sub Category: Standard

Power Configuration: 30A, 208V, 4.9kW

Physical Configuration: 17in / 432mm, Horizontal/Vertical

Product Summary: rPDU, Metered Standard, 30A, 208V, 4.9kW, Horizontal/Vertical, (4) IEC C13, (4) IEC C19, 10ft power cord with L6-30P, Black Powder Coat.

Monitoring: Power - Local (A, V, W, PF)
Digital RMS Scrolling Power Meter +/- 2% Accuracy with Full Scale 60Hz sine wave input

Plug Form:



L6-30P

Receptacle:



IEC C13
(Quantity: 4)



IEC C19
(Quantity: 4)

Chassis Color Options:



To discuss color options, contact your local sales representative.

Product Specification and Options

System Features

Monitoring	Power - Local (A, V, W, PF) Digital RMS Scrolling Power Meter +/- 2% Accuracy with Full Scale 60Hz sine wave input
Monitoring Level 1	Aggregate - Total Unit Monitoring
Quantity Of Inputs	1
Voltage	200-240V
Current	30A
VA per Input (Load Capacity)	4.9kW (208V)
Frequency	50/60Hz
Over Current Protection	(4) 15A Thermal Breakers
Switch	No
Power Cable Wire Gauge	10/3
Power Cable Length	10ft
Plug Type	NEMA L6-30P Twistlock
Combined Total Receptacle/Socket Quantity	8
Receptacle/Socket Type #1	IEC C13
- Quantity on Face	4
- Quantity per Breaker	2
- Style	Banks of 2
- Maximum Output per Receptacle/Socket	15A per receptacle bank
- Voltage per Receptacle/Socket	208V
Receptacle/Socket Type #2	IEC C19
- Quantity on Face	4
- Quantity per Breaker Pair	2
- Style	Individual
- Maximum Output per Receptacle/Socket	20A
- Voltage per Receptacle/Socket	208V
Continuous Operating Temperature Range	10-45C / 50-113F
Heavy Steel - Powder Coat Finish	Black
Configuration	17in / 432mm Vertical/Horizontal Rackmount
19in Panel Mount Brackets	Yes
SLB-4 Brackets	Yes
Country of Origin	USA, TAA Compliant and Buy American Act COTS Compliant
Product Warranty	5-year limited warranty if registered within 120 days of purchase, otherwise warranty defaults to 3 years
Certification/Agency Approvals	RoHS Compliant
Certification/Agency Approvals	UL & c-UL Listed Accessory 1950
Chassis Dimensions (LxWxD)	17.0in x 1.72in x 1.85in

Shipped Weight

7lbs (3.18kg)