

OVERVIEW

Upgradeable Metered rPDUs provide reliable power distribution to critical IT equipment within a rack or cabinet while delivering a view of real-time view of power usage from a local LED display.

Benefits

- With the Geist Upgradeable hot-swap technology, users may easily transform metered rPDUs to monitored rPDUs with the addition of the appropriate Interchangeable Monitoring Device (IMD).
- Avoid accidental overloads when deploying or moving critical server equipment with instant access to power consumption metrics on the local digital display.
- Every unit is 100% tested for reliability and functionality.
- Simple and convenient configuration options for cord lengths and chassis colors.



Part #: I10497

Model Number: MN01D4W1-36CF18-3TL15A0A10-S-A

Category: Metered

Sub Category: Upgradeable

Power Configuration: 30A, 208V DELTA, 8.6kW

Physical Configuration: 70in / 1778mm, Vertical

Product Summary:

rPDU, Metered Upgradeable, 30A, 208V DELTA, 8.6kW, Vertical, (36) Combination C13/C19, 10ft power cord with L15-30P, Black Powder Coat.

Monitoring:


Input Phase and Circuit/Breaker current monitoring. Local high visibility LED display.

Plug Form:



L15-30P

Receptacle:



Combination C13/C19
(Quantity: 36)

Chassis Color Options:



To discuss color options, contact your local sales representative.

Product Specification and Options

System Features

Monitoring

Input Phase and Circuit/Breaker current monitoring. Local high visibility LED display.

Monitoring Level 1	Aggregate - Total Unit Monitoring (kWh, W, VA, PF) Power Measurements Compliant with ANSI C12.1 and IEC 62053-21 at 1% Accuracy Class Requirements
Monitoring Level 2	Phase (AB, BC, CA) Monitoring (kWh, W, VA, PF, V, A) Line (A,B,C) Monitoring (A) Power Measurements Compliant with ANSI C12.1 and IEC 62053-21 at 1% Accuracy Class Requirements
Monitoring Level 3	Circuit / Breaker Monitoring (A) Circuit/Breaker Current Measurements Independently Tested and Verified at 2% Accuracy
Quantity Of Inputs	1
Voltage	200-240V Delta
Current	30A x 3 Phase DELTA
VA per Input (Load Capacity)	8.6kW (208V)
Frequency	50/60Hz
Over Current Protection	(3) 20A Double Pole Magnetic Breakers (22kAIC Rated)
Switch	Breaker/Switch Combination
Scrolling / Rotatable Digital Display	Yes
Power Cable Wire Gauge	10/4
Power Cable Length	10ft / 3m
Power Entry Location	Bottom Front
Plug Type	NEMA L15-30P Twistlock
Alternating Phase/Circuits	Yes
Receptacle/Socket Type #1	Combination C13/C19
- Quantity on Face	36
- Quantity per Breaker and Phase Combination	12
- Circuit Color ID	3 Circuit = Orange, Green, Blue
- Style	Banks of 6
- Voltage per Receptacle/Socket	208V
Internal RMS Voltage Sensor	Yes
Internal RMS Current Sensor	Yes
Maximum Operating Temperature	60C / 140F
Heavy Steel - Powder Coat Finish	Black
Configuration	Zero U
7938 Vertical Mounting Bracket Kit	Yes
Toolless Mounting Hardware - Center to Center Spacing	61.25in and 64.75in / 1556mm and 1645mm
Country of Origin	USA, TAA Compliant and Buy American Act COTS Compliant
Product Warranty	5-year limited warranty if registered within 120 days of purchase, otherwise warranty defaults to 3 years
Certification/Agency Approvals	RoHS Compliant
Certification/Agency Approvals	FCC Part 15 Class A Conformance
Certification/Agency Approvals	UL & c-UL Listed 62368-1

Chassis Dimensions (LxWxD)	70in x 2in x 2in / 1778mm x 51mm x 51mm
Shipped Weight	17lbs (7.71kg)