

CTL® Chromebook NL71/NL71X

Classic Clamshell with Optional X-panel

ctl.re/ctl-chromebook-nl71



- 1 Water resistant keyboard with anti-peel keys
- 2 180-degree hinge
- 3 Drop resistant design
- 4 Reinforced ports, hinges and power plug
- 5 Anti-glare 11.6" HD Panel* (10 point multi-touch panel on NL7CT, CL7CT-L, NL71T and NL71TW models. Touchscreen models not anti-glare.)
- 6 Optional X-Protect Panel™ (Top Cover. Not shown in photo.)
- 7 180-degree rotating HD camera

32GB eMMC storage

Powerful Intel® Gemini Lake R N4020 Processor (4M Cache, up to 2.80 GHz)

Non-slip texture with carrying handle

USB-C Charging and HDMI port

IP rated design

HDMI port

Optional LTE

AUE June 2026

4GB Memory

32GB Storage

Intel® Gemini Lake R N4020 Processor (4M Cache, up to 2.80 GHz)

FEATURES & BENEFITS

- **180-degree rotating camera** to capture front-facing and world-facing views.
- **Intel® Wireless-AC 9560** is the first wireless solution that provides Gigabit Wi-Fi speeds. When using 160MHz channels, it can deliver up to 1.73Gbps maximum theoretical throughput, nearly 12x faster than baseline 1x1 BGN (150Mbps) Wi-Fi used in today's PCs.
- **NL71X includes the X-PANEL™** (patent pending) pressure-resistant cover. Built to withstand up to 365 lbs. of pressure, this added feature protects your investment and doubles as a whiteboard.
- **Want even more functionality?** Try our touch-versions. The NL71CT and NL71T model have 10-point capacitive touch screen, while the NL71TW and is compatible with Wacom Stylus 9013EMR Pen. The 360-degree hinges convert from laptop to tablet and makes interactive learning intuitive and easy!





Models: NL71, NL71X

CTL® Chromebook NL71/NL71X

Classic Clamshell with Optional X-panel



<p>PERFORMANCE</p>	<p>PROCESSOR Intel® Gemini Lake R N4020 Processor (4M Cache, up to 2.80 GHz)</p>	<p>MEMORY 4GB LPDDR4 1600 RAM</p>	<p>CAMERA HD 720P 180-degree rotating camera with LED indicator</p>	<p>AUDIO 1 Audio Combo Jack 2 Speakers</p>
	<p>OPERATING SYSTEM Chrome OS</p>	<p>GRAPHICS Intel® UHD Graphics 600</p>	<p>STORAGE 32GB eMMC and optional Google Drive storage</p>	<p>BATTERY Up to 12 hours of battery life Serviceable battery - can be replaced by school IT</p>
<p>DESIGN</p>	<p>DISPLAY* 16:9 HD 11.6" 1366 X 768 HD LED anti-glare screen</p>	<p>DIMENSION NL71: 11.5"x 8.0"x .81" NL71X: 11.5"x 8.0"x .88"</p>	<p>SCREEN Anti-glare</p>	<p>WEIGHT NL71: 2.5 lbs. NL71X: 2.85 lbs.</p>
	<p>CONNECTIVITY</p>	<p>PORTS</p> <ul style="list-style-type: none"> • 1x HDMI • 2x USB 3.0 • 1x USB-C • 1x 2-in-1 SD/MMC Card Reader • 1x Audio Combo Jack 	<p>DURABILITY & SECURITY</p> <ul style="list-style-type: none"> • Non-slip surface • Carrying handle • Kensington security lock slot • Optional X-panel <p>DC-in Cable USB-C Type</p>	<p>INTERNET CONNECTION WL/BT 802.11ABGN/AC 9560.NG.WG.NV Intel® 9560 Wireless</p>



UPGRADES



WARRANTIES

<ul style="list-style-type: none"> • Full Color Logo Painting • Chrome Management Licenses • White Glove Service • Bulk Pack Shipping • "Buy and Try" discounted prices • Store and Charge Carts • Educational apps 	<ul style="list-style-type: none"> • CTL 1 Year Parts/Labor Warranty (included with NL7 and NL7X) • CTL 1 Year AD Depot (included with NL7X) <p>Available warranty upgrades include:</p> <ul style="list-style-type: none"> • 1, 2, 3 and 4-year warranty • 1, 2, 3 and 4-year 2-way shipping • 1, 2, 3 and 4-year accidental damage • 3-year premium battery support • 3 and 4-year Complete Suite
--	---