

CTL® Chromebook NL71T/ NL71T-X2

Touch Screen Convertible with Optional Case

ctl.re/ctl-chromebook-nl7t



1 Water resistant keyboard with anti-peel keys

2 360-degree hinge

3 Drop resistant design

4 Reinforced ports, hinges and power plug

5 11.6" HD 10-point multi-touch IPS panel

6 One front and one world facing HD camera

7 Corning® Gorilla® Glass is scratch-resistant and durable

32GB eMMC storage

Powerful Intel® Gemini Lake R N4020 Processor (4M Cache, up to 2.80 GHz)

Non-slip texture and carrying handle

USB-C charging

IP rated design

MUMIMO - BT 5.0, speed up to 1.73 GHz

AUE June 2026

4GB Memory

32GB Storage

Intel® Gemini Lake R N4020 Processor (4M Cache, up to 2.80 GHz)

FEATURES & BENEFITS

- **10-point multi-touch Chromebook NL71T and NL71T-X2** make interactive learning intuitive and easy! The 360-degree hinge allows the device to convert to tablet orientation.
- **Convertible and ruggedized design.** Drop resistant and spill-proof, the Chromebook NL71T and NL71T-X2 are made to transport from home to the workplace or classroom. The Corning® Gorilla® Glass panel is durable, keeping the screen safe from cracks and scratches. The NL71T-X2 model includes and added extra protective case to prolong your investment.
- **Intel® Wireless-AC 9560** is the first wireless solution that provides Gigabit Wi-Fi speeds. When using 160MHz channels, it can deliver up to 1.73Gbps maximum theoretical throughput, nearly 12x faster than baseline 1x1 BGN (150Mbps) Wi-Fi used in today's PCs.
- **Bluetooth® 5 provides 4x2 the range** over Bluetooth® 5.0 Low Energy with the same power, doubles the transmit speed, and improves the broadcasting functionality. This translates to better coverage, improved location-based services, and simpler connectivity between devices.





Models: NL71T, NL71T-X2

CTL® Chromebook NL71T/ NL71T-X2

Touch Screen Convertible with Optional Case



<p>PERFORMANCE</p>	<p>PROCESSOR Intel® Gemini Lake R N4020 Processor (4M Cache, up to 2.80 GHz)</p> <p>OPERATING SYSTEM Chrome OS</p>	<p>MEMORY 4GB LPDDR4 1600 RAM</p> <p>GRAPHICS Intel® UHD Graphics 600</p>	<p>CAMERAS 2 HD cameras Front facing - 5.0MP 720P Rear facing - 1.0MP 720P</p> <p>STORAGE 32GB eMMC and optional Google Drive storage</p>	<p>AUDIO Stereo sound; integrated microphone rotates with camera</p> <p>BATTERY Up to 12 hours of battery life Serviceable battery - can be replaced by school IT</p>
<p>DESIGN</p>	<p>DISPLAY* 11.6" 1366 X 768 HD IPS Corning® Gorilla® Glass</p>	<p>DIMENSION NL71T: 12.13"x 8.19"x .81" NL71T-X2: 12.63"x 8.5"x .1.13"</p>	<p>SCREEN 10-point multi-touch IPS panel</p>	<p>WEIGHT NL71T: 2.8 lbs. NL71T-X2: 3.4 lbs.</p>
<p>CONNECTIVITY</p>	<p>PORTS</p> <ul style="list-style-type: none"> • 2x USB 3.0 • 2x USB-C • 1x 2-in-1 card reader • Audio Jack <p>DC-in Cable USB-C Type</p>	<p>DURABILITY & SECURITY</p> <ul style="list-style-type: none"> • Non-slip surface • Carrying handle • Kensington security lock slot • TPM 1.2 and 2.0 	<p>INTERNET CONNECTION WL/BT 802.11ABGN/AC Intel® 9560 Wireless MUMIMO - BT 5.0</p>	<p>SKU NL71T: CBUS1100002 NL71T-X2: CBKUS110003</p>



UPGRADES



WARRANTIES

- Full Color Logo Painting
- Chrome Management Licenses
- White Glove Service
- Bulk Pack Shipping
- "Buy and Try" discounted prices
- Store and Charge Carts
- Educational apps

- CTL 1 Year Parts/Labor Warranty
 - CTL 1 Year AD Depot
- Available warranty upgrades include:**
- 1, 2, 3 and 4-year warranty
 - 1, 2, 3 and 4-year 2-way shipping
 - 1, 2, 3 and 4-year accidental damage
 - 3-year premium battery support
 - 3 and 4-year Complete Suite