

# CTL® Chromebook NL71TW/NL71TW-X2

Touch Screen Convertible with Stylus and Optional Case



[ctl.re/ctl-chromebook-nl71tw](http://ctl.re/ctl-chromebook-nl71tw)



- ① Water resistant keyboard with anti-peel keys
- ② 360-degree hinge
- ③ Drop resistant design
- ④ Reinforced ports, hinges and power plug
- ⑤ 11.6" HD 10-point multi-touch IPS panel
- ⑥ Includes Wacom® Stylus 9013 EMR Pen
- ⑦ Corning® Gorilla® Glass is scratch-resistant and durable

One front and one world facing HD camera

Up to 64GB eMMC storage

Intel® Gemini Lake R Quad Core N4120 Processor (4M Cache, up to 2.60 GHz)

Non-slip texture and carrying handle

USB-C charging

IP rated design

**AUE June 2026**

**Up to 8GB LPDDR4 Memory**

**Up to 64GB storage**

**Intel® Gemini Lake R Quad Core N4120 Processor (4M Cache, up to 2.60 GHz)**

## FEATURES & BENEFITS

- **The electromagnetic resonance [EMR] pen** is included with the Chromebook NL71TW and makes interactive learning intuitive and easy! The 360-degree hinge allows the device to convert to tablet orientation.
- **Convertible and ruggedized design.** Drop resistant and spill-proof, the Chromebook NL71TW and NL71TW-X2 are made to transport from home to the workplace or classroom. The Corning® Gorilla® Glass panel is durable, keeping the screen safe from cracks and scratches. The NL71TW-X2 model includes and added extra protective case to prolong your investment.
- **Bluetooth® 5 provides 4x2 the range** over Bluetooth® 5.0 Low Energy with the same power, doubles the transmit speed, and improves the broadcasting functionality. This translates to better coverage, improved location-based services, and simpler connectivity between devices.
- **Intel® Wireless-AC 9560** is the first wireless solution that provides Gigabit Wi-Fi speeds. When using 160MHz channels, it can deliver up to 1.73Gbps maximum theoretical throughput, nearly 12x faster than baseline 1x1 BGN (150Mbps) Wi-Fi used in today's PCs.






Models: NL71TW, N71TW-X2

# CTL® Chromebook NL71TW/NL71TW-X2

## Touch Screen Convertible with Stylus and Optional Case



<p><b>PERFORMANCE</b></p>	<p><b>PROCESSOR</b> Intel® Gemini Lake R Quad Core N4120 Processor (4M Cache, up to 2.60 GHz)</p>	<p><b>MEMORY</b> 4GB LPDDR4 1600 RAM 8GB LPDDR4 1600 RAM</p>	<p><b>CAMERAS</b> 2 HD cameras Front facing - 5.0MP 720P Rear facing - 1.0MP 720P</p>	<p><b>AUDIO</b> Stereo sound; integrated microphone rotates with camera</p>
	<p><b>OPERATING SYSTEM</b> Chrome OS</p>	<p><b>GRAPHICS</b> Intel® UHD Graphics 600</p>	<p><b>STORAGE</b> 32GB eMMC 64GB eMMC Optional Google Drive storage</p>	<p><b>BATTERY</b> Up to 12 hours of battery life Serviceable battery - can be replaced by school IT</p>
<p><b>DESIGN</b></p>	<p><b>DISPLAY*</b> 11.6" 1366 X 768 HD IPS Corning® Gorilla® Glass</p>	<p><b>DIMENSION</b> NL71TW: 12.13"x 8.19"x .81" NL71TW-X2: 12.63"x 8.5"x 1.13"</p>	<p><b>SCREEN</b> 10-point multi-touch IPS panel</p>	<p><b>WEIGHT</b> NL71TW: 2.85 lbs. NL71TW-X2: 3.5 lbs.</p>
	<p><b>CONNECTIVITY</b></p> <p><b>PORTS</b></p> <ul style="list-style-type: none"> <li>• 2x USB 3.0</li> <li>• 2x USB-C</li> <li>• 1x 2-in-1 card reader</li> <li>• Audio Jack</li> <li>• Carrying handle</li> </ul>	<p><b>INTERNET CONNECTION</b> WL/BT 802.11ABGN/AC Intel® 9560 Wireless</p> <p><b>DC-in Cable</b> USB-C Type</p>	<p><b>SECURITY</b> TPM 1.2 and 2.0, Kensington Lock</p> <p><b>STYLUS</b> Includes Wacom® Stylus 9013 EMR Pen</p>	<p><b>SKU</b> 4GB NL71TW: CBUS1100003 4GB NL71TW-X2: CBKUS110004 8GB NL71TW: CBUS1100007 8GB NL71TW-X2: CBKUS110005</p>



### UPGRADES



### WARRANTIES

<ul style="list-style-type: none"> <li>• Full Color Logo Painting</li> <li>• Chrome Management Licenses</li> </ul>	<ul style="list-style-type: none"> <li>• CTL 1 Year Parts/Labor Warranty</li> <li>• CTL 1 Year AD Depot</li> </ul>
<ul style="list-style-type: none"> <li>• White Glove Service</li> <li>• Bulk Pack Shipping</li> </ul>	<p><b>Available warranty upgrades include:</b></p> <ul style="list-style-type: none"> <li>• 1, 2, 3 and 4-year warranty</li> </ul>
<ul style="list-style-type: none"> <li>• "Buy and Try" discounted prices</li> <li>• Store and Charge Carts</li> </ul>	<ul style="list-style-type: none"> <li>• 1, 2, 3 and 4-year 2-way shipping</li> <li>• 1, 2, 3 and 4-year accidental damage</li> </ul>
<ul style="list-style-type: none"> <li>• Educational apps</li> </ul>	<ul style="list-style-type: none"> <li>• 3-year premium battery support</li> <li>• 3 and 4-year Complete Suite</li> </ul>