

DynamiQ™ Wall Stand

Easy glide, height adjustable stand


The DynamiQ Wall Stand is a height adjustable wall-mounted stand—perfect solution for interactive displays in the classroom, library, training center or board room. The DynamiQ Wall Stand is ADA compliant and ideal for large displays.

The easy glide mount uses spring-weighted technology, which allows the display to move up or down with a simple touch of the finger.

Your choice of black or gun metal gray for frame and panel color. Panels may be custom skinned in veneer or laminate to match any environment. Cabling pathways throughout with 3RU of vertical rack space. The stand must be anchored to the wall.

FEATURES

- Supports a single display up to 198 lbs.
- Optional mount supports the 55" or 70" Cisco™ Spark Board
- ADA compliant
- Wall anchoring required
- 3RU vertical rack space
- 6-port surge protector
- Cable management features
- Ventilation requirements based on application
- Gun metal gray or black powder coat finish. Custom colors available
- 100% solid steel construction



Locking front door for easy access to rack space

SPECIFICATIONS

PRODUCT	DIMENSIONS	LIFT	VERTICAL ADJUST	RACK SPACE	LOAD CAPACITY	DISPLAY SIZE	PART NUMBER
DynamiQ Wall Stand	79"H x 29"W x 9"D	Easy glide	15.75"	3RU	44 - 83.6 lbs	Based on weight	D-WMS-BB40
					83.6 - 145.2 lbs	Based on weight	D-WMS-BB70
					145.2 - 198 lbs	Based on weight	D-WMS-BB90
	79"H x 48"W x 9"D				55" Cisco Spark Board	D-WMS-CSB55	
					79"H x 62"W x 9"D	70" Cisco Spark Board	D-WMS-CSB70



Call 800.285.8315 or visit AVTEQ.net

- facebook.com/avteq
- twitter.com/avteqinc
- youtube.com/avteq



Need a custom solution? Give us call.